

# PSR-M-EM7-SINCOS2-SC - Extension module



1105018

<https://www.phoenixcontact.com/us/products/1105018>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe extension module for monitoring zero-speed, speed, direction of rotation, monitoring of 2 axes, NPN/PNP proximity switch, 2 x sin/cos encoder, TBUS interface, up to SIL 3, Cat. 4/PL e, pluggable screw terminal block, TBUS connector included

## Product description

The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The safe extension module is used to monitor downtimes, speed, and direction of rotation. The module is suitable for connection of NPN/PNP proximity switches and sine/cosine encoders.

## Your advantages

- Cost-effective safety solution with a high level of adaptability to individual requirements
- Fast startup, thanks to easy hardware and software configuration
- Machine downtimes minimized with comprehensive, easy-to-understand diagnostics
- Low housing width of just 22.6 mm
- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Suitable for elevator applications in accordance with EN 81-20

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1105018       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN02          |
| Product key                          | DNA363        |
| GTIN                                 | 4055626974811 |
| Weight per piece (including packing) | 205.4 g       |
| Weight per piece (excluding packing) | 173 g         |
| Customs tariff number                | 85371098      |
| Country of origin                    | IT            |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|              |                                      |
|--------------|--------------------------------------|
| Product type | Safety device                        |
| Application  | Over-speed safety relay              |
|              | Zero-speed safety relay              |
|              | Monitoring the direction of rotation |
| Control      | 1 and 2 channel                      |

#### Insulation characteristics

|                  |     |
|------------------|-----|
| Protection class | III |
|------------------|-----|

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 2   |

#### Times

|               |                       |
|---------------|-----------------------|
| Response time | see user manual       |
| Restart time  | min. 5 s (Boot time)  |
|               | max. 10 s (Boot time) |

### Electrical properties

|                                                 |                                                                         |
|-------------------------------------------------|-------------------------------------------------------------------------|
| Maximum power dissipation for nominal condition | 3.68 W ( $U_B = 28,8 \text{ V}$ , $IN1 = IN2 = 50 \text{ mA}$ )         |
| Nominal operating mode                          | 100% operating factor                                                   |
| Interfaces                                      | DIN rail TBUS for connection to the master module, supplied as standard |
|                                                 | Encoder                                                                 |
|                                                 | Proximity switches                                                      |
| Rated surge voltage/insulation                  | Basic insulation 4 kV between 24 V power supply and I/Os to the housing |

#### Supply

|                                            |                                                                    |
|--------------------------------------------|--------------------------------------------------------------------|
| Designation                                | A1/A2                                                              |
| Rated control circuit supply voltage $U_S$ | 19.2 V DC ... 28.8 V DC                                            |
| Rated control circuit supply voltage $U_S$ | 24 V DC -20 % / +20 % (provide external protection, typically 1 A) |
| Rated control supply current $I_S$         | typ. 80 mA                                                         |
| Power consumption at $U_S$                 | typ. 1.92 W                                                        |
| Inrush current                             | 20 A ( $\Delta t = 500 \mu\text{s}$ at $U_S$ )                     |
| Filter time                                | typ. 5 ms (at A1 in the event of voltage dips at $U_S$ )           |
| Protective circuit                         | Serial protection against polarity reversal                        |
|                                            | Suppressor diode                                                   |

# PSR-M-EM7-SINCOS2-SC - Extension module



1105018

<https://www.phoenixcontact.com/us/products/1105018>

## Input data

### Measurement

|                                               |                                                     |
|-----------------------------------------------|-----------------------------------------------------|
| Input name                                    | Proximity switch inputs                             |
|                                               | IN1, IN2                                            |
| Description of the input                      | NPN / PNP (3- or 4-wire)                            |
| Number of inputs                              | 2                                                   |
| Input voltage range "0" signal                | 0 V DC ... 5 V DC (NPN)                             |
|                                               | 16 V DC ... 28.8 V DC (PNP)                         |
| Input voltage range "1" signal                | 16 V DC ... 28.8 V DC (NPN)                         |
|                                               | 0 V DC ... 5 V DC (PNP)                             |
| Input current range "0" signal                | < 2 mA (NPN)                                        |
| Precision                                     | 5 % (in reference to the parameterized limit value) |
| Limit frequency                               | max. 5 kHz                                          |
| Duty factor                                   | 55 % ... 95 %                                       |
| Pulse width                                   | min. 20 µs                                          |
| Max. permissible overall conductor resistance | 150 Ω                                               |
| Protective circuit                            | Suppressor diode                                    |
| Current consumption                           | typ. 13 mA (NPN, at U <sub>S</sub> )                |
|                                               | typ. -13 mA (PNP, at U <sub>S</sub> )               |
|                                               | max. 17 mA (NPN, at 28.8 V DC)                      |
|                                               | max. -15 mA (PNP, at 28.8 V DC)                     |

### Measurement

|                                        |                                                                                                    |
|----------------------------------------|----------------------------------------------------------------------------------------------------|
| Input name                             | Encoder inputs                                                                                     |
| Description of the input               | Sin/Cos                                                                                            |
|                                        | Diagnostic function: $\sin^2(x) + \cos^2(x) = 1$                                                   |
| Number of inputs                       | 2                                                                                                  |
| Input impedance                        | 120 Ω (per trace)                                                                                  |
| Precision                              | 5 % (in reference to the parameterized limit value)                                                |
| Limit frequency                        | max. 500 kHz                                                                                       |
| Sine / cosine Signal form/signal level | 0.8 V <sub>PP</sub> ... 1.2 V <sub>PP</sub> (Offset: 2.5 V ±20%, phase shift trace A, B: 90° ±30°) |
| Current consumption                    | typ. 8 mA (Per track for U <sub>S</sub> )                                                          |

## Output data

Digital: Proximity switch supply (24V/0V)

|                              |                                                  |
|------------------------------|--------------------------------------------------|
| Short-circuit protection     | no                                               |
| Nominal output voltage range | 16.7 V DC ... 26.3 V DC (U <sub>S</sub> - 2,5 V) |

## Connection data

### Connection technology

|           |     |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

# PSR-M-EM7-SINCOS2-SC - Extension module



1105018

<https://www.phoenixcontact.com/us/products/1105018>

## Conductor connection

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Connection method                | Screw connection                            |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |
| Stripping length                 | 7 mm                                        |
| Screw thread                     | M3                                          |
| Tightening torque                | 0.5 Nm ... 0.6 Nm                           |

## Signaling

|                           |                                                       |
|---------------------------|-------------------------------------------------------|
| Status display            | 1 x LED (green), 2 x LED (orange)<br>6 x LED (yellow) |
| Operating voltage display | 1 x LED (green)                                       |
| Error indication          | 2 x LED (red)                                         |

## Dimensions

|        |           |
|--------|-----------|
| Width  | 22.61 mm  |
| Height | 112.58 mm |
| Depth  | 114.5 mm  |

## Material specifications

|                  |                             |
|------------------|-----------------------------|
| Color (Housing)  | yellow (RAL 1018)           |
| Housing material | Polyamide PA non-reinforced |

## Characteristics

Safety data: EN ISO 13849

|                        |   |
|------------------------|---|
| Category               | 4 |
| Performance level (PL) | e |

Safety data: IEC 61508 - High demand

|                              |   |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: EN IEC 62061

|                              |   |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

## Environmental and real-life conditions

### Ambient conditions

|                                                |                                     |
|------------------------------------------------|-------------------------------------|
| Degree of protection                           | IP20                                |
| Min. degree of protection of inst. location    | IP54                                |
| Ambient temperature (operation)                | -10 °C ... 55 °C (observe derating) |
| Ambient temperature (storage/transport)        | -20 °C ... 85 °C                    |
| Maximum altitude                               | ≤ 2000 m (Above sea level)          |
| Max. permissible humidity (storage/transport)  | 95 % (non-condensing)               |
| Max. permissible relative humidity (operation) | 95 % (non-condensing)               |

# PSR-M-EM7-SINCOS2-SC - Extension module



1105018

<https://www.phoenixcontact.com/us/products/1105018>

|                       |                                                                                    |
|-----------------------|------------------------------------------------------------------------------------|
| Shock                 | 10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction) |
| Vibration (operation) | 10 Hz ... 150 Hz, 2g                                                               |

## Approvals

CE

|                |              |
|----------------|--------------|
| Identification | CE-compliant |
|----------------|--------------|

## Mounting

|                   |                        |
|-------------------|------------------------|
| Mounting type     | DIN rail mounting      |
| Assembly note     | Observe derating       |
| Mounting position | vertical or horizontal |


PSR-M-EM7-SINCOS2-SC - Extension module



1105018  
<https://www.phoenixcontact.com/us/products/1105018>


Drawings

Application drawing



Example application

Block diagram



Block diagram

# PSR-M-EM7-SINCOS2-SC - Extension module



1105018

<https://www.phoenixcontact.com/us/products/1105018>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1105018>



**cULus Listed**

Approval ID: E238705



**Functional Safety**

Approval ID: Z10029429 0013Rev.02

# PSR-M-EM7-SINCOS2-SC - Extension module



1105018

<https://www.phoenixcontact.com/us/products/1105018>

## Classifications

### ECLASS

|                   |          |
|-------------------|----------|
| ECLASS-13.0       | 27371819 |
| ECLASS-15.0       | 27371819 |
| ECLASS-15.0 ASSET | 27250101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001449 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|



# PSR-M-EM7-SINCOS2-SC - Extension module



1105018  
<https://www.phoenixcontact.com/us/products/1105018>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)