

# ES-FT-BPC-S 16-25 OG - Connector



1106303

<https://www.phoenixcontact.com/us/products/1106303>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Range of articles: BPC, color: orange, number of positions: 1, min. conductor cross-section: 16 mm<sup>2</sup>, max. conductor cross-section: 25 mm<sup>2</sup>, rated voltage: 1500, rated current: 120 A, Connection method: Screw connection

## Your advantages

- Patented design, with 3 proofs and one rotation
- Mismatching and short circuit proof
- Touch-proof
- Foolproof mechanism installed
- 360° free rotation and flexible wiring
- Safety lock

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1106303       |
| Packing unit                         | 15 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB04          |
| Product key                          | ABLDBA        |
| GTIN                                 | 4063151003494 |
| Weight per piece (including packing) | 29.707 g      |
| Weight per piece (excluding packing) | 19.872 g      |
| Customs tariff number                | 85359000      |
| Country of origin                    | CN            |

## Technical data

### Notes

#### Safety note

##### Safety note

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
- WARNING:** The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
  - o On the product
  - o On the packing label
  - o In the supplied documentation
  - o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product
- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

## Product properties

|                     |                               |
|---------------------|-------------------------------|
| Product type        | Connectors for energy storage |
| Product family      | BPC                           |
| Number of positions | 1                             |

## Insulation characteristics

|                     |   |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

## Electrical properties

|                                |                                                                                                                                                                                                                                 |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated voltage (III/2)          | 1500 V DC                                                                                                                                                                                                                       |
| Nominal voltage ATD            | 1500 (III/2.00) in accordance with IEC 61984<br>1000 in accordance with UL 4128                                                                                                                                                 |
| Rated current                  | 120 A (with 25 mm <sup>2</sup> conductor cross-section, in accordance with IEC 61984)<br>76 A (with 16 mm <sup>2</sup> conductor cross-section, in accordance with IEC 61984)<br>120 A (with AWG 4, in accordance with UL 4128) |
| Contact resistance             | ≤ 5 mΩ                                                                                                                                                                                                                          |
| Insulation resistance          | 1000 MΩ                                                                                                                                                                                                                         |
| Nominal voltage U <sub>N</sub> | 1000 V (in accordance with UL 4128)                                                                                                                                                                                             |

## Connection data

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
| Tightening torque | 0.6 ... 0.6 Nm   |

## Material specifications

|                                        |                                                           |
|----------------------------------------|-----------------------------------------------------------|
| Color                                  | orange                                                    |
| Material                               | Polyamide (Housing)<br>Copper (Contact)<br>Silicon (Seal) |
| Flammability rating according to UL 94 | V0                                                        |

## Cable/line

|                            |                                       |
|----------------------------|---------------------------------------|
| Single wire, cross section | 16 mm <sup>2</sup> 25 mm <sup>2</sup> |
| AWG signal line            | 4                                     |
| Cable pull-out force       | ≥ 10 N                                |

## Mechanical properties

### Mechanical data

|                             |        |
|-----------------------------|--------|
| Insertion/withdrawal cycles | 100    |
| Insertion force             | ≤ 75 N |
| Withdrawal force            | ≥ 10 N |

1106303

<https://www.phoenixcontact.com/us/products/1106303>

## Environmental and real-life conditions

### Ambient conditions


|                                         |                                       |
|-----------------------------------------|---------------------------------------|
| Degree of protection (when plugged in)  | IP65 (The panel is feed-through hole) |
| Degree of protection (not plugged in)   | IP20                                  |
| Degree of protection                    | IP65                                  |
| Ambient temperature (operation)         | -40 °C ... 70 °C                      |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                      |
| Altitude                                | 4000 m                                |

## Standards and regulations


|                          |                 |
|--------------------------|-----------------|
| Standard designation     | TÜV (PPP51090A) |
| Standards/specifications | IEC 61984:2008  |
|                          | EN 61984:2008   |
|                          | UL 4128         |
|                          | PPP 51090A      |

## Drawings

Dimensional drawing



Drilling plan/solder pad geometry



# ES-FT-BPC-S 16-25 OG - Connector



1106303

<https://www.phoenixcontact.com/us/products/1106303>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1106303>

|       | TÜV SÜD Type tested<br>Approval ID: 704071905102-03 |                                |                   |                               |
|-------|-----------------------------------------------------|--------------------------------|-------------------|-------------------------------|
|       | Nominal voltage U <sub>N</sub>                      | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine | 1500 V                                              | 120 A                          | -                 | 16 - 25                       |

|       | UL Recognized<br>Approval ID: E511681-20200609 |                                |                   |                               |
|-------|------------------------------------------------|--------------------------------|-------------------|-------------------------------|
|       | Nominal voltage U <sub>N</sub>                 | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine | 1000 V                                         | 120 A                          | - 4               | -                             |

# ES-FT-BPC-S 16-25 OG - Connector



1106303

<https://www.phoenixcontact.com/us/products/1106303>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440209 |
| ECLASS-15.0 | 27440209 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002641 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# ES-FT-BPC-S 16-25 OG - Connector



1106303

<https://www.phoenixcontact.com/us/products/1106303>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)