

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLCnext Technology Starterkit including PLCnext Control AXC F 2152, AXL Smart Elements DI16/DO16/AI4 I/O modules, slide potentiometer, push buttons, power supply unit, and patch cables.

## Product description

Would you prefer to try out the operating principle, handling, and high performance of PLCnext Technology in a small-scale application first? Phoenix Contact can provide you with a starter kit for this, complete with pre-installed components for your test applications.

## Your advantages

- Quick application development: several developers work independently in different programming languages
- Convenient engineering with your favorite programming tools
- PLC-typical real-time performance and data consistency, also for high-level languages and model-based code
- Limitless adaptation capabilities, thanks to the quick and easy integration of open-source software, apps, and future technologies
- Intelligent networking, thanks to cloud connection and the integration of current and future communication standards

## Commercial data

Item number	1188165
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DT04
Product key	DTHDBA
GTIN	4063151233426
Weight per piece (including packing)	2.48 g
Weight per piece (excluding packing)	2.087 g
Customs tariff number	85371091
Country of origin	DE

# PLCNEXT TECHNOLOGY STARTERKIT - Starter kit



1188165

<https://www.phoenixcontact.com/us/products/1188165>

## Set consists of

### AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



Controller (SPS), PLCnext Control; Programming: High-level language and IEC 61131-3; Operating system: Yocto/Linux® (real-time); Programming tool: PLCnext Engineer, Eclipse®, Visual Studio®, MATLAB®/ Simulink®; IoT connection: PROFICLOUD and every cloud via cloud connectors; Development process certified in accordance with IEC 62443-4-1, Product certified in accordance with IEC 62443-4-2 (Certification conditions see user documentation); Processor: Arm® Cortex®-A9, 2x 800 MHz.

---

### AXL F BP SE4 - Module carrier

1088135

<https://www.phoenixcontact.com/us/products/1088135>



Axioline F, Backplane, 4 slots for Axioline Smart Elements, transmission speed in the local bus: 100 Mbps, degree of protection: IP20

1188165

<https://www.phoenixcontact.com/us/products/1188165>

## AXL SE AI4 U 0-10 - Analog module

1088104

<https://www.phoenixcontact.com/us/products/1088104>



Axiline Smart Elements, Analog input module, Analog inputs: 4, 0 V ... 10 V, connection technology: 2-conductor, degree of protection: IP20

---

## AXL SE DI16/1 - Digital module

1088127

<https://www.phoenixcontact.com/us/products/1088127>



Axiline Smart Elements, Digital input module, Digital inputs: 16, 24 V DC, connection technology: 1-conductor, degree of protection: IP20

# PLCNEXT TECHNOLOGY STARTERKIT - Starter kit



1188165

<https://www.phoenixcontact.com/us/products/1188165>

## AXL SE DO16/1 - Digital module

1088129

<https://www.phoenixcontact.com/us/products/1088129>



Axioline Smart Elements, Digital output module, Digital outputs: 16, 24 V DC, 500 mA, connection technology: 1-conductor, degree of protection: IP20

---

## FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>



Patch cable, CAT5, assembled, 1 m

# PLCNEXT TECHNOLOGY STARTERKIT - Starter kit



1188165

<https://www.phoenixcontact.com/us/products/1188165>

## AXL SE SC - Cover

1167159

<https://www.phoenixcontact.com/us/products/1167159>

Axioline Smart Elements, Slot cover, degree of protection: IP20



Technical data

Notes

Note regarding documentation	For technical data, refer to the product documentation in the "Downloads" area
------------------------------	--

Product properties

Product type	Starter kit
--------------	-------------

System properties

System requirements	
Engineering tool	PLCnext Engineer

1188165

<https://www.phoenixcontact.com/us/products/1188165>

## Classifications

### ECLASS

ECLASS-13.0	27242219
ECLASS-15.0	27242219

### ETIM

ETIM 9.0	EC002581
----------	----------

### UNSPSC

UNSPSC 21.0	32151700
-------------	----------

1188165

<https://www.phoenixcontact.com/us/products/1188165>

## Environmental product compliance

## EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I, 7(c)-II

## China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

## EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c0d32a94-8e11-4144-b2f3-fb7b016a7b56

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)