

# AI-TWIN 2X10 -14 BN - Ferrule



1213206

<https://www.phoenixcontact.com/us/products/1213206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 14 mm, sleeve length: 26 mm, color: brown

## Your advantages

- These special ferrules allow chain bridges to be set up with ease
- The TWIN ferrules provide a practical way of crimping two conductors in one ferrule
- Different versions of the individual TWIN ferrules can be selected for specific applications

## Commercial data

Item number	1213206
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH3413
GTIN	4055626280868
Weight per piece (including packing)	0.996 g
Weight per piece (excluding packing)	0.932 g
Customs tariff number	85369010
Country of origin	DE

1213206

<https://www.phoenixcontact.com/us/products/1213206>

## Technical data

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of UL 486F
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

### Connection data

#### Conductor connection

Conductor cross-section flexible max.	10 mm <sup>2</sup>
Conductor cross-section AWG max.	8
Stripping length	19 mm

### Dimensions

Dimensional drawing	
Sleeve length	26 mm
Length contact range	14 mm
Maximum stripping length	19 mm
Ferrule diameter	6.5 mm
Sleeve wall thickness	0.2 mm
Insulating collar thickness	0.4 mm
Inner dimensions of the insulating collar	7.2 mm

### Material specifications

Color	brown (RAL 8028)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

#### Technical data

# AI-TWIN 2X10 -14 BN - Ferrule



1213206

<https://www.phoenixcontact.com/us/products/1213206>

Sleeve length	26 mm
---------------	-------

## Environmental and real-life conditions

### Ambient conditions


Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

## Standards and regulations

Design according to standard	UL 486F-F, NF C 63-023
------------------------------	------------------------

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI-TWIN 2X10 -14 BN - Ferrule



1213206

<https://www.phoenixcontact.com/us/products/1213206>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1213206>



**cULus Listed**

Approval ID: E488001

# AI-TWIN 2X10 -14 BN - Ferrule



1213206

<https://www.phoenixcontact.com/us/products/1213206>

## Classifications

### ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# AI-TWIN 2X10 -14 BN - Ferrule



1213206  
<https://www.phoenixcontact.com/us/products/1213206>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)