

# SACC-DSI-M12FSL4CON-M16XL-L180X - Device connector rear mounting



1239524

<https://www.phoenixcontact.com/us/products/1239524>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Power, 4-position, Socket, straight, M12, L-coding, Wave soldering, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- For compact devices: transmit high power in a confined space
- Easy-to-install, optimized XL housing contour with wrench size 19
- Mechanical tightening limitation for long-term-stable gasket

## Commercial data

Item number	1239524
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB26
Product key	ABQEHN
GTIN	4063151432744
Weight per piece (including packing)	17.635 g
Weight per piece (excluding packing)	16.607 g
Customs tariff number	85366990
Country of origin	DE



# SACC-DSI-M12FSL4CON-M16XL-L180X - Device connector rear mounting



1239524

<https://www.phoenixcontact.com/us/products/1239524>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

### Product properties

Product type	Circular connectors (device side)
Sensor type	Power
Number of positions	4
Shielded	no
Coding	L
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

### Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage $U_N$	63 V DC
Nominal current $I_N$	16 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

### Mechanical properties



# SACC-DSI-M12FSL4CON-M16XL-L180X - Device connector rear mounting



1239524

<https://www.phoenixcontact.com/us/products/1239524>

## Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	L

## Cable/line

Signal type/category	Power
----------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
	IP65/IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111




# SACC-DSI-M12FSL4CON-M16XL-L180X - Device connector rear mounting

1239524

<https://www.phoenixcontact.com/us/products/1239524>

## Drawings

Schematic diagram



Pin assignment of M12 socket, 4-pos., L-coded, socket side view



# SACC-DSI-M12FSL4CON-M16XL-L180X - Device connector rear mounting



1239524  
<https://www.phoenixcontact.com/us/products/1239524>

## Classifications

### ECLASS

ECLASS-13.0	27440110
-------------	----------

### ETIM

ETIM 9.0	EC003569
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------



# SACC-DSI-M12FSL4CON-M16XL-L180X - Device connector rear mounting



1239524

<https://www.phoenixcontact.com/us/products/1239524>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)