

MC 1000-MM ST - FO converters



1329818

<https://www.phoenixcontact.com/us/products/1329818>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with ST (B-FOC) connection (1310 nm) for 100Base-TX to multimode fiber optics, DIN rail mountable.

Product description

The MC 1000-MM ST media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an ST connector

Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring

Commercial data

Item number	1329818
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC314
GTIN	4063151625702
Weight per piece (including packing)	184.9 g
Weight per piece (excluding packing)	110 g
Customs tariff number	85176200
Country of origin	CA

MC 1000-MM ST - FO converters

1329818

<https://www.phoenixcontact.com/us/products/1329818>



Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Media converter
Product family	MC 1000
MTTF	84.6 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	756.3 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	668.4 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day))

Electrical properties

Supply

Supply voltage range	12 V DC ... 48 V DC
Nominal supply voltage	24 V DC
Typical current consumption	20 mA (24 V DC)
Max. current consumption	170 mA (12 V DC, 60 °C)

Connection data

Supply

Connection method	Push-in spring connection
Single conductor/terminal point, rigid	0.2 mm² ... 2.5 mm²
Single-wire/terminal point, flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section, flexible [AWG]	24 ... 12
Conductor cross-section AWG	24 ... 12
Stripping length	10.00 mm

Interfaces

Signal	Ethernet
--------	----------

Data: optical FO

Transmit capacity, minimum	-20 dBm (62.5/125 µm, multimode fiberglass)
	-23.5 dBm (50/125 µm, multimode fiberglass)
Transmit capacity, maximum	-14 dBm
Transmission length incl. 3 dB system reserve	2 km

MC 1000-MM ST - FO converters



1329818

<https://www.phoenixcontact.com/us/products/1329818>

Connection method	B-FOC (ST)
Wavelength	1310 nm
Minimum receiver sensitivity	-32 dBm
Maximum receiver sensitivity	-8 dBm
Transmission medium	Multi-mode fiberglass

Data: Ethernet interface, 100Base-T(X) in accordance with IEEE 802.3

Transmission speed	10/100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, SPD, US
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

Dimensions

Width	22.5 mm
Height	123 mm
Depth	90 mm

Material specifications

Housing material	Polyamide fiber reinforced
------------------	----------------------------

Cable/line

FO cable

Fiber types	50/125 µm
	62.5/125 µm
	Fiberglass

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 5g, 150 Hz, Criterion 3
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 30g, 11 ms half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (in acc. with UL)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Shock	300 m/s ² , 11 ms (IEC 60068-2)

MC 1000-MM ST - FO converters



1329818

<https://www.phoenixcontact.com/us/products/1329818>

Approvals

CE

Certificate	CE-compliant
-------------	--------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Comments	Criterion B
----------	-------------

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Comments	Criterion A
----------	-------------

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Comments	Criterion A
----------	-------------

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Comments	Criterion B
----------	-------------

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Comments	Criterion A
----------	-------------

Emitted interference

Standards/regulations	EN 55032
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715
Useable DIN rail type	DIN rail: 35 mm

MC 1000-MM ST - FO converters

1329818

<https://www.phoenixcontact.com/us/products/1329818>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1329818>



cULus Listed

Approval ID: E238705

MC 1000-MM ST - FO converters

1329818

<https://www.phoenixcontact.com/us/products/1329818>



Classifications

ECLASS

ECLASS-13.0	19170411
ECLASS-15.0	19170411

ETIM

ETIM 9.0	EC001467
----------	----------

UNSPSC

UNSPSC 21.0	43223323
-------------	----------

MC 1000-MM ST - FO converters

1329818

<https://www.phoenixcontact.com/us/products/1329818>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

MC 1000-MM ST - FO converters



1329818


<https://www.phoenixcontact.com/us/products/1329818>

Accessories

FKCT 2,5/ 3-ST KMGY - PCB connector

1998263

<https://www.phoenixcontact.com/us/products/1998263>



PCB connector, nominal cross section: 2.5 mm², color: light gray, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: FKCT 2,5/...-ST, pitch: 5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting method: without, type of packaging: packed in cardboard

DT-LAN-CAT.6+ - Surge protection device

2881007

<https://www.phoenixcontact.com/us/products/2881007>



Surge protection in accordance with Class E_A (CAT6_A), for Gigabit Ethernet (up to 10 Gbps), token ring, FDDI/CDDI, ISDN, DS1. Suitable for Power over Ethernet (PoE++/4PPoE) "Mode A" and "Mode B". RJ45 intermediate plug with separate grounding cable and ground connection snap-on foot for NS 35 DIN rails. Products with similar requirements: DT-LAN-CAT.6A (2908726) und D-LAN-CAT.5-HC (2800763).

MC 1000-MM ST - FO converters



1329818

<https://www.phoenixcontact.com/us/products/1329818>

FL DIN-RAIL ADAPTER 22.5 - Mounting panel

1085485

<https://www.phoenixcontact.com/us/products/1085485>



The FL DIN-RAIL ADAPTER 22.5 is designed to allow products 22.5 mm wide to be mounted flush to a standard 35 mm DIN rail, in any orientation.

FL PANEL ADAPTER 22.5 - Mounting panel

1085488

<https://www.phoenixcontact.com/us/products/1085488>



The FL PANEL ADAPTER 22.5 is designed to allow products 22.5 mm wide to be mounted flush to a panel, in any orientation.

MC 1000-MM ST - FO converters

1329818


<https://www.phoenixcontact.com/us/products/1329818>



E/NS 35 N - End bracket

0800886

<https://www.phoenixcontact.com/us/products/0800886>



End clamp, width: 9.5 mm, color: gray

FL CAT5 PATCH 0,5 - Patch cable

2832263

<https://www.phoenixcontact.com/us/products/2832263>



Patch cable, CAT5, assembled, 0.5 m

MC 1000-MM ST - FO converters

1329818

<https://www.phoenixcontact.com/us/products/1329818>



FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>



Patch cable, CAT5, assembled, 1 m

FL CAT5 PATCH 2,0 - Patch cable

2832289

<https://www.phoenixcontact.com/us/products/2832289>



Patch cable, CAT5, assembled, 2 m

MC 1000-MM ST - FO converters

1329818


<https://www.phoenixcontact.com/us/products/1329818>



NBC-R4AC-R4AC-IE8A/.../... - Patch cable

1411854

<https://www.phoenixcontact.com/us/products/1411854>




Patch cable, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, cable outlet: straight, Ethernet

NBC-R4AC/10G-R4AC/10G-94F/2,0 - Patch cable

1408360

<https://www.phoenixcontact.com/us/products/1408360>



Patch cable, CAT6_A, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 2.0 m

MC 1000-MM ST - FO converters




1329818

<https://www.phoenixcontact.com/us/products/1329818>

NBC-R4AC/10G-R4AC/10G-94F/3,0 - Patch cable

1408365

<https://www.phoenixcontact.com/us/products/1408365>




Patch cable, CAT6_A, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 3.0 m

FOC-ST:PA-SC:PA-OM2:D01/1 - FO patch cable

1115574

<https://www.phoenixcontact.com/us/products/1115574>



Multi-mode OM2 duplex jumper, ST-SC, UPC polishing, length 1 m

MC 1000-MM ST - FO converters



1329818


<https://www.phoenixcontact.com/us/products/1329818>

FOC-ST:PA-SC:PA-OM2:D01/2 - FO patch cable

1115573

<https://www.phoenixcontact.com/us/products/1115573>

Multi-mode OM2 duplex jumper, ST-SC, UPC polishing, length 2 m



FOC-ST:PA-ST:PA-OM2:D01/1 - FO patch cable

1115560

<https://www.phoenixcontact.com/us/products/1115560>

Multi-mode OM2 duplex jumper, ST-ST, UPC polishing, length 1 m



MC 1000-MM ST - FO converters



1329818

<https://www.phoenixcontact.com/us/products/1329818>

FOC-ST:PA-ST:PA-OM2:D01/2 - FO patch cable

1115557

<https://www.phoenixcontact.com/us/products/1115557>

Multi-mode OM2 duplex jumper, ST-ST, UPC polishing, length 2 m




FOC-LC:PA-ST:PA-OM2:D01/1 - Fiber optic cable

1115588

<https://www.phoenixcontact.com/us/products/1115588>

Multi-mode OM2 duplex jumper, LC-ST, UPC polishing, length 1 m



MC 1000-MM ST - FO converters

1329818

<https://www.phoenixcontact.com/us/products/1329818>




FOC-LC:PA-ST:PA-OM2:D01/2 - Fiber optic cable

1115587

<https://www.phoenixcontact.com/us/products/1115587>

Multi-mode OM2 duplex jumper, LC-ST, UPC polishing, length 2 m



SZS 0,4X2,0 - Screwdriver

1205202

<https://www.phoenixcontact.com/us/products/1205202>

Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap



MC 1000-MM ST - FO converters



1329818

<https://www.phoenixcontact.com/us/products/1329818>

FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/us/products/2891053>

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com