

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Temperature recording module, Functional safety, Inputs for resistive temperature sensors, PROFI-safe, only for connection to Phoenix Contact or Siemens controller, Safe analog inputs: 8 (1-channel assignment), 4 (2-channel assignment), connection technology: 2-, 3-, 4-conductor (shielded), transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connectors

Your advantages

- 8 safe inputs for 1-channel assignment
- 4 safe inputs for 2-channel assignment

Commercial data

Item number	1374265
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNA522
GTIN	4063151733094
Weight per piece (including packing)	244.47 g
Weight per piece (excluding packing)	189.88 g
Country of origin	DE

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Technical data

Dimensions

Width	53.6 mm
Height	126.1 mm
Depth	54 mm
Note on dimensions	Housing dimensions

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Interfaces

Axioline F local bus

Connection method	Bus base module
Transmission speed	100 Mbps




System properties

Module

Input address area	22 Byte
Output address area	5 Byte

Input data

Analog

Input name	Safe analog inputs
Description of the input	Inputs for resistive temperature sensors
Number of inputs	8 (1-channel assignment)
	4 (2-channel assignment)
Connection method	Push-in connection
Connection technology	2-, 3-, 4-conductor (shielded)
A/D converter resolution	24 bit
Data formats	Standardized representation
Measured value representation	16 bits (15 bits + sign bit)
Nominal value of the current sources	100 μ A
Linear resistance measuring range	0 Ω ... 327.67 Ω (Resolution: 0.01 Ω )
	0 Ω ... 3276.7 Ω (Resolution: 0.1 Ω )
	0 k Ω ... 5400 Ω (Resolution: 1 Ω )
Protective circuit	Short-circuit protection, overload protection of the inputs
	Transient protection of inputs; Suppressor diode
	Transient protection of sensor supplies

Product properties

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Product type	I/O component
Product family	Axioline F
Application	Functional safety
	Inputs for resistive temperature sensors
	PROFIsafe
	only for connection to Phoenix Contact or Siemens controller
Type	modular
Mounting position	any
Scope of supply	including bus base module and Axioline F connectors
Operating mode	PROFIsafe 2.6.1

Insulation characteristics

Overvoltage category	II (IEC 60664-1)
Pollution degree	2 (IEC 60664-1)

Electrical properties

Potentials: Axioline F local bus supply (U_{Bus})

Supply voltage	5 V DC (via bus base module)
Current draw	typ. 115 mA (at U_{Bus} 5 V DC)

Potentials: I/O supply (U_A)

Supply voltage	24 V DC (Power connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 10 mA
Protective circuit	Surge protection
	Reverse polarity protection ()
	Undervoltage detection; at 16.8 V
	Surge voltage detection; yes, at 33.5 V

Connection data

Conductor connection

Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm
Connection method	Push-in connection
Note on the connection method	Note the specification in the section Conductor cross-sections, and stripping and insertion lengths.
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Environmental and real-life conditions

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Ambient conditions

Ambient temperature (operation)	-35 °C ... 60 °C
Degree of protection	IP20
Degree of protection at installation location	min. IP54
Note	Recommendation Do not use the AXL F PSRTD8 1F in an atmosphere that contains corrosive gas.
Air pressure (operation)	70 kPa ... 108 kPa
Air pressure (storage/transport)	66 kPa ... 108 kPa
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140-1)
------------------	-------------------

Air clearances and creepage distances

Air clearances and creepage distances	IEC 60664-1
---------------------------------------	-------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1374265>



cULus Listed

Approval ID: E238705

PROFIsafe

Approval ID: Z20396

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

ETIM

ETIM 9.0	EC001596
----------	----------

AXL F PSRTD8 1F - Safety module



1374265

<https://www.phoenixcontact.com/in/products/1374265>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I, 7(c)-II

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in