

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, PVC, green RAL 6018, Socket, straight, M12-SPEEDCON, D-coding, on free cable end, Bus line, cable length: 5 m, 0.34 mm², PROFINET, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1402474
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABQDGI
GTIN	4046356616669
Weight per piece (including packing)	356.1 g
Weight per piece (excluding packing)	330.715 g
Country of origin	DE

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

Safety note

Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property. • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the corresponding technical data. You will find information: - o On the product - o On the packing label - o In the supplied documentation - o Online at phoenixcontact.com/products under the product • Only use tools recommended by Phoenix Contact • Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory
-------------	--

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Mounting

Mounting type

Rear mounting (M16 x 1,5)

Product properties

Product type

Circular connectors (device side)

Number of positions

4

No. of cable outlets

1

Shielded

yes

Coding

D

Thread type

M12

Insulation characteristics

Overvoltage category

II

Degree of pollution

3

Material specifications

Material Housing

GD-Zn

Material Housing surface

Ni

Material Insulating body

PA 6.6

Material Contact

CuZn

Material Contact surface

Au

Material Seal

NBR

Flammability rating according to UL 94

V0

Outer sheath, material

PVC

Conductor material

Tin-plated Cu litz wires

Electrical properties

Rated surge voltage

2.5 kV AC

Contact resistance

≤ 3 mΩ

Insulation resistance

≥ 100 MΩ

Nominal voltage U_N

250 V

Nominal current I_N

4 A

Transmission medium

Copper

Transmission characteristics (category)

CAT5 (IEC 11801:2002)

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Wave impedance	100 Ω
----------------	--------------

Connection data

Conductor connection

Connection method	Bus line
Contact connection type	Socket
Conductor cross-section	0.34 mm ²

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	D


Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	5 m
--------------	-----

PROFINET PVC stranded CAT5 [93B]

Dimensional drawing	
UL AWM Style	21695 (80 °C / 600 V)
Number of positions	4
Shielded	yes
Cable type	PROFINET PVC stranded CAT5 [93B]
Conductor structure	1x4xAWG22/7, SF/TQ
AWG signal line	22
Conductor cross section	4x 0.34 mm ²
Wire diameter incl. insulation	1.5 mm $\pm$ 0.1 mm
External cable diameter	6.50 mm $\pm$ 0.2 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Material wire insulation	PE
Single wire, color	white, yellow, blue, orange
Overall twist	Star quad
Optical shield covering	85 %
Insulation resistance	$\geq 5 \text{ G}\Omega \cdot \text{km}$
Loop resistance	$\leq 120.00 \text{ }\Omega/\text{km}$
Wave impedance	$100 \text{ }\Omega \pm 5 \text{ }\Omega$ (at 100 MHz)
Nominal voltage, cable	$\leq 600 \text{ V}$
Test voltage Core/Core	2000 V ((50 Hz/1 min))
Test voltage Core/Shield	2000.00 V ((50 Hz/1 min))
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1685 (CSA FT 4)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
Resistance to oil	OIL RES I according to UL 2256
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-10 °C ... 70 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (cable, fixed installation)
	-5 °C ... 50 °C (Cable, flexible installation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	according to IEC 61076-2-101


SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting

1402474

<https://www.phoenixcontact.com/us/products/1402474>

Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side


SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Circuit diagram



Contact assignment of the M12 socket

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1402474>

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	4 A	- 22	-

 cUL Recognized Approval ID: E221474-20220907				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	1.5 A	-	-

 UL Recognized Approval ID: E221474-20220907				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	4 A	-	-

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 9.0	EC003570
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACCBP-FSD-4CON-M16/5,0-933SCO - Device connector rear mounting



1402474

<https://www.phoenixcontact.com/us/products/1402474>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a08afcfa-4695-48df-bde2-604b31ee07f0

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com