

1732664  
<https://www.phoenixcontact.com/us/products/1732664>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Managed switch with 24 SFP ports at 100/1000 Mbps, 4 SFP ports at 1000/10000 Mbps, operating temperature: -40 °C ... +85 °C, and power supply: 24 V DC ... 48 V DC



### Product description

Developed according to IEC 61850-3 (Ambient conditions)

### Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- Layer 2 managed switch
- 28-port rack-mount switch

### Commercial data

Item number	1732664
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN36
Product key	DNN513
GTIN	4067923290365
Weight per piece (including packing)	6,552 g
Weight per piece (excluding packing)	4,550 g
Country of origin	TW

# FL SWITCH EP5200-28SFP-LV - Industrial Ethernet Switch



1732664

<https://www.phoenixcontact.com/us/products/1732664>

## Technical data

### Dimensions

Width	442 mm
Height	44 mm
Depth	325 mm

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color	gray
Housing material	Metal

### Mounting

Mounting type	Rack mounting (with holder)
Holder system	19" rack

### Interfaces

#### Ethernet (SFP)

Connection method	SFP
Transmission speed	1000/10,000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
No. of channels	4 (SFP ports)

#### Ethernet (SFP)

Connection method	SFP
Transmission speed	100/1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
No. of channels	24 (SFP ports)

### Output data

#### Digital:

Output name	Alarm relay output: 30 V DC, 0.6 A maximum
-------------	--

### Product properties

Product type	Switch
Product family	Managed Switch EP5000
MTBF	87.4 Years (Telcordia standard, 25 °C temperature, 50% stress)
	5.9 Years (MIL-HDBK-217F standard, temperature 25°C)
	SN 29500 standard, temperature 25°C, operating cycle 21%

# FL SWITCH EP5200-28SFP-LV - Industrial Ethernet Switch



1732664

<https://www.phoenixcontact.com/us/products/1732664>

## Switch functions

Signal contact control voltage	30 V DC
Signal contact control current	0.6 A
MAC address table	16k
Redundancy	RSTP (Rapid Spanning Tree, IEEE 802.1w)
	STP
	MSTP
Status and diagnostic indicators	LEDs: POWER, ERROR, Link status

## Electrical properties

Local diagnostics	US1, US2 Supply voltage Green LED
	Alarm Alarm signal LED red
Maximum power dissipation for nominal condition	50 W ()

## Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	24 V DC ... 48 V DC (Screw connection)

## Function

Signal contact control voltage	30 V DC
Signal contact control current	0.6 A

## Connection data

### Connection technology

Connection name	Power supply
-----------------	--------------

### Power supply

Connection method	Screw connection
-------------------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-40 °C ... 85 °C (Type tested to 85 °C for 16 hours)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

## Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3
	IEEE 1613

## Approvals

### Conformity/Approvals

1732664  
<https://www.phoenixcontact.com/us/products/1732664>

Conformance	CE-compliant
EMC data	
Noise immunity	IEC 61850-3, IEEE 1613
Signaling	
Status display	LEDs: POWER, ERROR, Link status

# FL SWITCH EP5200-28SFP-LV - Industrial Ethernet Switch



1732664  
<https://www.phoenixcontact.com/us/products/1732664>

## Classifications

### ECLASS

ECLASS-13.0	19170401
ECLASS-15.0	19170401

### ETIM

ETIM 9.0	EC000734
----------	----------

# FL SWITCH EP5200-28SFP-LV - Industrial Ethernet Switch



1732664

<https://www.phoenixcontact.com/us/products/1732664>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)