

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PE-X halogen-free, black, shielded, free cable end, on Socket straight M12 SPEEDCON, coding: A, cable length: 10 m, For railway applications

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Securely locked by special vibration brake
- Resistant to temperature influences – tested for an extended temperature range and for resistance to temperature shocks
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1407333
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF03
Product key	AF1CDA
GTIN	4046356774499
Weight per piece (including packing)	714.5 g
Weight per piece (excluding packing)	714 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Technical data

Notes

General	Further products with variable cable type and variable cable length can be found in the accessories section
---------	---

Product properties

Product type	Sensor/actuator cable
Application	Railway applications
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	PA 6.6
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated
Standards/regulations	PA 6.6

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A

Cable/line

Cable length	10 m
--------------	------

Shielded black RADOX® [28R]

Dimensional drawing		
Cable weight	70 kg/km	
Number of positions	5	
Shielded	yes	
Cable type	Shielded black RADOX® [28R]	
Conductor structure signal line	19x 0.18 mm	
AWG signal line	20	
Conductor cross section	5x 0.5 mm²	
Wire diameter incl. insulation	1.43 mm	
External cable diameter	6.20 mm ±0.3 mm	
Outer sheath, material	PE-X	
External sheath, color	black	
Conductor material	Tin-plated Cu litz wires	
Material wire insulation	PE-X	
Single wire, color	white 1, white 2, white 3, white 4, white 5	
Overall twist	5 cores, twisted	
Max. conductor resistance	≤ 40.1 Ω/km	
Nominal voltage, cable	600 V AC (Core-ground, U ₀)	
	1000 V AC (Core-ground, U)	
	≤ 720 V AC (core-ground)	
	≤ 1200 V AC (Core-ground, U _m)	

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Test voltage	≤ 900 V DC (Core-ground, V ₀)
	≤ 1500 V DC (Line-line)
	3500 V AC (50 Hz, 5 min.)
	8400 V DC (50 Hz, 5 min.)
Minimum bending radius, fixed installation	3 x D
Minimum bending radius, flexible installation	4 x D
Smallest bending radius, fixed installation	19 mm
Smallest bending radius, movable installation	25 mm
Halogen-free	in accordance with EN 50267-2-1
Flame resistance	IEC 60332-1-2
	EN 50266
	EN 60332-3-25
	NF C32-070, 2.1
	NF C32-070, 2.2
	UL 1685, 12 (FT4)
	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Fume corrosiveness	EN 50267-2-2
Fume toxicity	BS 6853 B.1
	EN 50305, 9.2
Concentration of fumes	BS 6853 D.8.7
	EN 61034-2
	UL 1685, 12 (FT4)
Resistance to oil	according to IRM 902, 72 h at 100 °C
Fire protection in rail vehicles	BS 6853 (Category Ia, Ib, II)
	GM/RT 2130 (Category Ia, Ib, II)
	EN 45545 (Risk level HL1 - HL3)
	DIN 5510 (Fire protection level 1, 2, 3, 4)
	NF F16-101 (Category A1, A2, B)
	NF F16-101 (Class C/F0)
	NFPA 130
Other resistance	UNI CEI 11170 (Risk level LR1 - LR4)
	Resistance to fuels (according to IRM 903, 168 h at 70 °C)
Ambient temperature (operation)	-50 °C ... 120 °C (cable, fixed installation)
	-25 °C ... 90 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug / socket)

Standards and regulations

M12

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Standard designation	Shock, vibration
Standards/specifications	EN 50155


SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable

1407333

<https://www.phoenixcontact.com/us/products/1407333>


Drawings

Dimensional drawing



Socket M12-SPEEDCON, straight, shielded

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Circuit diagram



Contact assignment of the M12 socket

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407333>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-10,0-28R/FS SCO RAIL - Sensor/actuator cable



1407333

<https://www.phoenixcontact.com/us/products/1407333>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	29c9f8fd-d835-4c1e-8490-00b551b04e1d

EF3.0 Climate Change

CO2e kg	5.221 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com