


1407446

<https://www.phoenixcontact.com/us/products/1407446>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5 (1 Gbps), 8-position, PUR halogen-free, water blue RAL 5021, shielded (Advanced Shielding Technology), Plug straight RJ45 / IP20, on Socket straight M12, coding: A / IP67, cable length: 10 m

Commercial data

Item number	1407446
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF04
Product key	AF1CMI
GTIN	4046356775670
Weight per piece (including packing)	483.2 g
Weight per piece (excluding packing)	472.9 g
Customs tariff number	85444210
Country of origin	PL

Technical data

Notes

General	Further products with variable cable type and variable cable length can be found in the accessories section
---------	---

Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	Ethernet
Number of positions	8
Shielded	yes

Interfaces

Signal type/category	Ethernet CAT5 (IEC 11801), 1 Gbps
----------------------	-----------------------------------

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	1 A
Transmission medium	Copper
Transmission speed	1 Gbps

Connector

Connection 1

Type	Plug straight RJ45 / IP20
Number of positions	8
Degree of protection	IP20

Connection 2

Type	Socket straight M12 / IP67
Number of positions	8
Coding type	A (Standard)
Degree of protection	IP67

Cable/line

Cable length	10 m
--------------	------

Ethernet flexible CAT5, 4-pair [94B]

NBC-M12FS/10,0-94B/R4AC - Network cable



1407446

<https://www.phoenixcontact.com/us/products/1407446>

Dimensional drawing	
UL AWM Style	21238 (80 °C / 600 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet flexible CAT5, 4-pair [94B]
Conductor structure	4x2xAWG26/7, SF/UTP
AWG signal line	26
Conductor cross section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	0.96 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Optical shield covering	70 %
Insulation resistance	≥ 500 MΩ*km
Loop resistance	≤ 290.00 Ω/km
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	26 mm
Smallest bending radius, movable installation	51 mm
Halogen-free	according to IEC 60754-1
Flame resistance	according to IEC 60332-1-2 according to CSA C 22.2 No. 210-FT1
Resistance to oil	in accordance with EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

NBC-M12FS/10,0-94B/R4AC - Network cable



1407446


<https://www.phoenixcontact.com/us/products/1407446>

Ambient conditions

Degree of protection	IP65 (M12 connector)
	IP67 (M12 connector)
	IP20 (RJ45 connector)


Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

Dimensional drawing




RJ45 connector, IP20

1407446

<https://www.phoenixcontact.com/us/products/1407446>

Schematic diagram




Pin assignment M12 socket, 8-pos., A-coded, view female side

1407446

<https://www.phoenixcontact.com/us/products/1407446>

Schematic diagram




Connector pin assignment plug RJ45

1407446

<https://www.phoenixcontact.com/us/products/1407446>

Circuit diagram



Contact assignment of the M12 and RJ45 plug

NBC-M12FS/10,0-94B/R4AC - Network cable



1407446

<https://www.phoenixcontact.com/us/products/1407446>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407446>



UL Listed

Approval ID: FILE E 335024



cUL Listed

Approval ID: FILE E 335024



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387



cUL Listed

Approval ID: FILE E 335024



UL Listed

Approval ID: FILE E 335024



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

NBC-M12FS/10,0-94B/R4AC - Network cable



1407446

<https://www.phoenixcontact.com/us/products/1407446>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	8.277 kg CO2e