

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357

<https://www.phoenixcontact.com/us/products/1409357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 17-position, PVC, black RAL 9005, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 5 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with SPEEDCON fast locking system
- Save space – with high-pos. connectors

Commercial data

Item number	1409357
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1CGA
GTIN	4046356872430
Weight per piece (including packing)	343.9 g
Weight per piece (excluding packing)	343.9 g
Customs tariff number	85444290
Country of origin	DE

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357

<https://www.phoenixcontact.com/us/products/1409357>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	17
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	1.5 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	17
Locking type	SPEEDCON
Coding type	A

Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	17
Locking type	SPEEDCON
Coding type	A

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357

<https://www.phoenixcontact.com/us/products/1409357>

Cable/line

Cable length	5 m
--------------	-----

PVC black [PVC]

Dimensional drawing	
Number of positions	17
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross section	17x 0.14 mm ² (Signal line)
Wire diameter incl. insulation	1 mm ±0.05 mm (Signal line)
External cable diameter	6.80 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	white, brown, green, yellow, gray, pink, blue, red, black, violet, gray-pink, red-blue, white-green, brown-green, white-yellow, yellow-brown, white-gray
Overall twist	17 wires twisted in layers
Max. conductor resistance	≤ 142 Ω/km (at 20 °C)
Insulation resistance	> 10 MΩ*km
Nominal voltage, cable	250 V
Test voltage Core/Core	1500 V AC
Smallest bending radius, fixed installation	34 mm
Smallest bending radius, movable installation	102 mm
Flame resistance	DIN EN 50265-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357

<https://www.phoenixcontact.com/us/products/1409357>

Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-5 °C ... 80 °C (Cable, flexible installation)
Ambient temperature (operation) (Cable, flexible installation)	-25 °C ... 80 °C (cable, fixed installation)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable

1409357

<https://www.phoenixcontact.com/us/products/1409357>


Drawings

Dimensional drawing



M12 SPEEDCON plug, straight

Schematic diagram




Pin assignment M12 male connector, 17-pos., male side view

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357
<https://www.phoenixcontact.com/us/products/1409357>

Circuit diagram



Contact assignment of the M12 plug

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357

<https://www.phoenixcontact.com/us/products/1409357>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-17P-MS/ 5,0-PVC/FS SCO - Sensor/actuator cable



1409357

<https://www.phoenixcontact.com/us/products/1409357>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	abacbf03-20de-4d12-abd7-6c3cf6e9b353

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com