

G-INTRO-M20-S68N-PEPDS-BK - Cable gland



1415189

<https://www.phoenixcontact.com/us/products/1415189>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 6 mm ... 13 mm, shielding: no, connecting thread: M20 x 1.5, color: jet black, with external strain relief

Your advantages

- Glow-wire test: 750°C
- Weatherproof sealing material
- Halogen-free

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1415189 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF68 |
| Product key | AF7DEX |
| GTIN | 4055626038179 |
| Weight per piece (including packing) | 22.1 g |
| Weight per piece (excluding packing) | 17.87 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

G-INTRO-M20-S68N-PEPDS-BK - Cable gland



1415189

<https://www.phoenixcontact.com/us/products/1415189>

Technical data


Product properties

| | |
|--------------------------------|-------------------|
| Product type | Cable screw gland |
| Application | Standard |
| No. of conductors | 1 |
| Manufacturer | WISKA |
| Manufacturer Designation | ESKVZ 20 |
| Shielded | no |
| Execution of the strain relief | B |

Characteristics

| | |
|--------------------------|---|
| Category of shock impact | 2 |
| Design, Strain relief | B |

Dimensions

| | |
|--|--|
| Dimensional drawing |  |
| Length | 49 mm |
| Length of the connecting thread | 10 mm |
| Length without connecting thread | 39 mm |
| Hole diameter | 20.1 mm ... 20.2 mm |
| Wrench size, union nut | 24 mm |
| Wrench size, support | 24 mm |
| Clamping range of the strain relief clip | 6.00 mm ... 13.00 mm |
| Hexagon angular dimension | 27 mm |
| Thread type connection side | M20 x 1.5 |
| Thread pitch | 1.5 mm |

Connection data

| | |
|-------------------|----------------------------|
| Tightening torque | 4 Nm (Union nut: EN 62444) |
| | 4 Nm (Support: EN 62444) |
| | 0.5 Nm (Screw for clip) |

Material specifications

| | |
|--|-------------------------------------|
| Color | black (RAL 9005) |
| Material | PA (Screw connection, halogen-free) |
| Seal material Cable seal | EPDM |
| Glow wire ignition temperature GWIT according to EN 60695-2-13 | 750 |
| Material for screw connection | PA |

G-INTRO-M20-S68N-PEPDS-BK - Cable gland



1415189

<https://www.phoenixcontact.com/us/products/1415189>

Cable/line

| | |
|---------------------------------|-----------------------------------|
| External cable diameter Cable 1 | 6 mm ... 13 mm |
| External cable diameter | 7.5 mm ... 11.3 mm (for UL 514 B) |
| Halogen-free | yes |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|---------------------------------|
| Degree of protection | IP68 (5 bar / 0.5 h) |
| | IP69 (DIN EN 60529 / IEC 60529) |
| Ambient temperature (operation) | -40 °C ... 100 °C (static) |


G-INTRO-M20-S68N-PEPDS-BK - Cable gland

1415189

<https://www.phoenixcontact.com/us/products/1415189>



Drawings



G-INTRO-M20-S68N-PEPDS-BK - Cable gland



1415189

<https://www.phoenixcontact.com/us/products/1415189>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415189>



cUL Recognized

Approval ID: E179850



UL Recognized

Approval ID: E179850



GOST-R

Approval ID: POCC DE.A*98.H12052

G-INTRO-M20-S68N-PEPDS-BK - Cable gland



1415189

<https://www.phoenixcontact.com/us/products/1415189>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27140801 |
| ECLASS-13.0 | 27140801 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000441 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

G-INTRO-M20-S68N-PEPDS-BK - Cable gland



1415189

<https://www.phoenixcontact.com/us/products/1415189>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com