

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable

1419559
<https://www.phoenixcontact.com/us/products/1419559>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on Valve connector A, Wiring: Varistor, cable length: 0.6 m

Commercial data

Item number	1419559
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	AF1DJA
GTIN	4055626175249
Weight per piece (including packing)	50.4 g
Weight per piece (excluding packing)	50 g
Country of origin	PL

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable



1419559

<https://www.phoenixcontact.com/us/products/1419559>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Material specifications

Flammability rating according to UL 94	HB
Seal material	TPU
Material housing valve plug	TPU
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC
Nominal current I_N	4 A

Signaling

Status display	1 LED
Status display present	yes

Connector

Connection 1

Type	Plug straight M12
Coding type	A

Connection 2

Type	Valve connector A
Material	CuSn (Contact)
	Sn (Contact surface)
	PA 6.6 (Contact carrier)
	TPU (Housing)
Protective circuit	Varistor


SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable



1419559

<https://www.phoenixcontact.com/us/products/1419559>

Cable/line

Cable length	0.6 m
PUR halogen-free black [PUR]	
Dimensional drawing	
Cable weight	23 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)
External cable diameter	3.85 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) approx. 0.50 mm (Outer cable sheath)
Overall twist	3 wires, twisted
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	19 mm
Smallest bending radius, movable installation	38 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 38 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥2000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable



1419559

<https://www.phoenixcontact.com/us/products/1419559>

Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67

Standards and regulations

M8

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

Valve connector

Standard designation	Valve connector
Standards/specifications	EN 175301-803

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable

1419559

<https://www.phoenixcontact.com/us/products/1419559>


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing




Valve connector, type A

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable


1419559

<https://www.phoenixcontact.com/us/products/1419559>



Valve connector, type A, side view

Schematic diagram




Pin assignment M8 plug, 3-pos., view male side

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable

1419559

<https://www.phoenixcontact.com/us/products/1419559>



Contact assignment of the M8 plug and the valve connector

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable



1419559

<https://www.phoenixcontact.com/us/products/1419559>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-3P-M 8MS/0,9-PUR/A-1L-V - Sensor/actuator cable



1419559
<https://www.phoenixcontact.com/us/products/1419559>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com