

MCS-78X64-AP-7035 - Adapter plate


1524155

<https://www.phoenixcontact.com/us/products/1524155>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter plate, color: light gray (similar RAL 7035), dimensions: 82.6 x 68.11 x 20.2 mm



Your advantages

- Convenient operation during device installation and maintenance thanks to optional hinges on the housing cover
- Flexible mounting thanks to the optional adapter plate
- Safe operation with the right degree of protection
- Individualized product selection due to the modular system
- Optimized PCB installation: PCB can be installed in a nearly horizontal orientation thanks to the angled housing edge

Commercial data

Item number	1524155
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC04
Product key	ACFFAF
GTIN	4063151990879
Weight per piece (including packing)	36.7 g
Weight per piece (excluding packing)	33.7 g
Customs tariff number	85389099
Country of origin	DE

MCS-78X64-AP-7035 - Adapter plate

1524155

<https://www.phoenixcontact.com/us/products/1524155>



Technical data


Notes

Assembly note	Please observe the assembly instructions available in the download area.
Assembly note	It is removed using a bladed screwdriver.
Recommendation	Further information and detailed dimensions are available in the download area.

Product properties

Product type	Adapter plate
Housing type	Field housing
Housing series	MCS
Product family	MCS-78X64

Dimensions

Dimensional drawing	
Width	82.6 mm
Height	68.11 mm
Depth	20.2 mm
Hole diameter	6 mm
Dimensions	82.6 mm x 68.4 mm x 20.2 mm

Material specifications

Color (Frame)	light gray (RAL 7035)
Material Housing	PA-GF
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Environmental and real-life conditions

Vibration test	
Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

MCS-78X64-AP-7035 - Adapter plate

1524155

<https://www.phoenixcontact.com/us/products/1524155>



Glow-wire test

Specification	IEC 60695-2-11:2021-10
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	10

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Test for substances that would hinder coating with paint or varnish

Specification	VDMA 24364:2018-05
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 85 °C
Relative humidity (storage/transport)	max. 80 %

Mounting

Mounting type	Panel, mast, or DIN rail mounting
Mounting position	any

Packaging specifications

Type of packaging	Box packaging
-------------------	---------------

MCS-78X64-AP-7035 - Adapter plate


1524155

<https://www.phoenixcontact.com/us/products/1524155>



Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center

MCS-78X64-AP-7035 - Adapter plate

1524155

<https://www.phoenixcontact.com/us/products/1524155>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

MCS-78X64-AP-7035 - Adapter plate

1524155

<https://www.phoenixcontact.com/us/products/1524155>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com