

SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting



1553488

<https://www.phoenixcontact.com/us/products/1553488>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type plug, 12-pos., M12, rear/screw mounting with M12 thread, with straight solder connection

Commercial data

Item number	1553488
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB23
Product key	ABQEGI
GTIN	4046356157278
Weight per piece (including packing)	10.655 g
Weight per piece (excluding packing)	10.655 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting



1553488

<https://www.phoenixcontact.com/us/products/1553488>

Technical data

Mounting

Mounting type	Rear mounting
---------------	---------------

Product properties

Product type	Circular connectors (device side)
Sensor type	Universal
Number of positions	12
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
--	----

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	1.5 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Pin

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

Cable/line

Signal type/category	Universal
----------------------	-----------

Environmental and real-life conditions

SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting



1553488

<https://www.phoenixcontact.com/us/products/1553488>

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101


SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting

1553488

<https://www.phoenixcontact.com/us/products/1553488>

Drawings

Schematic diagram



Pin assignment M12 male connector, 12-pos., male side view

SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting





1553488

<https://www.phoenixcontact.com/us/products/1553488>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1553488>

	UL Recognized Approval ID: E221474-20070307			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	keine			
	30 V	1.5 A	-	-

	cUL Recognized Approval ID: E221474-20070307			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	keine			
	30 V	1.5 A	-	-

SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting



1553488

<https://www.phoenixcontact.com/us/products/1553488>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M12MS-12CON-M12 - Device connector rear mounting



1553488

<https://www.phoenixcontact.com/us/products/1553488>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	be0d6b9a-092b-475c-9fa0-c39212c78e83

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com