

RC-09S1N124100 - Device connector rear mounting



1595844

<https://www.phoenixcontact.com/us/products/1595844>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector rear mounting, series: RC, straight, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Socket, Solder cup, Flat gasket, Panel thickness min.: 2.7 mm, Panel thickness max.: 3.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1595844
Packing unit	40 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFR
GTIN	4046356208550
Weight per piece (including packing)	32.582 g
Weight per piece (excluding packing)	30.564 g
Customs tariff number	85366990
Country of origin	DE

RC-09S1N124100 - Device connector rear mounting



1595844

<https://www.phoenixcontact.com/us/products/1595844>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number Contact (Contact group 1)	1
Diameter Contact (Contact group 1)	2 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	8
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section min. Contact (Contact group 2)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Type	Flange housing
Thread type	M23
Design	straight

RC-09S1N124100 - Device connector rear mounting



1595844

<https://www.phoenixcontact.com/us/products/1595844>

Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Rear mounting/square flange (4x M3)
Material (Housing)	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Flat gasket


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------


Drawings

Dimensional drawing



Dimensional drawing


Dimensional drawing



Dimensional drawing


1595844

<https://www.phoenixcontact.com/us/products/1595844>




Installation dimensions

Schematic diagram



Connector pin assignment

Schematic diagram




Connector pin assignment

1595844

<https://www.phoenixcontact.com/us/products/1595844>

Schematic diagram




Connector pin assignment

1595844

<https://www.phoenixcontact.com/us/products/1595844>

Schematic diagram



Dimensional drawing

RC-09S1N124100 - Device connector rear mounting



1595844

<https://www.phoenixcontact.com/us/products/1595844>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1595844

<https://www.phoenixcontact.com/us/products/1595844>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cfd1897a-a211-406d-8a3c-b67bb521744e

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com