

VC-TR4/5M-PEA - Sleeve frame

1607088

<https://www.phoenixcontact.com/us/products/1607088>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve frame, Range of articles: VARIOCON, design: VC4, color: black

Your advantages

- Proven COMBICON technology
- Universal connection
- Can be keyed to prevent incorrect connection

Commercial data

Item number	1607088
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AB01
Product key	ABLABA
GTIN	4017918940911
Weight per piece (including packing)	19.93 g
Weight per piece (excluding packing)	14.231 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Notes

Safety note

Safety note

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- Observe the corresponding technical data. You will find information:
 - o On the product
 - o On the packing label
 - o In the supplied documentation
 - o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product

- Only use tools recommended by Phoenix Contact

- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.

- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Operate the connector only when it is fully plugged in.

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the

VC-TR4/5M-PEA - Sleeve frame

1607088

<https://www.phoenixcontact.com/us/products/1607088>



standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Contact insert
Product family	VARIOCON
Series	VC-M
Type	VC4
Number of module slots	5

Insulation characteristics

Degree of pollution	3
---------------------	---


Electrical properties

Rated voltage (II/2)	1000 V
Rated voltage (III/2)	400 V
Rated surge voltage (III/3)	6 kV

Connection data

Tightening torque	0.8 ... 0.8 Nm
Screw thread	ST2,9

Dimensions

Dimensional drawing	
Width	95.2 mm
Height	27.5 mm
Depth	20.2 mm
Length	32 mm

Material specifications

Color	black
Color of the housing part	black
Material Housing	Polyamide (Sleeve frame)
Material Contact	CuZn
Flammability rating according to UL 94	V2
Insulating material group	I
Contact surface material	nickel-plated
Material for screw connection	Steel, galvanized

VC-TR4/5M-PEA - Sleeve frame

1607088

<https://www.phoenixcontact.com/us/products/1607088>



Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

VC-TR4/5M-PEA - Sleeve frame


1607088

<https://www.phoenixcontact.com/us/products/1607088>




Drawings

Dimensional drawing



Functional drawing



VC-TR4/5M-PEA - Sleeve frame



1607088

<https://www.phoenixcontact.com/us/products/1607088>

Classifications

ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VC-TR4/5M-PEA - Sleeve frame



1607088

<https://www.phoenixcontact.com/us/products/1607088>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com