

1955057  
<https://www.phoenixcontact.com/us/products/1955057>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 2.5 mm<sup>2</sup>, color: black, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: CCA 2,5/..-G, pitch: 5.08 mm, connection method: Plug-in connection, mounting: THR soldering / wave soldering, pin layout: Linear pinning, solder pin [P]: 2.6 mm, number of solder pins per potential: 1, plug-in system: COMBICON MSTB 2,5, Pin connector pattern alignment: Standard, locking: without, mounting method: without, type of packaging: 56 mm wide tape, For user information and design recommendations for through-hole reflow technology, go to: Downloads

Your advantages

- Designed for integration into the SMT soldering process
- Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- Closed contour for optimum stability of the plug-in connection

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1955057       |
| Packing unit                         | 330 pc        |
| Minimum order quantity               | 330 pc        |
| Sales key                            | AA03          |
| Product key                          | AACTBC        |
| GTIN                                 | 4017918925864 |
| Weight per piece (including packing) | 3.539 g       |
| Weight per piece (excluding packing) | 3.388 g       |
| Customs tariff number                | 85366930      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                           |                                            |
|---------------------------|--------------------------------------------|
| Product type              | PCB headers                                |
| Product family            | CCA 2,5/...-G                              |
| Product line              | COMBICON Connectors M                      |
| Type                      | Component suitable for through hole reflow |
| Number of positions       | 4                                          |
| Pitch                     | 5.08 mm                                    |
| Number of connections     | 4                                          |
| Number of rows            | 1                                          |
| Number of potentials      | 4                                          |
| Mounting type             | without                                    |
| Pin layout                | Linear pinning                             |
| Solder pins per potential | 1                                          |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 12 A   |
| Nominal voltage $U_N$       | 320 V  |
| Contact resistance          | 1.3 mΩ |
| Rated voltage (III/3)       | 250 V  |
| Rated surge voltage (III/3) | 4 kV   |
| Rated voltage (III/2)       | 320 V  |
| Rated surge voltage (III/2) | 4 kV   |
| Rated voltage (II/2)        | 400 V  |
| Rated surge voltage (II/2)  | 4 kV   |

### Mounting

|               |                                |
|---------------|--------------------------------|
| Mounting type | THR soldering / wave soldering |
| Pin layout    | Linear pinning                 |

#### Processing notes

|                                  |                       |
|----------------------------------|-----------------------|
| Process                          | Reflow/wave soldering |
| Moisture Sensitive Level         | MSL 1                 |
| Classification temperature $T_c$ | 260 °C                |
| Solder cycles in the reflow      | 3                     |

### Material specifications

#### Material data - contact

|                  |                                                                                  |
|------------------|----------------------------------------------------------------------------------|
| Note             | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material | Cu alloy                                                                         |

# CCA 2,5/ 4-G-5,08 P26THRR56 - PCB header



1955057

<https://www.phoenixcontact.com/us/products/1955057>

|                                             |                        |
|---------------------------------------------|------------------------|
| Surface characteristics                     | Tin-plated             |
| Metal surface contact area (top layer)      | Tin (3 - 5 µm Sn)      |
| Metal surface contact area (middle layer)   | Nickel (1.3 - 3 µm Ni) |
| Metal surface soldering area (top layer)    | Tin (3 - 5 µm Sn)      |
| Metal surface soldering area (middle layer) | Nickel (1.3 - 3 µm Ni) |


## Material data - housing

|                                        |              |
|----------------------------------------|--------------|
| Color (Housing)                        | black (9005) |
| Insulating material                    | LCP          |
| Insulating material group              | IIIa         |
| CTI according to IEC 60112             | 175          |
| Flammability rating according to UL 94 | V0           |

## Notes

|                                 |                                                                                                                                                                                 |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Details for soldering processes | Processing using reflow processes in compliance with IEC 60068-2-58 or DIN EN 61760-1 (latest version)<br>Moisture Sensitive Level (MSL) = 1 according to IPC/JEDEC J-STD-020-C |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 5.08 mm                                                                              |
| Width [w]             | 23.12 mm                                                                             |
| Height [h]            | 11.17 mm                                                                             |
| Length [l]            | 12 mm                                                                                |
| Installed height      | 8.57 mm                                                                              |
| Solder pin length [P] | 2.6 mm                                                                               |
| Pin dimensions        | 1 x 1 mm                                                                             |

## PCB design

|               |        |
|---------------|--------|
| Hole diameter | 1.6 mm |
|---------------|--------|

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

### Resistance of inscriptions

1955057

<https://www.phoenixcontact.com/us/products/1955057>

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

## Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

## Contact holder in insert

|                                                |                        |
|------------------------------------------------|------------------------|
| Specification                                  | IEC 60512-15-1:2008-05 |
| Contact holder in insert<br>Requirements >20 N | Test passed            |

## Insertion and withdrawal forces

|                                     |             |
|-------------------------------------|-------------|
| Result                              | Test passed |
| No. of cycles                       | 25          |
| Insertion strength per pos. approx. | 8 N         |
| Withdraw strength per pos. approx.  | 6 N         |

## Electrical tests

## Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 12                    |

## Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

## Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | IIIa                |
| Comparative tracking index (IEC 60112)                 | CTI 175             |
| Rated insulation voltage (III/3)                       | 250 V               |
| Rated surge voltage (III/3)                            | 4 kV                |
| minimum clearance value - non-homogenous field (III/3) | 3 mm                |
| minimum creepage distance (III/3)                      | 4 mm                |
| Rated insulation voltage (III/2)                       | 320 V               |
| Rated surge voltage (III/2)                            | 4 kV                |
| minimum clearance value - non-homogenous field (III/2) | 3 mm                |
| minimum creepage distance (III/2)                      | 3.2 mm              |
| Rated insulation voltage (II/2)                        | 400 V               |
| Rated surge voltage (II/2)                             | 4 kV                |
| minimum clearance value - non-homogenous field (II/2)  | 3 mm                |
| minimum creepage distance (II/2)                       | 4 mm                |

## Environmental and real-life conditions

## Vibration test

# CCA 2,5/ 4-G-5,08 P26THRR56 - PCB header



1955057

<https://www.phoenixcontact.com/us/products/1955057>

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

## Durability test

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level       | 4.8 kV                |
| Contact resistance $R_1$                     | 1.3 mΩ                |
| Contact resistance $R_2$                     | 1.3 mΩ                |
| Insertion/withdrawal cycles                  | 25                    |
| Insulation resistance, neighboring positions | > 5 MΩ                |


## Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 2.21 kV                                                                   |


## Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |


## Packaging specifications

|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Type of packaging           | 56 mm wide tape                                                                      |
| [W] tape width              | 56 mm                                                                                |
| [W2] coil overall dimension | ≤ 62.4 mm                                                                            |
| [A] coil diameter           | ≤ 330 mm                                                                             |
| Outer packaging type        | Transparent-Bag                                                                      |


## Drawings




Type: MSTBT 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P26 THR




Type: FK 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P26THR




Type: FKCN 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P26THR



Type: FKCS 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P26THR




Type: MSTBP 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P26THR




Type: TFKC 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P...THR







Type: LPC 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P...THR




Type: MVSTBW 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P26THR




Type: ICV 2,5/...-G-5,08 with CCA 2,5/...-G-5,08 P...THR




Type: XPC 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P...THR



Type: TVMSTB 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P...THR



Type: FKCVR 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P...THR



Type: FKCT 2,5/...-ST-5,08 with CCA 2,5/...-G-5,08 P...THR

1955057

<https://www.phoenixcontact.com/us/products/1955057>

## Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1955057>

|  <b>cULus Recognized</b><br>Approval ID: E60425-19931011 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                         |                       |                       |                   |                             |
| Standard                                                                                                                                  | 300 V                 | 16 A                  | -                 | -                           |
| D                                                                                                                                         |                       |                       |                   |                             |
| Standard                                                                                                                                  | 300 V                 | 10 A                  | -                 | -                           |
| Alternative 1                                                                                                                             | 150 V                 | 15 A                  | -                 | -                           |

|  <b>VDE report with production monitoring</b><br>Approval ID: 40041286 |                       |                       |                   |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                                   |                       |                       |                   |                             |
|                                                                                                                                                         | 400 V                 | 12 A                  | -                 | -                           |

|  <b>VDE approval of drawings</b><br>Approval ID: 40050079 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                              | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                        |                       |                       |                   |                             |
|                                                                                                                                              | 320 V                 | 16 A                  | -                 | -                           |

1955057

<https://www.phoenixcontact.com/us/products/1955057>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |