

# AI-GB 1,5-10 BK-15000 - Ferrule

2100079

<https://www.phoenixcontact.com/pc/products/2100079>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, Length contact range: 10 mm, sleeve length: 16 mm, color: black



## Your advantages

- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2100079       |
| Packing unit                         | 15,000 pc     |
| Minimum order quantity               | 45,000 pc     |
| Product key                          | BH341S        |
| GTIN                                 | 4067923214378 |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# AI-GB 1,5-10 BK-15000 - Ferrule



2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## Technical data

### Product properties


|                    |                                                                                               |
|--------------------|-----------------------------------------------------------------------------------------------|
| Product type       | Cable end sleeve                                                                              |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M                                               |
| Product property   | Suitable for AWG/multi-standard cables due to the increased diameter of the insulating collar |
|                    | UL certified                                                                                  |
|                    | Made from soft tin-plated electrolytic copper                                                 |
|                    | Correspond to the requirements of UL 486F                                                     |
|                    | Plastic collar made of polypropylene                                                          |
|                    | Halogen-free                                                                                  |
|                    | Long/short-term temperature: +105°C/+120°C                                                    |

### Connection data

#### Conductor connection

|                                       |                     |
|---------------------------------------|---------------------|
| Conductor cross-section flexible max. | 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG max.      | 16                  |
| Stripping length                      | 13 mm               |

### Dimensions

|                                           |                                                                                      |
|-------------------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing                       |  |
| Sleeve length                             | 16 mm                                                                                |
| Length contact range                      | 10 mm                                                                                |
| Maximum stripping length                  | 13 mm                                                                                |
| Ferrule diameter                          | 1.7 mm                                                                               |
| Sleeve wall thickness                     | 0.15 mm                                                                              |
| Insulating collar thickness               | 0.3 mm                                                                               |
| Inner dimensions of the insulating collar | 3.8 mm                                                                               |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | black (RAL 9005)               |
| Material                               | CU-DHP                         |
| Flammability rating according to UL 94 | HB                             |
| Coating                                | galvanically tin-plated        |
| Surface characteristics                | Tin-plated                     |
| Components                             | free from silicone and halogen |

### Mechanical properties

# AI-GB 1,5-10 BK-15000 - Ferrule



2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## Technical data

|               |       |
|---------------|-------|
| Sleeve length | 16 mm |
|---------------|-------|

## Standards and regulations

|                              |             |
|------------------------------|-------------|
| Design according to standard | DIN 46228-4 |
|                              | UL 486F-E   |

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI-GB 1,5-10 BK-15000 - Ferrule



2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/2100079>



**cULus Listed**

Approval ID: E488001

# AI-GB 1,5-10 BK-15000 - Ferrule



2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000005 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

# AI-GB 1,5-10 BK-15000 - Ferrule



2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

# AI-GB 1,5-10 BK-15000 - Ferrule



2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## Accessories

### CRIMPFOX CENTRUS 6S - Crimping pliers

1213144

<https://www.phoenixcontact.com/pc/products/1213144>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm<sup>2</sup> ... 6 mm<sup>2</sup>, also for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, lateral insertion, equipped with fall protection

---

### CRIMPFOX CENTRUS 6H - Crimping pliers

1213146

<https://www.phoenixcontact.com/pc/products/1213146>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm<sup>2</sup> ... 6 mm<sup>2</sup>, also for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, lateral insertion, equipped with fall protection

# AI-GB 1,5-10 BK-15000 - Ferrule

2100079

<https://www.phoenixcontact.com/pc/products/2100079>



## CRIMPFOX CENTRUS 10S - Crimping pliers

1213154

<https://www.phoenixcontact.com/pc/products/1213154>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>, also for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, lateral insertion, equipped with fall protection

---

## CRIMPFOX CENTRUS 10H - Crimping pliers

1213156

<https://www.phoenixcontact.com/pc/products/1213156>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>, also for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, lateral insertion, equipped with fall protection

# AI-GB 1,5-10 BK-15000 - Ferrule

2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## CRIMPFOX 2,5-M - Crimping pliers

1212719

<https://www.phoenixcontact.com/pc/products/1212719>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, lateral entry, trapezoidal crimp

---

## CRIMPFOX 6-M - Crimping pliers

1212720

<https://www.phoenixcontact.com/pc/products/1212720>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm<sup>2</sup> ... 6.0 mm<sup>2</sup>, lateral entry, trapezoidal crimp

# AI-GB 1,5-10 BK-15000 - Ferrule

2100079

<https://www.phoenixcontact.com/pc/products/2100079>

## CRIMPFOX 6 - Crimping pliers

1212034

<https://www.phoenixcontact.com/pc/products/1212034>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm<sup>2</sup> ... 6.0 mm<sup>2</sup>, lateral entry, trapezoidal crimp

---

## CRIMPFOX DUO 10 - Crimping pliers

1031721

<https://www.phoenixcontact.com/pc/products/1031721>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 mm<sup>2</sup>, max. cross section: 10 mm<sup>2</sup>, for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

# AI-GB 1,5-10 BK-15000 - Ferrule

2100079

<https://www.phoenixcontact.com/pc/products/2100079>



## CRIMPFOX 10T-F - Crimping pliers

1134913

<https://www.phoenixcontact.com/pc/products/1134913>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 0.14 mm<sup>2</sup>, max. cross section: 10 mm<sup>2</sup>, For TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, frontal insertion, compression: Trapezoidal crimp, weight 302 g, black

---

## CRIMPFOX DUO 16S - Crimping pliers

1202877

<https://www.phoenixcontact.com/pc/products/1202877>



Crimping pliers, contact type: insulated and uninsulated ferrules, standards/regulations: DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F, cross-section, minimum: 0.14 mm<sup>2</sup>, cross-section, maximum: 16 mm<sup>2</sup>, for TWIN ferrules up to 2 mm<sup>2</sup> x 6 mm<sup>2</sup>, automatic cross-section adjustment, rotating dies, lateral and front entry, crimping: square

---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)