

FB-PS-MB-Y/EX - Power supply unit



2316148

<https://www.phoenixcontact.com/us/products/2316148>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Four-channel redundant fieldbus power supply base. Host connections are for two Yokogawa AKB336 20-pin cables.



Product description

Yokogawa four-channel, redundant fieldbus power supply base with host connectors for two AKB336 Yokogawa 20-pin cables.

Your advantages

- Built-in relay diagnostics
- Redundancy

Commercial data

Item number	2316148
Packing unit	25 pc
Minimum order quantity	1 pc
Sales key	DN11
Product key	DNC1Z1
GTIN	4055626128368
Weight per piece (including packing)	1,136.8 g
Weight per piece (excluding packing)	1,136.8 g
Customs tariff number	85366990
Country of origin	US

FB-PS-MB-Y/EX - Power supply unit



2316148

<https://www.phoenixcontact.com/us/products/2316148>

Technical data

Notes

Utilization restriction

CCCex note

Use in potentially explosive areas is not permitted in China.

Product properties

Product type

Device coupler

Output data

Signal

Output name

Alarm

Connection data

Supply

Conductor cross-section, flexible

0.20 mm² ... 2.50 mm²

Conductor cross-section, rigid

0.20 mm² ... 2.50 mm²

Conductor cross-section AWG

30 ... 12

Ex data

Safety data

Inductance Li

17.8 mH (trunk and host)

Max. output voltage U_o

30 V DC (trunk and host)

Interfaces

Data: Yokogawa DCS cabling system

Number of connections

2

Connection method

AKB336 cable

Tightening torque

0.4 Nm ... 0.5 Nm (AKB336 cable)

Dimensions

Width

180 mm

Height

77 mm

Depth

180 mm

Mechanical tests

Corrosive resistance in accordance with ANSI-ISA 71.04-1985 - Severity level G3

:

Environmental and real-life conditions

Ambient conditions

Degree of protection

IP20

FB-PS-MB-Y/EX - Power supply unit



2316148

<https://www.phoenixcontact.com/us/products/2316148>

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (non-condensing)
Permissible humidity (operation)	95 % (non-condensing)

Approvals

ATEX

Identification	II 3 G Ex ec nC IIC T4 Gc
Certificate	Sira 11ATEX4216X

IECEX

Identification	Ex ec nC IIC T4 Gc
Certificate	IECEX SIR 11.0097X

UKCA Ex (UKEX)

Identification	II 3G Ex ec nC IIC T4 Gc
Certificate	PxCAI22UKEx2316132X

Ex data

CSA, USA/Canada	Class I, Div. 2, Groups A, B, C, D; Ex nA nC IIC T4 Class I, Zone 2, AEx nA nC IIC T4
-----------------	--

Standards and regulations

Standards

Standards/regulations	NE21
	EN 61326

Standards/regulations

Standards/regulations	Ring wave noise immunity in acc. with IEC 61000-4-12
-----------------------	--

Standards/regulations

Standards/regulations	Dry heat in acc. with IEC 61131-2
-----------------------	-----------------------------------

Standards/regulations

Standards/regulations	Damp heat in acc. with IEC 61131-2
-----------------------	------------------------------------

Standards/regulations

Standards/regulations	Shock and vibration in acc. with EN 61131-2 and EN 50178
Standards/regulations	IEC 61158-2

FB-PS-MB-Y/EX - Power supply unit



2316148

<https://www.phoenixcontact.com/us/products/2316148>

Classifications

ECLASS

ECLASS-13.0	27242692
-------------	----------

ETIM

ETIM 9.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FB-PS-MB-Y/EX - Power supply unit



2316148

<https://www.phoenixcontact.com/us/products/2316148>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com