

FL CAT5 FLEX - Installation cable

2744830

<https://www.phoenixcontact.com/us/products/2744830>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Installation cable, Ethernet CAT5 (100 Mbps), shielded, PUR halogen-free, water blue RAL 5021, 4-wire (2x2xAWG26/7, SF/UTP), color single wire: white/orange-orange, white/green-green, cable length: Free entry (1.0 ... 1000.0 m)

Commercial data

Item number	2744830
Packing unit	1 m
Minimum order quantity	1 m
Note	Made to order (non-returnable)
Sales key	BF04
Product key	AF1LEA
GTIN	4017918600501
Weight per piece (including packing)	40.24 g
Weight per piece (excluding packing)	40.24 g
Customs tariff number	85444993
Country of origin	DE

FL CAT5 FLEX - Installation cable

2744830

<https://www.phoenixcontact.com/us/products/2744830>



Technical data

Product properties

Product type	Data cable by the meter
Sensor type	Ethernet
Number of positions	4

Electrical properties

Nominal voltage U_N	48 V AC
Transmission medium	Copper
Transmission speed	100 Mbps


Interfaces

Signal type/category	Ethernet CAT5 (IEC 11801), 100 Mbps
----------------------	-------------------------------------

Cable/line

Cable length	Free entry (1.0 ... 1000.0 m)
--------------	-------------------------------

Ethernet [93E]

Dimensional drawing	
Cable weight	43 kg/km
Number of positions	4
Shielded	yes
Cable type	Ethernet [93E]
Conductor structure	2x2xAWG26/7, SF/UTP
Signal runtime	4.3 ns/m
Signal speed	0.77 c
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	2x 2x 0.14 mm ²
Wire diameter incl. insulation	1 mm -0.2 mm
External cable diameter	5.75 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Foam-Skin PE
Single wire, color	white/orange-orange, white/green-green

FL CAT5 FLEX - Installation cable



2744830

<https://www.phoenixcontact.com/us/products/2744830>

Twisted pairs	2 cores to the pair
Overall twist	Two pairs with two fillers to the core
Optical shield covering	85 %
Max. conductor resistance	$\leq 284 \Omega/\text{km}$
Insulation resistance	$\geq 5 \text{ G}\Omega \cdot \text{km}$
Coupling resistance	$\leq 5.00 \text{ m}\Omega/\text{m}$ (at 20 MHz)
Wave impedance	$100 \Omega \pm 15 \%$ (at 1 ... 100 MHz)
Cable capacity	nom. 48 nF/km (At 800 Hz)
Nominal voltage, cable	50 V _{rms}
	125 V (Peak value, not for high-power applications)
Test voltage Core/Core	1000 V _{rms}
Test voltage Core/Shield	500.00 V _{rms}
Smallest bending radius, fixed installation	30 mm (cable, fixed installation)
Smallest bending radius, movable installation	78 mm (Cable, flexible installation)
Tensile strength	$\leq 50 \text{ N}$ (temporary)
	$\leq 10 \text{ N}$ (Permanent)
Near end crosstalk attenuation (NEXT)	66 dB/m (with 1 MHz)
	57 dB/m (at 4 MHz)
	52 dB/m (at 10 MHz)
	50 dB/m (at 16 MHz)
	47 dB/m (at 20 MHz)
	45 dB/m (at 31.25 MHz)
	40 dB/m (at 62.5 MHz)
	36 dB/m (at 100 MHz)
Crosstalk attenuation (ACR)	6.57 dB/m (with 1 MHz)
	5.64 dB/m (at 4 MHz)
	5.12 dB/m (at 10 MHz)
	4.89 dB/m (at 16 MHz)
	4.57 dB/m (at 20 MHz)
	4.34 dB/m (at 31.25 MHz)
	3.77 dB/m (at 62.5 MHz)
	3.31 dB/m (at 100 MHz)
Shield attenuation	0.028 dB/m (with 1 MHz)
	0.06 dB/m (at 4 MHz)
	0.085 dB/m (at 10 MHz)
	0.115 dB/m (at 16 MHz)
	0.128 dB/m (at 20 MHz)
	0.162 dB/m (at 31.25 MHz)
	0.23 dB/m (at 62.5 MHz)
	0.29 dB/m (at 100 MHz)
Flame resistance	according to VDE 0482 Part 265-2-1
	according to IEC 332-1
Ambient temperature (operation)	-30 °C ... 80 °C (cable, fixed installation)
Ambient temperature (installation)	-5 °C ... 60 °C

FL CAT5 FLEX - Installation cable

2744830

<https://www.phoenixcontact.com/us/products/2744830>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2744830>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00395

FL CAT5 FLEX - Installation cable



2744830

<https://www.phoenixcontact.com/us/products/2744830>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FL CAT5 FLEX - Installation cable



2744830

<https://www.phoenixcontact.com/us/products/2744830>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com