

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation contactor (Hum-free); input voltage: 24 V AC/DC; contact switching type: 3 N/O contacts, 1 N/C contact; rated current: 32 A

Commercial data

Item number	1791349
Packing unit	5 pc
Minimum order quantity	5 pc
Product key	DK6441
GTIN	4067923412217
Weight per piece (including packing)	264.6 g
Weight per piece (excluding packing)	264.6 g
Country of origin	SI

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

Technical data

Product properties

Product type	Installation contactor
Mechanical service life	10 ⁷ cycles

Electrical properties

Electrical service life (AC-1, AC-7a, AC-21)	150000 switching cycles
Electrical service life (AC-3, AC-3e, AC-7b, AC-23)	150000 switching cycles
Electrical service life (AC-5a)	100000 switching cycles
Electrical service life (AC-5b)	100000 switching cycles
Electrical service life (DC-1)	100000 switching cycles

Insulation characteristics: Control circuit/load circuit

Rated insulation voltage	440 V
Rated surge voltage	4 kV

Input data

Voltage	24 V AC/DC
Voltage range (AC)	20.4 V AC ... 26.4 V AC
Voltage range (DC)	20.4 V DC ... 26.4 V DC
Mains frequency	50/60 Hz
Response time range	15 ms ... 45 ms
Release time range	20 ms ... 70 ms
Drive and function	monostable
Power consumption	2.6 W

Output data

Contact switching type	3 N/O contacts
	1 N/C contact
Type of switch contact	Single contact
Minimum distance	3.6 mm (open contacts)
Fuse	≤ 32 A (Backup fuse for short-circuit protection KS according to UL and CSA)
Rated operating voltage (AC/DC)	400 V (IEC)
Rated operating voltage	480 V (UL/CSA)
Current (thermal)	32 A
Rated operating current (AC-1, AC-7a, AC-21)	32 A
Rated operating current (AC-3, AC-3e, AC-7b, AC-23)	8.5 A
Rated operating current (AC-5a)	13 A (230 V)
Rated operating current (AC-5b)	11 A (230 V)
Rated operating current (DC-1 (L/R < 1 ms), 1 pole)	32 A (24 V DC)
	25 A (48 V DC)
	15 A (60 V DC)

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

	6 A (110 V DC)
	0.6 A (220 V DC)
Rated operating current (DC-1 (L/R < 1 ms), 2 poles in series)	32 A (24 V DC)
	32 A (48 V DC)
	20 A (60 V DC)
	10 A (110 V DC)
	6 A (220 V DC)
Rated operating current (DC-1 (L/R < 1 ms), 3 poles in series)	32 A (24 V DC)
	32 A (48 V DC)
	32 A (60 V DC)
	20 A (110 V DC)
	15 A (220 V DC)
Rated operating current (DC-1 (L/R < 1 ms), 4 poles in series)	32 A (24 V DC)
	32 A (48 V DC)
	32 A (60 V DC)
	20 A (110 V DC)
	15 A (220 V DC)
Rated operating power (AC-1, AC-7a, AC-21)	7 kW (1~, 230 V)
	12 kW (3~, 230 V)
	21 kW (3~, 400 V)
Rated operating power (AC-3, AC-3e, AC-7b, AC-23)	1.3 kW (1~, 230 V)
	2.2 kW (3~, 230 V)
	4 kW (3~, 400 V)
Mains frequency	50/60 Hz

Connection data

Coil

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	1.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	1.5 mm ² ... 2.5 mm ²
Conductor cross-section AWG	16 ... 14
Tightening torque	0.5 Nm ... 0.6 Nm

Contact

Connection method	Screw connection
Stripping length	9 mm
Screw thread	M3,5
Conductor cross-section rigid	1 mm ² ... 10 mm ²
Conductor cross-section flexible	1 mm ² ... 6 mm ²
Conductor cross-section AWG (rigid)	18 ... 8
Conductor cross-section AWG (flexible)	18 ... 10
Tightening torque	1.1 Nm ... 1.2 Nm

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

Dimensions

Item dimensions

Width	35 mm
Height	85 mm
Depth	64.9 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 IP40 (for installation in a junction box - distribution board)
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C
Altitude	≤ 2000 m
Shock (operation)	switched contacts: 15g (Z-axis) and 2g (X-axis)
Shock (storage/transport)	unswitched contacts: 10g (Z-axis and X-axis)
Vibration (operation)	switched contacts: 3g (Z-axis) and 1g (X-axis)
Vibration (storage/transport)	unswitched contacts: 2g (Z-axis and X-axis)
Noise level	20 dB

Mounting

Mounting type	DIN rail mounting
Assembly note	Number of contactors or switches next to each other < 40°C: no restriction
Mounting position	vertical (DIN rail horizontal, see mounting drawing)

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1791349>



cULus Listed

Approval ID: E228652

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

Classifications

ECLASS

ECLASS-13.0	27142308
ECLASS-15.0	27142308

CBL-SC-24UC/31/32A - Installation contactor



1791349

<https://www.phoenixcontact.com/in/products/1791349>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	1.97 kg CO2e
---------	--------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in