

PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays



2963763

<https://www.phoenixcontact.com/us/products/2963763>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay for emergency stop and safety door monitoring up to SIL 3 or Cat. 4, PL e in accordance with EN ISO 13849, 2-channel operation, 3 enabling current paths, nominal input voltage: 24 V DC, plug-in screw terminal block

Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- 2 channel control
- 3 enabling current paths, 1 signaling current path
- Manually monitored and automatic activation in a single device

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2963763 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN01 |
| Product key | DNA113 |
| GTIN | 4017918878085 |
| Weight per piece (including packing) | 182 g |
| Weight per piece (excluding packing) | 161.12 g |
| Customs tariff number | 85371098 |
| Country of origin | DE |

PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays

2963763

<https://www.phoenixcontact.com/us/products/2963763>



Technical data

Product properties

| | |
|-------------------------|--|
| Product type | Safety relays |
| Product family | PSRclassic |
| Application | Emergency stop Safety door |
| Control | 2-channel |
| Mechanical service life | approx. 10^7 cycles |
| Relay type | Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 2 |

Times

| | |
|-------------------------------|--|
| Typical response time | typ. 150 ms (For U_s autostart) |
| Typ. starting time with U_s | typ. 250 ms (with U_s / when controlled via A1) |
| Typical release time | typ. 20 ms (At U_s on demand via sensor circuit) |
| | typ. 45 ms (At U_s /on demand via A1) |
| Restart time | < 1 s (Boot time) |
| Recovery time | < 1 s (following demand of the safety function) |

Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 16.44 W ($U_s = 26.4$ V, $I_s^2 = 72$ A 2 , $P_{Total\ max} = 2.04$ W + 14.4 W) |
| Nominal operating mode | 100% operating factor |
| Rated insulation voltage | 250 V |
| Rated surge voltage/insulation | See data sheet, section "Insulation coordination". |

Supply

| | |
|--|---|
| Rated control circuit supply voltage U_s | 24 V DC -15 % / +10 % |
| Rated control supply current I_s | typ. 70 mA (at U_s) |
| Power consumption at U_s | typ. 1.68 W |
| Inrush current | < 3.5 A (typ. with U_s , $\Delta t = 3$ ms) |
| Filter time | 5 ms (in the event of voltage dips at U_s) |
| Protective circuit | Serial protection against polarity reversal; Suppressor diode |

Input data

Digital: Logic (S12, S22)

| | |
|--------------------------------|-------------------------|
| Description of the input | safety-related |
| Number of inputs | 2 |
| Input voltage range "0" signal | 0 V DC ... 5 V DC (S12) |
| Input voltage range "1" signal | 20.4 V ... 26.4 V (S12) |
| Input current range "0" signal | 0 mA ... 2 mA |

PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays

2963763

<https://www.phoenixcontact.com/us/products/2963763>



| | |
|---|---|
| Inrush current | < 100 mA (typ. with U_S at S12) > -100 mA (typ. with U_S at S22) |
| Filter time | No test pulses permitted |
| Concurrency | ∞ |
| Max. permissible overall conductor resistance | 50 Ω |
| Protective circuit | Suppressor diode |
| Current consumption | 38 mA (typ. with U_S at S12) -38 mA (typ. with U_S at S22) |

Digital: Start circuit (S34)

| | |
|---|---------------------------|
| Description of the input | non-safety-related |
| Number of inputs | 1 |
| Input voltage range "1" signal | 20.4 V ... 26.4 V |
| Inrush current | < 6 mA (typ. with U_S) |
| Filter time | No test pulses permitted |
| Max. permissible overall conductor resistance | 50 Ω |
| Protective circuit | Suppressor diode |
| Current consumption | 1 mA (typ. with U_S) |

Output data

Relay: Enabling current paths (13/14, 23/24, 33/34)

| | |
|-----------------------------|--|
| Output description | 2 N/O contacts in series, safety-related, floating |
| Number of outputs | 3 |
| Contact switching type | 3 enabling current paths |
| Contact material | AgSnO ₂ |
| Switching voltage | min. 10 V AC/DC max. 250 V AC/DC |
| Switching power | min. 100 mW |
| Inrush current | min. 10 mA max. 6 A |
| Switching capacity | 5 A (AC15) 6 A (DC13) |
| Limiting continuous current | 6 A |
| Sq. Total current | 72 A ² (observe derating) |
| Switching frequency | max. 0.5 Hz |
| Mechanical service life | 10 ⁷ cycles |
| Output fuse | 10 A gL/gG (High demand) 4 A gL/gG (Low demand) |

Relay: Signaling current path (41/42)

| | |
|------------------------|---|
| Output description | 2 N/C contacts parallel, non-safety-related, floating |
| Number of outputs | 1 |
| Contact switching type | 1 signaling current path |
| Contact material | AgSnO ₂ |

PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays

2963763

<https://www.phoenixcontact.com/us/products/2963763>



| | |
|---------------------------------------|---------------------------------------|
| Switching voltage | min. 10 V AC/DC |
| | max. 250 V AC/DC |
| Switching power | min. 100 mW |
| Inrush current | min. 10 mA |
| | max. 6 A |
| Switching capacity | 1.5 A (AC15) |
| | 2 A (DC13) |
| Limiting continuous current | 6 A (Signaling current path) |
| Sq. Total current | 36 A ² |
| Switching frequency | max. 0.5 Hz |
| Mechanical service life | 10 ⁷ cycles |
| Interrupting rating (ohmic load) max. | Observe derating and load limit curve |
| Output fuse | 6 A gL/gG |

Connection data

Connection technology

| | |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

Conductor connection

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Signaling

| | |
|---------------------------|-----------------|
| Status display | 3 x LED (green) |
| Operating voltage display | 1 x LED (green) |

Dimensions

| | |
|--------|----------|
| Width | 22.5 mm |
| Height | 99 mm |
| Depth | 114.5 mm |

Material specifications

| | |
|------------------|-------------------|
| Color (Housing) | yellow (RAL 1018) |
| Housing material | PA |

Characteristics

Safety data

| | |
|---------------|---|
| Stop category | 0 |
|---------------|---|

Safety data: EN ISO 13849

PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays

2963763

<https://www.phoenixcontact.com/us/products/2963763>



| | |
|------------------------|--|
| Category | 4 |
| Performance level (PL) | e (5 A DC13; 5 A AC15; 8760 switching cycles/year) |

Safety data: IEC 61508 - High demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: IEC 61508 - Low demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: EN IEC 62061

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Min. degree of protection of inst. location | IP54 |
| Ambient temperature (operation) | -20 °C ... 55 °C (observe derating) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Maximum altitude | ≤ 2000 m (Above sea level) |
| Max. permissible humidity (storage/transport) | 75 % (on average, 85% infrequently, non-condensing) |
| Max. permissible relative humidity (operation) | 75 % (on average, 85% infrequently, non-condensing) |
| Shock | 15g |
| Vibration (operation) | 10 Hz ... 150 Hz, 2g |

Approvals

CE


| | |
|----------------|--------------|
| Identification | CE-compliant |
|----------------|--------------|

Mounting


| | |
|-------------------|------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | See derating curve |
| Mounting position | vertical or horizontal |

Drawings

Circuit diagram



Circuit diagram



Single-channel safety door monitoring


PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays



2963763

<https://www.phoenixcontact.com/us/products/2963763>

Circuit diagram



PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays

2963763

<https://www.phoenixcontact.com/us/products/2963763>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2963763>



cULus Listed
Approval ID: E140324



Functional Safety
Approval ID: 01/205/0652.05/22

Classifications

ECLASS

| | |
|-------------------|----------|
| ECLASS-13.0 | 27371819 |
| ECLASS-15.0 | 27371819 |
| ECLASS-15.0 ASSET | 27250101 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001449 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122205 |
|-------------|----------|

PSR-SCP- 24UC/ESA4/3X1/1X2/B - Safety relays

2963763

<https://www.phoenixcontact.com/us/products/2963763>



Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|-------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 77d74c49-23b7-4bdb-92d0-34cf3aa6b30 |

EF3.0 Climate Change

| | |
|---------|---------------|
| CO2e kg | 6.792 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com