


RBO 16-3L/N/FE - Bolt connection terminal block



3076316

<https://www.phoenixcontact.com/us/products/3076316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bolt connection terminal block, nom. voltage: 1000 V, nominal current: 520 A, number of connections: 10, number of positions: 5, connection method: Bolt connection, Rated cross section: 300 mm², 1 level, mounting type: NS 35/7,5, NS 35/15, direct screw connection, color: gray/blue/black-yellow

Commercial data

Item number	3076316
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BE4412
GTIN	4046356653558
Weight per piece (including packing)	2,832.9 g
Weight per piece (excluding packing)	2,832.9 g
Country of origin	CN

RBO 16-3L/N/FE - Bolt connection terminal block



3076316

<https://www.phoenixcontact.com/us/products/3076316>

Technical data

Product properties

Product type	Bolt connection terminal block
Number of positions	5
Pitch	54.8 mm
Number of connections	10
Number of rows	1
Potentials	5

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
---------------------	------

Connection data

Number of connections per level	10
Nominal cross section	300 mm ²

1 level

Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal current	520 A
Maximum load current	520 A (At a conductor cross-section of 300 mm ²)
Nominal voltage	1000 V
Nominal cross section	300 mm ²

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	25 mm ² ... 300 mm ²
Cross section range AWG	4 ... 600 kcmil (converted acc. to IEC)
Hole diameter	17 mm
Width	38 mm
Bolt diameter	16 mm
Screw thread	M16
Tightening torque	25 ... 35 Nm
Connection in acc. with standard	DIN 46235:1983-07
Cross section	25 mm ² ... 300 mm ²
Cross section range AWG	4 ... 600 kcmil (converted acc. to IEC)
Hole diameter	17 mm
Width	48 mm

RBO 16-3L/N/FE - Bolt connection terminal block



3076316

<https://www.phoenixcontact.com/us/products/3076316>

Bolt diameter	16 mm
Screw thread	M16
Tightening torque	25 ... 35 Nm

Dimensions

Dimensional drawing	
Width	274 mm
Pitch	54.8 mm

Material specifications

Color	gray/blue/black-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data	
Open side panel	No

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	direct screw connection

RBO 16-3L/N/FE - Bolt connection terminal block




3076316

<https://www.phoenixcontact.com/us/products/3076316>

Drawings

Dimensional drawing



RBO 16-3L/N/FE - Bolt connection terminal block



3076316
<https://www.phoenixcontact.com/us/products/3076316>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com