

AI 0,5-10 WH-GB - Ferrule

3203150

<https://www.phoenixcontact.com/us/products/3203150>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, color: white



Your advantages

- Due to the increased diameter of the insulating collar, this type of ferrule is specifically used with AWG cables
- These ferrules enable practical crimping of conductors with increased insulation

Commercial data

Item number	3203150
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH341S
GTIN	4046356135030
Weight per piece (including packing)	0.093 g
Weight per piece (excluding packing)	0.088 g
Customs tariff number	85369010
Country of origin	DE

AI 0,5-10 WH-GB - Ferrule

3203150

<https://www.phoenixcontact.com/us/products/3203150>



Technical data

Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M

Connection data

Conductor connection	
Conductor cross-section flexible max.	0.5 mm ²
Conductor cross-section AWG max.	20
Stripping length	13 mm

Dimensions

Dimensional drawing	
Sleeve length	10 mm
Maximum stripping length	13 mm
Ferrule diameter	1.1 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	3 mm

Material specifications

Color	white (RAL 9010)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data	
Sleeve length	10 mm

Environmental and real-life conditions

Ambient conditions	
Optimum ambient temperature (storage/transport)	23.00 °C 50.00 % Storage in a dry and dark place in the original packaging is recommended
Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)

AI 0,5-10 WH-GB - Ferrule

3203150

<https://www.phoenixcontact.com/us/products/3203150>



Short-term temperature

120 °C

Standards and regulations

Design according to standard

UL 486F-E

AI 0,5-10 WH-GB - Ferrule


3203150

<https://www.phoenixcontact.com/us/products/3203150>



Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI 0,5-10 WH-GB - Ferrule

3203150

<https://www.phoenixcontact.com/us/products/3203150>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3203150>



cULus Listed
Approval ID: E488001

AI 0,5-10 WH-GB - Ferrule

3203150

<https://www.phoenixcontact.com/us/products/3203150>



Classifications

ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

ETIM

ETIM 9.0	EC000005
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI 0,5-10 WH-GB - Ferrule

3203150

<https://www.phoenixcontact.com/us/products/3203150>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com