


# BCH-508V-12 BK - PCB header

5452422

<https://www.phoenixcontact.com/us/products/5452422>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 2.5 mm<sup>2</sup>, color: black, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 12, number of rows: 1, number of positions: 12, number of connections: 12, product range: BCH-V, pitch: 5.08 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.9 mm, number of solder pins per potential: 1, plug-in system: BASICLINE 2,5, Pin connector pattern alignment: Standard, locking: without, mounting method: without, type of packaging: packed in cardboard

## Your advantages

- Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- Well-known mounting principle allows worldwide use
- Vertical connection enables multi-row arrangement on the PCB
- Easy PCB replacement thanks to plug-in modules

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 5452422                        |
| Packing unit                         | 100 pc                         |
| Minimum order quantity               | 100 pc                         |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA03                           |
| Product key                          | AACSQD                         |
| GTIN                                 | 4046356851596                  |
| Weight per piece (including packing) | 4.311 g                        |
| Weight per piece (excluding packing) | 4.311 g                        |
| Customs tariff number                | 85366930                       |
| Country of origin                    | CN                             |

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

## Technical data

### Product properties

|                           |                       |
|---------------------------|-----------------------|
| Product type              | PCB headers           |
| Product family            | BCH-V                 |
| Product line              | COMBICON Connectors M |
| Type                      | Standard              |
| Number of positions       | 12                    |
| Pitch                     | 5.08 mm               |
| Number of connections     | 12                    |
| Number of rows            | 1                     |
| Number of potentials      | 12                    |
| Mounting type             | without               |
| Pin layout                | Linear pinning        |
| Solder pins per potential | 1                     |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 12 A   |
| Nominal voltage $U_N$       | 320 V  |
| Contact resistance          | 2.9 mΩ |
| Rated voltage (III/3)       | 250 V  |
| Rated surge voltage (III/3) | 4 kV   |
| Rated voltage (III/2)       | 320 V  |
| Rated surge voltage (III/2) | 4 kV   |
| Rated voltage (II/2)        | 400 V  |
| Rated surge voltage (II/2)  | 4 kV   |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Wave soldering |
| Pin layout    | Linear pinning |

### Material specifications

#### Material data - contact

|                                             |                                                                                  |
|---------------------------------------------|----------------------------------------------------------------------------------|
| Note                                        | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy                                                                         |
| Surface characteristics                     | Tin-plated                                                                       |
| Metal surface contact area (top layer)      | Tin (4 - 8 μm Sn)                                                                |
| Metal surface contact area (middle layer)   | Nickel (1.5 - 4 μm Ni)                                                           |
| Metal surface soldering area (top layer)    | Tin (4 - 8 μm Sn)                                                                |
| Metal surface soldering area (middle layer) | Nickel (1.5 - 4 μm Ni)                                                           |

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

## Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | black (9005) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Notes

|                    |                                                                                                                                                                                          |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 5.08 mm                                                                              |
| Width [w]             | 60.96 mm                                                                             |
| Height [h]            | 15.9 mm                                                                              |
| Length [l]            | 8.6 mm                                                                               |
| Installed height      | 12 mm                                                                                |
| Solder pin length [P] | 3.9 mm                                                                               |
| Pin dimensions        | 1 x 1 mm                                                                             |

## PCB design

|               |        |
|---------------|--------|
| Hole diameter | 1.4 mm |
|---------------|--------|

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

### Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
|---------------|------------------------|

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

|                                     |                        |
|-------------------------------------|------------------------|
| Result                              | Test passed            |
| Polarization and coding             |                        |
| Specification                       | IEC 60512-13-5:2006-02 |
| Result                              | Test passed            |
| Insertion and withdrawal forces     |                        |
| Result                              | Test passed            |
| No. of cycles                       | 25                     |
| Insertion strength per pos. approx. | 10 N                   |
| Withdraw strength per pos. approx.  | 8 N                    |

## Electrical tests

|                             |                       |
|-----------------------------|-----------------------|
| Thermal test   Test group C |                       |
| Specification               | IEC 60512-5-1:2002-02 |
| Tested number of positions  | 16                    |

|                                              |                       |
|----------------------------------------------|-----------------------|
| Insulation resistance                        |                       |
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Air clearances and creepage distances                  |                     |
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 250 V               |
| Rated surge voltage (III/3)                            | 4 kV                |
| minimum clearance value - non-homogenous field (III/3) | 3 mm                |
| minimum creepage distance (III/3)                      | 3.2 mm              |
| Rated insulation voltage (III/2)                       | 320 V               |
| Rated surge voltage (III/2)                            | 4 kV                |
| minimum clearance value - non-homogenous field (III/2) | 3 mm                |
| minimum creepage distance (III/2)                      | 3 mm                |
| Rated insulation voltage (II/2)                        | 400 V               |
| Rated surge voltage (II/2)                             | 4 kV                |
| minimum clearance value - non-homogenous field (II/2)  | 3 mm                |
| minimum creepage distance (II/2)                       | 3 mm                |

## Environmental and real-life conditions

|                |                             |
|----------------|-----------------------------|
| Vibration test |                             |
| Specification  | IEC 60068-2-6:2007-12       |
| Frequency      | 10 - 150 - 10 Hz            |
| Sweep speed    | 1 octave/min                |
| Amplitude      | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration   | 5g (60.1 Hz ... 150 Hz)     |

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

|                        |                   |
|------------------------|-------------------|
| Test duration per axis | 2.5 h             |
| Test directions        | X-, Y- and Z-axis |

## Durability test

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level       | 4.8 kV                |
| Contact resistance R <sub>1</sub>            | 2.9 mΩ                |
| Contact resistance R <sub>2</sub>            | 2.9 mΩ                |
| Insertion/withdrawal cycles                  | 25                    |
| Insulation resistance, neighboring positions | > 5 MΩ                |

## Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | EN ISO 22479:2022-06                                                      |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 2.21 kV                                                                   |

## Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|


## Drawings

Diagram




Type: BCVP-508R-... with BCH-508V-...

Diagram



Type: BCVP-508W-... with BCH-508V-...



Type: BCP-508-... with BCH-508V-...

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5452422>

|                                                                                                                                                       |                                |                                |                   |                               |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
| <div> <b>cULus Recognized</b><br/>Approval ID: E60425-20071007</div> |                                |                                |                   |                               |
|                                                                                                                                                       | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| B                                                                                                                                                     |                                |                                |                   |                               |
|                                                                                                                                                       | 300 V                          | 15 A                           | -                 | -                             |

|                                                                                                                                                                     |                                |                                |                   |                               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
| <div> <b>VDE report with production monitoring</b><br/>Approval ID: 40040694</div> |                                |                                |                   |                               |
|                                                                                                                                                                     | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                                               |                                |                                |                   |                               |
|                                                                                                                                                                     | 320 V                          | 12 A                           | -                 | 0.2 - 2.5                     |

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# BCH-508V-12 BK - PCB header



5452422

<https://www.phoenixcontact.com/us/products/5452422>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)