

FLKM 4-I/O-G4 - Optocoupler module



5521322
<https://www.phoenixcontact.com/us/products/5521322>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE 4-channel module for solid state relays



Your advantages

- Modules accept Opto 22 G4 or Grayhill G5 solid state relays
- Solid-state relay includes fuse and status indicator
- Can be fitted with solid-state relays or I/O modules

Commercial data

Item number	5521322
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61Y2
GTIN	4046356683814
Weight per piece (including packing)	110.2 g
Weight per piece (excluding packing)	110.2 g
Customs tariff number	85364190
Country of origin	US

FLKM 4-I/O-G4 - Optocoupler module



5521322

<https://www.phoenixcontact.com/us/products/5521322>

Technical data

Product properties

Product type	Multi-channel solid-state relay module
No. of channels	4
Compatible components	Digital I/O modules
With components	no

Input data

Input voltage range	4 V DC ... 32 V DC
Typical input current at U_N	30 mA (Optocoupler dependent)

Output data

Compatible components	Digital I/O modules
-----------------------	---------------------

Switching

Limiting continuous current	4 A
Error detection (line break / short-circuit)	no

Connection data

Input

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of connections	1
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 14

Dimensions

Width	67.5 mm
Height	77 mm
Depth	42 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC, side panel PA non-reinforced,

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Mounting

FLKM 4-I/O-G4 - Optocoupler module



5521322

<https://www.phoenixcontact.com/us/products/5521322>

Assembly note	in rows with zero spacing
Mounting position	any

FLKM 4-I/O-G4 - Optocoupler module



5521322

<https://www.phoenixcontact.com/us/products/5521322>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5521322>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705

FLKM 4-I/O-G4 - Optocoupler module



5521322

<https://www.phoenixcontact.com/us/products/5521322>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 9.0	EC001456
----------	----------

FLKM 4-I/O-G4 - Optocoupler module



5521322
<https://www.phoenixcontact.com/us/products/5521322>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com