

DATA SHEET

THIN FILM CHIP RESISTORS AUTOMOTIVE GRADE

RP series

0.1% TO 1%, TC10 TO TC50

sizes 0201/0402/0603/0805/1206/1210

RoHS compliant



SCOPE

This specification describes RP0201 to RP1210 high precision-high stability chip resistors made by thin film process.

APPLICATIONS

- Automotive electronics
- Industrial and medical equipment
- Test and measuring equipment
- Telecommunications

FEATURES

- AEC-Q200 qualified
- Pb free without RoHS exemption
- Halogen free epoxy
- Superior resistance against sulfur containing surroundings
- Moisture sensitivity level: MSL 1
- Environmental hazards reduction
- Non-forbidden materials used in products/production

ORDERING INFORMATION - GLOBAL PART NUMBER

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

RP XXXX X X X XX XXXXX L
(1) (2) (3) (4) (5) (6) (7)

(1) SIZE

0201 / 0402 / 0603 / 0805 / 1206 / 1210

(2) TOLERANCE

B = $\pm 0.1\%$

C = $\pm 0.25\%$

D = $\pm 0.5\%$

F = $\pm 1\%$

(3) PACKAGING TYPE

R = Paper taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

B = $\pm 10 \text{ ppm}/^{\circ}\text{C}$

C = $\pm 15 \text{ ppm}/^{\circ}\text{C}$

D = $\pm 25 \text{ ppm}/^{\circ}\text{C}$

E = $\pm 50 \text{ ppm}/^{\circ}\text{C}$

(5) TAPING REEL

07 / 7W inch dia. Reel and specific rated power

Detailed power rating are shown in the Table 2.

(6) RESISTANCE VALUE

There are 2~4 digits indicated the resistor value.

Letter R/K/M is decimal point

Example: 100R = 100 Ω

1K = 1,000 Ω

(7) DEFAULT CODE


Letter L is the system default code for ordering only. (NOTE)

ORDERING EXAMPLE


The ordering code of a RP0402 0.063W chip resistor, TCR 25 value 56 Ω with $\pm 0.5\%$ tolerance, supplied in 7-inch tape reel is: RP0402DRD0756RL.

NOTE


1. All our Rchip products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process".
2. On customized label, "LFP" or specific symbol can be printed.

MARKING**RP0201 / RP0402**


No marking

RP0603Value = 12.4 K Ω

E-96 series: including values 10/11/13/15/20/75 of E-24 series, 3 digits

Value = 56 K Ω

E-24 series: exception values 10/11/13/15/20/75 of E-24 series, one short bar under marking letter

RP0805 / RP1206 / RP1210Value = 10 K Ω Both E-24 and E-96 series: 4 digits
First three digits for significant figure and 4th digit for number of zeros**NOTE**


For further marking information, please see special data sheet "Chip resistors marking".

CONSTRUCTION

The resistors are constructed out of a ceramic body. Internal metal electrodes are added at each end connected by a resistive layer.

This resistive layer is trimmed to its nominal value and on both ends a contact is made which will guarantee optimum solderability. This is achieved by applying several layers and for ease of soldering the outer layer consists of Ni/matte tin. Adding a special protective layer, passivation coating, on this series to enhance moisture resistance of the environment.

OUTLINES



DIMENSIONS

Table I

TYPE	L (mm)	W (mm)	H (mm)	I1 (mm)	I2 (mm)
RP0201	0.60±0.03	0.30±0.03	0.23±0.03	0.13±0.05	0.15±0.05
RP0402	1.00 ±0.10	0.50 ±0.05	0.30 ±0.05	0.20 ±0.10	0.25 ±0.10
RP0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.25 ±0.15	0.25 ±0.15
RP0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.35 ±0.20	0.35 ±0.20
RPI206	3.10 ±0.10	1.60 ±0.10	0.55 ±0.10	0.45 ±0.20	0.40 ±0.20
RPI210	3.10 ±0.10	2.60 ±0.15	0.55 ±0.10	0.50 ±0.20	0.50 ±0.20

ELECTRICAL CHARACTERISTICS

Table 2

TYPE	Operating Temperature Range	Power Rating@70°C ⁽³⁾		Max. Working Voltage	Max. Overload Voltage	Resistance Range (E-24/E-96 series)(Ω) & Tolerance ⁽¹⁾					Unit weight (mg/pcs)
		07	7W			T.C.R. (ppm/°C) ⁽²⁾	±0.1% (B)	±0.25% (C)	±0.5% (D)	±1% (F)	
RP0201	-55 °C to +125 °C	1/20 W	--	25V	50V	±50 (E)	22~75K	22~75K	22~75K	22~75K	0.169
						±25 (D)	22~75K	22~75K	22~75K	22~75K	
						±50 (E)	1~300K	1~300K	1~300K	1~300K	
						±25 (D)	4.7~300K	4.7~300K	4.7~300K	4.7~300K	
RP0402		1/16 W	--	50 V	100 V	±15 (C)	10~240K	10~240K	10~240K	10~240K	0.572
						±10 (B)	10~240K	10~240K	10~240K	10~240K	
						±50 (E)	10~240K	10~240K	10~240K	10~240K	
						±25 (D)	10~240K	10~240K	10~240K	10~240K	
RP0603		1/8 W	--	75V	150 V	±15 (C)	10~240K	10~240K	10~240K	10~240K	2.128
						±10 (B)	10~240K	10~240K	10~240K	10~240K	
						±50 (E)	10~240K	10~240K	10~240K	10~240K	
						±25 (D)	10~240K	10~240K	10~240K	10~240K	
RP0805	-55 °C to +155 °C	1/10 W	--	75V	150 V	±15 (C)	10~1M	10~1M	10~1M	10~1M	4.642
						±10 (B)	10~1M	10~1M	10~1M	10~1M	
						±50 (E)	10~1M	10~1M	10~1M	10~1M	
						±25 (D)	10~1M	10~1M	10~1M	10~1M	
RP0805		1/5 W	--	150 V	300 V	±15 (C)	10~1M	10~1M	10~1M	10~1M	4.642
						±10 (B)	10~1M	10~1M	10~1M	10~1M	
						±50 (E)	10~1M	10~1M	10~1M	10~1M	
						±25 (D)	10~1M	10~1M	10~1M	10~1M	
RP0805		1/4 W	--	150 V	300 V	±15 (C)	10~1M5	10~1M5	10~1M5	10~1M5	4.642
						±10 (B)	10~1M5	10~1M5	10~1M5	10~1M5	
						±50 (E)	10~1M5	10~1M5	10~1M5	10~1M5	
						±25 (D)	10~1M5	10~1M5	10~1M5	10~1M5	
RP1206		1/4 W	--	200 V	400 V	±15 (C)	10~1M5	10~1M5	10~1M5	10~1M5	10.116
						±10 (B)	10~1M5	10~1M5	10~1M5	10~1M5	
						±50 (E)	10~1M5	10~1M5	10~1M5	10~1M5	
						±25 (D)	10~1M5	10~1M5	10~1M5	10~1M5	
RP1206		2/5W	--	200 V	400 V	±15 (C)	10~1M5	10~1M5	10~1M5	10~1M5	10.116
						±10 (B)	10~1M5	10~1M5	10~1M5	10~1M5	
						±50 (E)	10~1M5	10~1M5	10~1M5	10~1M5	
						±25 (D)	10~1M5	10~1M5	10~1M5	10~1M5	
RP1210		1/4 W	--	200 V	400 V	±50 (E)	1~3M	1~3M	1~3M	1~3M	15.805
						±25 (D)	4.7~3M	4.7~3M	4.7~3M	4.7~3M	

FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please see the special data sheet “Chip resistors mounting”.

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PRODUCT TYPE	PATKING STYLE	REEL DIMENSION	QUANTITY PER REEL
RP0201	Paper taping reel	7" (178 mm)	10,000 Units
RP0402	Paper taping reel	7" (178 mm)	10,000 Units
RP0603	Paper taping reel	7" (178 mm)	5,000 Units
RP0805	Paper taping reel	7" (178 mm)	5,000 Units
RPI206	Paper taping reel	7" (178 mm)	5,000 Units
RPI210	Paper taping reel	7" (178 mm)	5,000 Units

NOTE: for paper tape and reel specification/dimensions, please see the special data sheet “packing” document.

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

0201 Range: -55 °C to +125 °C

Other Range: -55 °C to +155 °C

POWER RATING

Each type rated power at 70 °C:

RP0201=1/20 W

RP0402=1/16 W; 1/8 W

RP0603=1/10 W; 1/5 W

RP0805=1/8 W; 1/4 W

RPI206=1/4 W; 2/5W

RPI210=1/4W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$


Or max. working voltage whichever is less

Where

V=Continuous rated DC
or AC (rms) working voltage (V)

P=Rated power

R=Resistance value (Ω)



TESTS AND REQUIREMENTS**Table 4** Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Short Time Overload	IEC60115-1 4.13	2.5 times of rated voltage or maximum overload voltage, the less of the above, for 5 sec at room temperature	$\pm(0.05\%+0.05\Omega)$
High Temperature Exposure	AEC-Q200 Test 3 MIL-STD-202 Method 108	1000 hours at maximum operating temperature depending on specification, unpowered	$\pm(0.3\%+0.05\Omega)$
Biased Humidity	AEC-Q200 Test 7 MIL-STD-202 Method 103	1,000 hours; 85 °C / 85% RH 10% of operating power Measurement at 24±4 hours after test conclusion	0201 : $\pm(0.2\%+0.05\Omega)$ 0402 / 0603 / 0805 / 1206 : $\pm(0.1\%+0.05\Omega)$ 1210 $1 \leq R \leq 1M \pm(0.1\%+0.05\Omega)$ $1M < R \leq 2M \pm(0.2\%+0.05\Omega)$ $2M < R \leq 3M \pm(0.5\%+0.05\Omega)$
Life	AEC-Q200 Test 8 MIL-STD-202 Method 108	1,000 hours at 70±5 °C, with the rated voltage or maximum working voltage applied (whichever is lesser), 1.5 hours on, 0.5 hour off, still air required.	$\pm(0.1\%+0.05\Omega)$
Resistance to Soldering Heat	AEC-Q200 Test 15 MIL-STD-202 Method 210	Specimen passed 3 times reflow temperature at 260°C, with solder	$\pm(0.05\%+0.05\Omega)$
Temperature Cycling	AEC-Q200 Test 4 JESD22-A104	RP0201: 1,000 cycles, -55/+125°C for 1 cycle per 30 minutes Others: 1,000 cycles, -55/+155°C for 1 cycle per 30 minutes	$\pm(0.3\%+0.05\Omega)$ No visible damage
Solderability Wetting	AEC-Q200 Test 18 J-STD-002	(1) Baking 4 hours at 155°C dry heat, dipping at 245± 3°C for 5± 0.5 seconds. (2) Baking 4 hours at 155°C dry heat, dipping at 260± 3°C for 30± 0.5 seconds.	Well tinned (>95% covered) No visible damage

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Board Flex / Bending	AEC-Q200 Test 2I AEC-Q200-005	Chips mounted on a glass epoxy resin PCB (FR4) Bending for 0201 / 0402: 5 mm 0603/0805: 3 mm 1206/1210: 2mm Holding time: minimum 60 second	$\pm(0.1\%+0.05\Omega)$
Temperature Coefficient of Resistance (T.C.R.)	IEC 60115-1 4.8	At +25/-55 °C and +25/+125°C Formula: $T.C.R = \frac{R2 - R1}{R1(t2 - t1)} \times 10^6 (\text{ppm}/^\circ\text{C})$ Where t1 = +25 °C or specified room temperature t2 = -55 °C or +125 °C test temperature R1 = resistance at reference temperature in ohms R2 = resistance at test temperature in ohms	Refer to table 2
Flower of Sulfur	ASTM-B-809-95* * Modified	Sulfur 750 hours, 105°C, unpowered.	0201 : $\pm(5.0\%+0.05\Omega)$ other: $\pm(2.0\%+0.05\Omega)$

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 5	Jul. 14, 2025	-	- Add RP0201 series - Extend RP0805 R value
Version 4	Apr. 07, 2025	-	- Extend R value
Version 3	May 10, 2024	-	- Add RP1210 series - Extend power rating
Version 2	Oct. 03, 2023	-	- Extend double power rating
Version 1	Nov. 07, 2022	-	- Extend temperature coefficient of resistance range ($B=\pm 10\text{ppm}/^{\circ}\text{C}$) - Add unit weight
Version 0	Jul. 25, 2022	-	- First issue of this specification

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.