

# DATA SHEET

## SURFACE MOUNT MULTILAYER CERAMIC CAPACITORS

General purpose class II

X6S

4 V TO 50 V

100 pF to 47μF

RoHS compliant & Halogen free



**YAGEO**

Product Specification – December 9, 2025 v.8



**SCOPE**

This specification describes X6S series chip capacitors with lead-free terminations.

**APPLICATIONS**

PCs, Hard disk, Game PCs  
Power supplies  
DVD players  
Mobile phones  
Data processing

**FEATURES**

Supplied in tape on reel  
Nickel-barrier end termination  
RoHS compliant  
Halogen free compliant

**ORDERING INFORMATION - GLOBAL PART NUMBER**

All part numbers are identified by the series, size, tolerance, TC material, packing style, voltage, process code, termination and capacitance value.

**YAGEO BRAND ordering code****GLOBAL PART NUMBER (PREFERRED)**

**CC    XXXX    X    X    **X6S**    X    **BB**    XXX**

(1)    (2)    (3)    (4)    (5)

**(1) SIZE – INCH BASED (METRIC)**

0201 (0603)

0402 (1005)

0603 (1608)

0805 (2012)

1206 (3216)

1210 (3225)

**(2) TOLERANCE**

K =  $\pm 10\%$

M =  $\pm 20\%$

**(3) PACKING STYLE**

R = Paper/PE taping reel; Reel 7 inch

K = Blister taping reel; Reel 7 inch

P = Paper/PE taping reel; Reel 13 inch

F = Blister taping reel; Reel 13 inch

C = Bulk case

**(4) RATED VOLTAGE**

4 = 4 V

5 = 6.3 V

6 = 10 V

7 = 16 V

8 = 25 V

9 = 50 V

**(5) CAPACITANCE VALUE**

2 significant digits+number of zeros

The 3rd digit signifies the multiplying factor, and letter R is decimal point


Example: 103 =  $10 \times 10^3 = 10,000 \text{ pF} = 10 \text{ nF}$



## CONSTRUCTION

The capacitor consists of a rectangular block of ceramic dielectric in which a number of interleaved metal electrodes are contained. This structure gives rise to a high capacitance per unit volume.

The inner electrodes are connected to the two end terminations and finally covered with a layer of plated tin (NiSn). The terminations are lead-free. A cross section of the structure is shown in Fig.1.




## DIMENSION

Table I For outlines see fig. 2

TYPE	L <sub>1</sub> (mm)	W (mm)	T (MM)	L <sub>2</sub> / L <sub>3</sub> (mm) min.	L <sub>2</sub> / L <sub>3</sub> (mm) max.	L <sub>4</sub> (mm) min.
0201	0.6 ±0.03	0.3 ±0.03	0.3 ±0.03	0.10	0.20	0.20
	0.6±0.09	0.3 ±0.09	0.3±0.09			
0402	1.0 ±0.05	0.5 ±0.05	0.5 ±0.05	0.15	0.35	0.30
	1.0 ±0.1	0.5 ±0.1	0.5 ±0.1			
	1.0 ±0.15	0.5 ±0.15	0.5 ±0.15			
0603	1.0 ±0.20	0.5 ±0.20	0.5 ±0.20	0.20	0.60	0.40
	1.6±0.10	0.8 ±0.10	0.8 ±0.10			
	1.6 ±0.15	0.8 ±0.15	0.8 ±0.15			
0805	1.6 ±0.20	0.8 ±0.20	0.8 ±0.20	0.25	0.75	0.70
	2.0±0.20	1.25 ±0.20	1.25 ±0.20			
	3.2 ±0.30	1.6 ±0.20	1.6 ±0.20			
1206	3.2 ±0.40	2.5 ±0.30	2.5 ±0.20	0.25	0.75	1.40
	3.2 ±0.40	2.5 ±0.30	2.5 ±0.30			

## OUTLINES



CAPACITANCE RANGE & THICKNESS FOR X6S

Table 2 Sizes from 0201 to 0603

CAP.	0201				0402				0603				
	6.3V	10V	16V	25V	6.3 V	10 V	16 V	25 V	4 V	6.3 V	10 V	16 V	25 V
<b>100 nF</b> 0.3±0.03 0.3±0.03 0.3±0.03 0.3±0.03 0.5±0.05 0.5±0.05 0.5±0.05 0.5±0.05													
220 nF	0.3±0.03	0.3±0.03			0.5±0.05	0.5±0.05	0.5±0.05	0.5±0.05					
470 nF	0.3±0.09				0.5±0.05	0.5±0.05	0.5±0.1						
1 uF	0.3±0.09				0.5±0.05	0.5±0.05	0.5±0.1	0.5±0.20	0.8±0.1	0.8±0.1	0.8±0.1	0.8±0.1	0.8±0.15
2.2 uF					0.5±0.20	0.5±0.20	0.5±0.20		0.8±0.1	0.8±0.1	0.8±0.1	0.8±0.2	0.8±0.2
4.7 uF					0.5±0.15				0.8±0.2	0.8±0.2	0.8±0.2	0.8±0.2	
10 uF					0.5±0.20				0.8±0.2	0.8±0.2	0.8±0.2	0.8±0.2	
22 uF									0.8±0.2	0.8±0.2			
47 uF													

Table 3 Sizes from 0805 to 1210

CAP.	0805					1206					1210		
	6.3 V	10 V	16 V	25 V	50 V	6.3 V	10 V	16 V	25 V	6.3 V	10 V	16 V	
<b>100 nF</b>													
220 nF													
470 nF													
1 uF													
2.2 uF	1.25±0.2	1.25±0.2	1.25±0.2	1.25±0.2	1.25±0.2								
4.7 uF	1.25±0.2	1.25±0.2	1.25±0.2	1.25±0.2									
10 uF	1.25±0.2	1.25±0.2	1.25±0.2	1.25±0.2		1.6±0.2	1.6±0.2	1.6±0.2	1.6±0.2				
22 uF	1.25±0.2	1.25±0.2	1.25±0.2			1.6±0.2	1.6±0.2						
47 uF	1.25±0.2									2.5±0.2	2.5±0.2		
100 uF													



THICKNESS CLASSES AND PACKING QUANTITY

Table 4

SIZE CODE	THICKNESS CLASSIFICATION	TAPE WIDTH QUANTITY PER REEL	Ø180 MM / 7 INCH		Ø330 MM / 13 INCH		QUANTITY PER BULK CASE
			Paper	Blister	Paper	Blister	
0201	0.3 ±0.03 mm	8 mm	15,000	---	50,000	---	---
0402	0.5 ±0.05 mm	8 mm	10,000	---	50,000	---	50,000
0603	0.8 ±0.1 mm	8 mm	4,000	---	15,000	---	15,000
0805	1.25 ±0.2 mm	8 mm	---	3,000	---	10,000	5,000
1206	1.6 ±0.2 mm	8 mm	---	2,000	---	8,000	---
1210	2.5±0.2/0.3 mm	8 mm	---	500	---	---	---

ELECTRICAL CHARACTERISTICS**X6S DIELECTRIC CAPACITORS; NISN TERMINATIONS**

Unless otherwise specified, all tests and measurements shall be made under standard atmospheric conditions for testing as given in 5.3 of IEC 60068-1:

- Temperature: 15 ° C to 35 ° C
- Relative humidity: 25% to 75%
- Air pressure: 86 kPa to 106 kPa

Before the measurements are made, the capacitor shall be stored at the measuring temperature for a time sufficient to allow the entire capacitor to reach this temperature.

The period as prescribed for recovery at the end of a test is normally sufficient for this purpose.

Table 5

DESCRIPTION	VALUE
Capacitance range	100 nF to 100 µF
Capacitance tolerance	±10% and ±20%
Dissipation factor (D.F.)	≤10%
Insulation resistance after 1 minute at $U_r$ (DC)	$R_{ins} \times C_r \geq 100 / 50 \Omega \cdot F^*$
Maximum capacitance change as a function of temperature (temperature characteristic/coefficient):	±22%
Operating temperature range:	-55 °C to +105 °C

## Note:

$R_{ins} \times C_r \geq 100 \Omega \cdot F$

0201: 100nF to 470nF

0603: 1uF, 2.2uF/ 6.3V to 16V, 4.7uF/ 6.3V to 16V

0805: 2.2uF, 4.7uF to 10uF/ 6.3V to 16V

1206: 10uF/ 6.3V to 16V, 22uF/ 6.3V to 10V

$R_{ins} \times C_r \geq 50 \Omega \cdot F$

0201: 100nF / 16V to 25V, 1uF

0402: 220nF to 1uF/ 6.3V to 25V, 470nF/ 6.3V to 16V,

1uF to 2.2uF/ 6.3V to 16V, 4.7uF/ 6.3V, 10uF/ 6.3V

0603: 1uF/ 50V, 2.2uF/ 25V, 4.7uF/ 25V, 10uF to 22uF

0805: 4.7uF/ 50V, 10uF/ 25V, 22uF to 47uF

1206: 10uF/ 25V, 22uF/ 16V, 47uF to 100uF

1210: 47uF to 100uF



**SOLDERING RECOMMENDATION**

Table 6

SOLDERING METHOD	SIZE $\leq 0402$	0603	0805	1206	$\geq 1210$
Reflow	Reflow only	$\geq 1.0 \mu F$	$\geq 2.2 \mu F$	$\geq 4.7 \mu F$	Reflow only
Reflow/Wave	---	$< 1.0 \mu F$	$< 2.2 \mu F$	$< 4.7 \mu F$	---

**TESTS AND REQUIREMENTS**

Table 7 Test procedures and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Mounting	IEC 60384- 21/22	4.3 The capacitors may be mounted on printed-circuit boards or ceramic substrates	No visible damage
Visual Inspection and Dimension Check	IEC 60384- 21/22	4.4 Any applicable method using $\times 10$ magnification	In accordance with specification
Capacitance <sup>(1)</sup>	IEC 60384- 21/22	4.5.1 Class 2:  At 20 °C, 24 hrs after annealing Cap $\leq 1 \mu F$ , f = 1 KHz, measuring at voltage 1 Vrms at 20 ° C Cap $> 1 \mu F$ , f = 1 KHz for C $\leq 10 \mu F$ , rated voltage $> 6.3 V$ , measuring at voltage 1 Vrms at 20 ° C f = 1 KHz, for C $\leq 10 \mu F$ , rated voltage $\leq 6.3 V$ , measuring at voltage 0.5 to 1 Vrms at 20 ° C f = 120 Hz for C $> 10 \mu F$ , measuring at voltage 0.5 Vrms at 20 ° C	Within specified tolerance
Dissipation Factor (D.F.) <sup>(1)</sup>	IEC 60384- 21/22	4.5.2 Class 2:  At 20 °C, 24 hrs after annealing Cap $\leq 1 \mu F$ , f = 1 KHz, measuring at voltage 1 Vrms at 20 ° C Cap $> 1 \mu F$ , f = 1 KHz for C $\leq 10 \mu F$ , rated voltage $> 6.3 V$ , measuring at voltage 1 Vrms at 20 ° C f = 1 KHz, for C $\leq 10 \mu F$ , rated voltage $\leq 6.3 V$ , measuring at voltage 0.5 Vrms at 20 ° C f = 120 Hz for C $> 10 \mu F$ , measuring at voltage 0.5 Vrms at 20 ° C	In accordance with specification
Insulation Resistance	IEC 60384- 21/22	4.5.3 At U <sub>r</sub> (DC) for 1 minute	In accordance with specification

**NOTE**

- I. The figure indicates typical inspection. Please refer to individual specifications.



TEST	TEST METHOD	PROCEDURE	REQUIREMENTS												
Temperature Characteristic	IEC 60384- 21/22	<p>Capacitance shall be measured by the steps shown in the following table.</p> <p>The capacitance change should be measured after 5 min at each specified temperature stage.</p> <table border="1"> <thead> <tr> <th>Step</th><th>Temperature(°C)</th></tr> </thead> <tbody> <tr> <td>a</td><td>25±2</td></tr> <tr> <td>b</td><td>Lower temperature±3°C</td></tr> <tr> <td>c</td><td>25±2</td></tr> <tr> <td>d</td><td>Upper Temperature±2°C</td></tr> <tr> <td>e</td><td>25±2</td></tr> </tbody> </table>	Step	Temperature(°C)	a	25±2	b	Lower temperature±3°C	c	25±2	d	Upper Temperature±2°C	e	25±2	X6S: Δ C/C: ±22%
Step	Temperature(°C)														
a	25±2														
b	Lower temperature±3°C														
c	25±2														
d	Upper Temperature±2°C														
e	25±2														
Adhesion	IEC 60384- 21/22	<p>Class II</p> <p>Capacitance Change shall be calculated from the formula as below</p> $\Delta C = \frac{C2 - C1}{C1} \times 100\%$ <p>C1: Capacitance at step c C2: Capacitance at step b or d</p>	<p>Force</p> <p>size ≥ 0603: 5N</p> <p>size = 0402: 2.5N</p> <p>size = 0201: 1N</p>												
Bending Strength	IEC 60384- 21/22	<p>Mounting in accordance with IEC 60384-22 paragraph 4.3</p> <p>Conditions: bending 1 mm at a rate of 1 mm/s, radius jig 5 mm</p>	<p>No visible damage</p> <p>ΔC/C</p> <p>X6S: ±10%</p>												

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Resistance to Soldering Heat	IEC 60384-21/22	<p>4.9</p> <p>Precondition: 150 +0/-10 °C for 1 hour, then keep for 24 ±1 hours at room temperature</p> <p>Preheating: for size ≤ 1206: 120 °C to 150 °C for 1 minute</p> <p>Preheating: for size &gt;1206: 100 °C to 120 °C for 1 minute and 170 °C to 200 °C for 1 minute</p> <p>Solder bath temperature: 260 ±5 °C</p> <p>Dipping time: 10 ±0.5 seconds</p> <p>Recovery time: 24 ±2 hours</p>	<p>Dissolution of the end face plating shall not exceed 25% of the length of the edge concerned</p> <p>ΔC/C</p> <p>X6S: ±10%</p> <p>D.F. within initial specified value</p> <p>R<sub>ins</sub> within initial specified value</p>
Solderability	IEC 60384-21/22	<p>4.10</p> <p>Preheated the temperature of 80 °C to 140 °C and maintained for 30 seconds to 60 seconds.</p> <p>1. Temperature: 235±5°C / Dipping time: 2 ±0.5 s</p> <p>2. Temperature: 245±5°C / Dipping time: 3 ±0.5 s (lead free)</p> <p>Depth of immersion: 10mm</p>	The solder should cover over 95% of the critical area of each termination
Rapid Change of Temperature	IEC 60384-21/22	<p>4.11</p> <p>Preconditioning: 150 +0/-10 °C for 1 hour, then keep for 24 ±1 hours at room temperature</p> <p>5 cycles with following detail:</p> <p>30 minutes at lower category temperature</p> <p>30 minutes at upper category temperature</p> <p>Recovery time 24 ±2 hours</p>	<p>No visual damage</p> <p>ΔC/C</p> <p>X6S: ±15%</p> <p>D.F. meet initial specified value</p> <p>R<sub>ins</sub> meet initial specified value</p>



TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Damp Heat with $U_r$ Load	IEC 60384-21/22	4.13 <ol style="list-style-type: none"> <li>Preconditioning, class 2 only: 150 <math>+0/-10</math> °C /1 hour, then keep for 24 <math>\pm 1</math> hour at room temp</li> <li>Initial measure: Spec: refer to initial spec C, D, IR</li> <li>Damp heat test: 500 <math>\pm 1</math> hours at 40 <math>\pm 2</math> °C; 90 to 95% R.H. 1.0 <math>U_r</math> applied</li> <li>Recovery: Class 2: 24 <math>\pm 2</math> hours</li> <li>Final measure: C, D, IR P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be preconditioned according to "IEC 60384 4.1" and then the requirements shall be met.</li> </ol>	No visual damage after recovery $\Delta C/C$ $\pm 20\%$ D.F. $2 \times$ initial value max $R_{ins}$ Rins $\times Cr \geq 5s$
Endurance	IEC 60384-21/22	4.14 <ol style="list-style-type: none"> <li>Preconditioning, class 2 only: 150 <math>+0/-10</math> °C /1 hour, then keep for 24 <math>\pm 1</math> hour at room temp</li> <li>Initial measure: Spec: refer to initial spec C, D, IR</li> <li>Endurance test: Temperature: X6S: 105 °C Specified stress voltage applied for 1,000 hours: Applied 1.5 <math>\times U_r</math>. Applied 1 <math>U_r</math>: 0201: 1uF 0402: 4.7uF, 10uF 0603: 10uF, 22uF 0805: 10uF/ 25V, 22uF/ 10V to 16V, 47uF/6.3V Recovery time: 24 <math>\pm 2</math> hours</li> <li>Final measure: C, D, IR P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be preconditioned according to "IEC 60384 4.1" and then the requirements shall be met.</li> </ol>	No visual damage $\Delta C/C$ $\pm 20\%$ D.F. $2 \times$ initial value max $R_{ins}$ Rins $\times Cr \geq 10s$
Voltage Proof	IEC 60384-1	4.6 <p>Specified stress voltage applied for 1~5 seconds  <math>U_r \leq 100</math> V: series applied 2.5 <math>U_r</math>            Charge/Discharge current is less than 50 mA</p>	No breakdown or flashover

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 8	Dec. 9, 2025	-	<ul style="list-style-type: none"><li>- Add 0402/6.3V/10uF</li><li>- Add 0402/16V/2.2uF</li><li>- Add 0402/25V/1uF</li><li>- Add 0603/10V/4.7uF to 10uF</li><li>- Add 0603/16V/4.7uF to 10uF</li><li>- Add 0603/25V/2.2uF</li><li>- Add 0603/50V/1uF</li><li>- Add 0805/6.3V/47uF</li><li>- Add 0805/10V/22uF</li><li>- Add 0805/16V/22uF</li><li>- Add 0805/25V/10uF</li></ul>
Version 7	Feb. 07, 2023	-	<ul style="list-style-type: none"><li>- Product range updated</li></ul>
Version 6	Jan. 20, 2021	-	<ul style="list-style-type: none"><li>- Product range updated</li></ul>
Version 5	Jun. 2, 2020	-	<ul style="list-style-type: none"><li>- Product range updated</li></ul>
Version 4	Aug 7, 2017	-	<ul style="list-style-type: none"><li>- 0402 Dimension update</li></ul>
Version 3	Jul 19, 2017	-	<ul style="list-style-type: none"><li>- Product range updated</li></ul>
Version 2	Feb. 20, 2017	-	<ul style="list-style-type: none"><li>- Dimension &amp; capacitance update</li></ul>
Version 1	Sep. 16, 2015	-	<ul style="list-style-type: none"><li>- Dimension &amp; capacitance update</li></ul>
Version 0	Nov. 18, 2014	-	<ul style="list-style-type: none"><li>- New datasheet for general purpose High Cap X6S</li></ul>



LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.