# **Technical Data Sheet**



SPDT Ramses SMA 3GHz Latching Indicators 28Vdc Positive common Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : SPDT PART NUMBER : R570343010

#### RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.10
Insertion loss max	0.15 dB
Isolation min	80 dB
Average power (*)	240 W

#### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 80 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

#### MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 10 million cycles

Switching Time\*\*\* : < 10 ms

Construction : Splashproof

Weight : < 45 g

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)



# **Technical Data Sheet**




SPDT Ramses SMA 3GHz Latching Indicators 28Vdc Positive common


Pins Terminals

PAGE 2/2 ISSUE 22-03-22 SERIE : SPDT PART NUMBER : R570343010

DRAWING

[1.343]






General tolerances : ±0,5 mm [0,02 in]

00 0 00 0 🛱

### SCHEMATIC DIAGRAM

(3)



Voltage	RF Continuity	Ind.
+C -1	$C \leftrightarrow 1$	C.1
+C -2	$C \leftrightarrow 2$	C.2