KRG Series

- Low profile : φ10×12.5mm to φ18×25mm
- Endurance : 1,000 hours at 105℃
- Solvent resistant type (see PRECAUTIONS AND GUIDELINES)
- RoHS2 Compliant

◆SPECIFICATIONS

Items	Characteristics							
Category Temperature Range	-55 to +105℃							
Rated Voltage Range	6.3 to 50Vdc							
Capacitance Tolerance	±20% (M)							(at 20℃, 120Hz)
Leakage Current	I=0.01CV or 3μA, whichever is greater. Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V)							(at 20℃ after 2 minutes)
Dissipation Factor (tan δ)	Rated voltage (Vdc)	6.3V	10V	16V	25V	35V	50V	
	tan δ (Max.)	0.28	0.24	0.20	0.16	0.14	0.12	
	When nominal capacitance exceeds 1,000μF, add 0.03 to the value above for each 1,000μF increase.							(at 20℃, 120Hz)
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (Vdc)	6.3V	10V	16V	25V	35V	50V	
	Z(-25℃)/Z(+20℃)	5	4	3	2	2	2	
	Z(-40℃)/Z(+20℃)	10	8	6	4	3	3	(at 120Hz)
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage is applied for 1,000 hours at 105℃.							
	Rated voltage	6.3 to 16Vdc				25 to 50Vdc		
	Capacitance change	≦±25% of the initial value				≦±20% of the initial value		
	D.F. (tan δ)	≦200% of the initial specified value				≦200% of the initial specified value		
	Leakage current	≦The initial specified value				≦The initial specified value		
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 500 hours at 105℃ without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.							
	Rated voltage	6.3 to 16Vdc				25 to 50Vdc		
	Capacitance change	≦±25% of the initial value				≦±20% of the initial value		
	D.F. (tan δ)	≦200% of the initial specified value				≦200% of the initial specified value		
	Leakage current	≦The initial specified value				≦The initial specified value		

◆DIMENSIONS [mm]

●Terminal Code : E



φD	10 & 12.5	16 & 18
φd	0.6	0.8
F	5.0	7.5
φD'	φD+0.5max.	
L'	L+1.5max.	

◆PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"

KRG Series

◆STANDARD RATINGS

WV (V_{dc})	Cap (μF)	Case size φD×L(mm)	tan δ	Rated ripple current (mArms/ 105℃, 120Hz)	Part No.
6.3	4,700	16×15	0.37	1,010	EKRG6R3E□□472ML15S
	6,800	18×15	0.43	1,190	EKRG6R3E□□682MM15S
	10,000	18×20	0.55	1,440	EKRG6R3E□□103MM20S
10	1,000	10×12.5	0.24	445	EKRG100E□□102MJC5S
	2,200	12.5×15	0.27	690	EKRG100E□□222MK15S
	3,300	16×15	0.30	940	EKRG100E□□332ML15S
	4,700	18×15	0.33	1,120	EKRG100E□□472MM15S
	6,800	18×20	0.39	1,330	EKRG100E□□682MM20S
	10,000	18×25	0.51	1,700	EKRG100E□□103MM25S
16	1,000	12.5×13	0.20	515	EKRG160E□□102MK13S
	2,200	16×15	0.23	830	EKRG160E□□222ML15S
	3,300	18×15	0.26	1,050	EKRG160E□□332MM15S
	4,700	18×20	0.29	1,260	EKRG160E□□472MM20S
	6,800	18×25	0.35	1,560	EKRG160E□□682MM25S

WV (V_{dc})	Cap (μF)	Case size φD×L(mm)	tan δ	Rated ripple current (mArms/ 105℃, 120Hz)	Part No.
25	470	10×12.5	0.16	370	EKRG250E□□471MJC5S
	1,000	12.5×15	0.16	590	EKRG250E□□102MK15S
	2,200	18×15	0.19	970	EKRG250E□□222MM15S
	3,300	18×20	0.22	1,220	EKRG250E□□332MM20S
	4,700	18×25	0.25	1,470	EKRG250E□□472MM25S
35	330	10×12.5	0.14	340	EKRG350E□□331MJC5S
	470	12.5×13	0.14	415	EKRG350E□□471MK13S
	1,000	16×15	0.14	720	EKRG350E□□102ML15S
	2,200	18×20	0.17	1,110	EKRG350E□□222MM20S
50	220	10×12.5	0.12	290	EKRG500E□□221MJC5S
	330	12.5×13	0.12	370	EKRG500E□□331MK13S
	470	16×15	0.12	535	EKRG500E□□471ML15S
	1,000	18×20	0.12	830	EKRG500E□□102MM20S

□□ : Enter the appropriate lead forming or taping code.

◆RATED RIPPLE CURRENT MULTIPLIERS

●Frequency Multipliers

Capacitance(μF) \ Frequency(Hz)	50	120	300	1k	10k	100k
220 to 1,000	0.80	1.00	1.15	1.30	1.40	1.50
2,200 to	0.85	1.00	1.03	1.05	1.08	1.08

The deterioration of aluminum electrolytic capacitors accelerates their life due to the internal heating produced by ripple current. For details, refer to Section "5-3 Ripple Current Effect on Lifetime" in the catalog, Technical Note.

■ Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.

■ Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.

■ The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.

■ The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.

■ We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.

■ We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products

■ We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

CAT. No. E1001Z 2025