

4-Port HDMI over Cat6 Extender Switch Kit, Wall Plate/Box - 4K 60 Hz, HDR, 4:4:4, IR, PoC, 230 ft. (70.1 m), TAA

MODEL NUMBER: B127A-4X1-BH



HDMI extender kit with receiver transmits and allows switching among four 4K signals to an HDMI display up to 230 ft. away via Cat6 cable.

Features

HDMI Extender Kit Ideal for Digital Signage in Schools, Restaurants and Lecture Halls

This HDMI switch kit includes a quad-input wall plate switch and a box-style receiver. It's recommended for office buildings, schools, houses of worship, trade shows, meeting facilities, retail settings, hotels and other settings with video presentations or digital signage applications. It extends 4K audio/video up to 230 feet (70.1 meters), making it ideal for areas where the four source devices and single display are farther apart than conventional cabling allows.

Extends a 4K A/V Transmission up to 230 ft....or More

The B127A-4X1-BH transmits and allows switching among four HDMI sources to an HDMI display up to 230 feet away via user-supplied Cat6 cabling. You may select which video to display using the push button on the switch or the included IR remote control, which lets you operate the switch from the receiver end of the installation. By installing a B127A-010-H signal repeater (sold separately) between the switch and receiver, you can extend the signal up to 400 feet (121.9 meters).

Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color

The B127A-4X1-BH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as specified in HDMI 2.0, with 36-bit Deep Color and DTS-HD, Dolby TrueHD and 7.1-channel surround sound via TOSLINK port. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This extender kit also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Built-In PoC Technology Provides Power to Avoid Bulky External Power Bricks

After you connect the included external power supply to the switch, Power over Cable (PoC) technology powers the receiver over Cat6 cable. LEDs on both the switch and receiver will light up to indicate the system is receiving power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to place the receiver without the need for a nearby AC outlet.

Plug-and-Play Operation for Quick Setup and Immediate Use

The included double-gang metal wall plate switch and box receiver operate with no software required. The receiver comes with detachable brackets for mounting to a pole, rack or flat surface. Connect the switch to as many as four sources with user-supplied HDMI cables (such as P568- or P569-Series). Then, connect

Highlights

- Supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0
- Switches between 4 source devices by manual push button or included IR remote
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Power over Cable (PoC) technology provides power to receiver via Cat6 cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

Switch between 4 different digital signage messages to display up to 230 ft. awayExtend video signals from one room to another using Cat6 cable, which can pass through conduit to meet building codesGain flexibility in where the PoC receiver is installed, with the freedom to install it away from an AC outletImprove the line of sight for digital signage in a hotel, restaurant, theater, house of worship, trade show or other location

System Requirements

- Source devices with HDMI output (Blu-ray player, cable box, laptop)
- Display device with HDMI input (HDTV, projector, monitor)

Package Includes

- Wall plate switch
- Box receiver
- IR adapter
- IR remote control
- External power supply (Input: 100-240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, Europe, U.K., Australia)
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

the receiver to the display with an HDMI cable. Finally, connect the two units with user-supplied Cat6 patch cable (such as N202-Series).

TAA-Compliant for GSA Schedule Purchases

The B127A-4X1-BH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332264107
Product Type	Extender Kit
Technology	Cat6; HDMI; Stereo Audio
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	(4) HDMI (FEMALE)
Video Ports Details	HDMI 2.0; HDCP 1.4; HDCP 2.2
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 3840x2160 (4K)
Max Supported Video Resolution	3840 x 2160 @ 60 Hz
Max. Distance (Between any 2 Units)	230 ft.
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K) Range (ft)	230
Maximum Distance with Booster	400
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	1
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	230
Signal Range (m)	70
Range Extension with Booster	Yes
Range Extension using other Tripp Lite product	Up to 400 ft. total



Powering Business Worldwide

TRIPP LITE
SERIES

Extended Mode	No
Mirror Mode	No
Other Tripp Lite product used to extend range	B27A-010-H
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Signal Transmission	Unidirectional
AUDIO	
Audio Ports	HDMI (FEMALE); TOSLINK (FEMALE)
Audio Ports Details	Pass-through audio to whichever display is currently in use, or via the Toslink port
Audio Input	HDMI
Audio Output	HDMI; Toslink
Audio Specification	Supports pass-through of Audio format including LPCM2.0/5.1/7.1
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
AC Power Adapter Output Specs (V / A)	24V / 1A
AC Power Adapter Cord Length (ft.)	4.53
AC Power Adapter Cord Length (m)	1.38
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
Power Source	AC Adapter
POWER	
Power Source Type	AC Adapter
AC Plug Type	AS/NZS 3112; BS1363; Bare Wire; CEE 7/16 Schuko; NEMA 1-15P
Power Source	Transmitter end only (Included)
Power Over Cable (PoC) Support	Yes
Receiver Power Source	Power Over Cable
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	(4) HDMI (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	3.5MM (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	TOSLINK (FEMALE)
Input x Output	4 x 1

USER INTERFACE, ALERTS & CONTROLS

LED Indicators	Switch Unit: (x1) Power/Data = Solid Green (Powered by external power supply), Flashing Green (Sending data to receiver), (x4) Output LED's = Orange (Shows which port is currently displaying to receiver); Receiver: (x1) Power = Green (Receiving power), (x1) RJ45 Port = Green (power), Orange (receiving data)0
----------------	---

PHYSICAL

Color	Black; White
Material of Construction	Metal
Included Mounting Accessories	Wall-plate switch includes screws; Receiver includes mounting brackets and screws
Number of Displays	1
Form Factor/Mounting Options	Box; Rackmount; Wall-mount; Wallplate
Rackmountable	Yes
Receiver Unit Dimensions (hwd / cm.)	2.7 x 11.5 x 6.24
Receiver Unit Dimensions (hwd / in.)	1.063 x 4.528 x 2.457
Receiver Unit Weight (kg)	0.453
Receiver Unit Weight (lbs.)	1
Shipping Dimensions (hwd / in.)	3.27 x 13.54 x 5.91
Shipping Dimensions (hwd / cm)	8.31 x 34.39 x 15.01
Shipping Weight (lbs.)	3.05
Shipping Weight (kg)	1.39
Transmitter Unit Dimensions (hwd / cm.)	11.45 x 11.6 x 5.12
Transmitter Unit Dimensions (hwd / in.)	4.51 x 4.57 x 2.02
Transmitter Unit Weight (kg)	0.453
Transmitter Unit Weight (lbs.)	1
Unit Packaging Type	Box

ENVIRONMENTAL

Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 85% RH, Non Condensing



Powering Business Worldwide

TRIPP LITE
SERIES

COMMUNICATIONS	
Signal Range (ft.)	230
Signal Range (m)	70
Transmission Distance	230 ft., 400 ft. (with B127A-010-H signal booster)
EDID Compatible	Yes
IR Remote Extension Support	Yes
Consumer Electronics Control (CEC) Supported	No
Latency	3-5 seconds (switching between ports)
FEATURES & SPECIFICATIONS	
All-in-One Kit	Yes
Integrated/Removable Cable	No
MST Support	No
Mounting Accessory Included	Yes
Multi-Resolution Support	No
Port Selection	Pushbutton; Remote Selector
HDCP Specification	2.2
Driver Required	No
Recommended Category Cable	24 AWG Cat6
DIN Mountable	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CCC; CE; FCC; GS; LPS; TUV; UL; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.