


DVI over Cat5/6 Active Extender, Box-Style Remote Receiver for Video, DVI-I Single Link, Up to 200 ft. (60 m), TAA

MODEL NUMBER: **B140-1A0**



Transmit a DVI-D Single-Link signal up to 200 ft. away using a single Cat5e/6 patch cable

Description

The B140-1A0 is a receiver unit that is used with the B140-002 and B140-004 extender/splitter transmitter units. It transmits a DVI-D Single-Link signal up to 200 feet (61 meters) away using a single Cat5e/6 Ethernet cable. To achieve maximum distance and resolution, use 24 AWG Solid Wire Cat5e/6 cable (N202-Series). The B140-1A0 is compatible with all operating systems and is plug and play with no software or drivers required. It features a built-in equalization control for adjustment of the video image. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Installation is simple. Connect a B140-002 or B140-004 transmitter (not included) to a DVI source using a P561-Series DVI cable (not included). Connect the B140-1A0 to a display using a P561-Series DVI cable (not included). Finally, the receiver unit is connected to an RJ45 port on the transmitter unit using a single Cat5e/6 cable. A 1920 x 1080 at 60 Hz signal can be extended up to 150 feet (45.7 meters) from the source or a 1024 x 768 at 60 Hz signal up to 200 feet.

Further expand the range and number of monitors by using a B140-110 repeater unit. Add up to four remote units (three repeaters and one active receiver) to each channel of the B140-002 or B140-004 for a total of four displays per channel (an active receiver should be the last unit in a channel). A 1920 x 1080 at 60 Hz signal can be extended up to 125 feet (38.1 meters) from each repeater to the next unit in the channel or a 1024 x 768 at 60 Hz signal can be extended up to 175 feet (53.3 meters)

Features

- Transmit a DVI-D Single-Link signal up to 200-ft. (61 m) away using a single Cat5e/6 patch cable
- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 at 60 Hz
- Extends a 1920 x 1080 at 60 Hz signal up to 150-ft. (45.7 m), or a 1024 x 768 at 60 Hz signal up to 200-ft. (61 m)
- Use 24 AWG Solid Wire Cat5e/6 cable, such as N202-Series, to achieve maximum distance and resolution
- Features a built-in Equalization control for adjustment of the video image
- Further expand the range and number of monitors by using a B140-110 repeater unit
- Add up to four remote units (three repeaters and one active receiver) to each channel of the B140-002 or B140-004, for a total of 4 displays per channel. (An active receiver should be the last unit in a channel)
- A 1920 x 1080 at 60 Hz signal can be extended up to 125-ft. (38.1 m) from each repeater to the next

Highlights

- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60 Hz
- Extends a 1920 x 1080 @ 60 Hz signal up to 150 ft. (45.72 m), or a 1024 x 768 @ 60 Hz signal up to 200 ft. (61 m)
- Use 24 AWG, Solid Wire Cat5e/6 cable, such as N202-Series, to achieve maximum distance and resolution
- Can further expand the range and number of monitors by adding B140-110 repeaters
- Compatible with all operating systems
- Plug and play, no software or drivers required
- Features a built-in Equalization control for adjustment of the video image
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Package Includes

- B140-1A0 DVI over Cat5 Active Extender Remote Unit
- Mounting hardware
- Screwdriver for adjustment of Equalization
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5-ft. (1.52 m))
- Owner's Manual



Powering Business Worldwide

TRIPP LITE
SERIES

unit in the channel, or a 1024 x 768 at 60 Hz signal can be extended up to 175-ft. (53.3 m)

- HDCP compatible
- Compatible with all operating systems
- Plug and play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332156631
Product Type	Receiver
Technology	DVI; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p @ 60Hz)
Max 720P Range (ft)	200
Max 1080P Range (ft)	150
Max 1280 x 720 (720p) Range (ft)	150
Max 1920 x 1080 (1080p) Range (ft)	150
Receiver/Transceiver Video Output	DVI-I
Receiver - Number of Video Outputs	1
Range Extension using other Tripp Lite product	175 ft. @ 1024 x 768 XGA 125 ft. @ 1920 x 1080 UXGA
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	B140-110
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	200
Maximum Signal Range (m)	61
Maximum Signal Range Details	200 ft @ 1024 x 768 XGA 150 ft @ 1920 x 1080 UXGA
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.4



Powering Business Worldwide

TRIPP LITE
SERIES

Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Requires B140-110
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45: Green (Connection), Orange (Data Transmission)
PHYSICAL	
Color	Black
Number of Displays	1
Form Factor/Mounting Options	Box; Wall-mount
Shipping Dimensions (hwd / in.)	2.20 x 7.20 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 18.29 x 16.51
Shipping Weight (lbs.)	1.08
Shipping Weight (kg)	0.49
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.14
Unit Packaging Type	Box
Unit Weight (lbs.)	0.43
Unit Weight (kg)	0.20
Housing	Metal
Mounting Details	Wallmount
ENVIRONMENTAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-85% non-condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	200
Max 480P Range (ft)	200
Max 1440 x 900 Range (ft)	200
Max 1080i Range (ft)	150
Max 480i Range (ft)	200
Max 640 x 480 Range (ft)	200
Max 800 x 600 Range (ft)	200
Max 1600 x 1200 Range (ft)	200
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
Built-In Equalizer	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
Product Compliance	RoHS; REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.