


Protect It! 8-Outlet Computer Surge Protector, 8 ft. (2.43 m) Cord, 2160 Joules, Tel/Modem/Fax Protection

MODEL NUMBER: **TLP808TEL**



Highlights

- 8 outlets / 8-ft. (2.43 m) cord
- 2160 joule rating
- Modem/fax surge protection

Package Includes

- TLP808TEL
- 6-ft. (1.83 m) telephone cord
- Instruction manual with warranty information

Description

The TLP808TEL surge suppressor has eight outlets, an eight-foot (2.4 m) cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment.

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Long 8-ft. (2.43 m) AC line cable with space-saving angle input plug conveniently reaches distant outlets
- built-in RJ11 jacks (1in/2 out) prevent surges from damaging your modem/fax/phone equipment
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332095367
INPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
Outlet Safety Covers Detail	Includes built-in sliding outlet safety covers
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	330/400/400
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Gray
Housing Color	Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal slots = 75 mm; Distance between vertical slots = 41.6 mm
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	11.00 x 7.40 x 2.00
Shipping Dimensions (hwd / cm)	27.94 x 18.80 x 5.08
Shipping Weight (lbs.)	2.11
Shipping Weight (kg)	0.96
Unit Dimensions (hwd / in.)	4.860 x 9.550 x 1.510
Unit Dimensions (hwd / cm)	12.34 x 24.26 x 3.84
Unit Weight (lbs.)	1.89
Unit Weight (kg)	0.86
Input Cord Color	White
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed



Powering Business Worldwide

TRIPP LITE
SERIES

Product Compliance	FCC Part 68; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.