

USB-C to VGA Vertical Adapter (M/F) - USB 3.1, Gen 1, Thunderbolt 3, 1920 x 1200 (1080p), 5 Gbps, Black

MODEL NUMBER: U444-000-VGA



USB Type-C to VGA converter connects a VGA monitor to your tablet, phone, MacBook, Chromebook or Ultrabook's USB-C or Thunderbolt 3 port.

Features

USB Type-C to VGA Adapter Connects to Your Laptop or Tablet's USB-C or Thunderbolt 3 Port This USB Type-C to VGA adapter connects a VGA monitor to the USB Type-C or Thunderbolt 3 port on your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen. It saves you money by allowing you to use your existing VGA display instead of buying a new monitor.

Supports USB Type-C DisplayPort Alternate Mode for Converting Video Signals By connecting the USB Type-C plug to a source device that supports USB DisplayPort Alt Mode, you can output 1080p video to a VGA monitor, television or projector without the hassle of installing special software drivers.

Transmits Crystal-Clear 1080p Video to a VGA Display To send high-definition video to a VGA television, projector or monitor, connect the VGA port to the display using a VGA cable (such as P500-Series, sold separately). The VGA port supports HD video resolutions up to 1920 x 1200 (1080p) at 60 Hz.

Vertical Molding Prevents Blockage of Adjacent Ports The USB Type-C input's vertical orientation results in a slimmer adapter that maximizes space around the device's ports and prevents them from being blocked. Unlike traditional USB cables that connect in only one direction, the reversible USB Type-C male connector plugs into a USB Type-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB Type-C to VGA adapter is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB Type-C or Thunderbolt 3 port. It requires no software, drivers or external power. The palm-sized one-piece molding fits into your pocket, briefcase or laptop bag for connecting to VGA displays anywhere.

Specifications

Highlights

- Vertical USB Type-C plug orientation prevents adjacent ports from being blocked
- Converts video signals from sources supporting USB Type-C DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Reversible USB Type-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect your laptop to a VGA monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the MacBook, Chromebook or laptop in your office or home workspace
- Stream online video or games from your computer on a larger VGA display

System Requirements

- Source device with USB Type-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with VGA input

Package Includes

- U444-000-VGA USB-C to VGA Vertical Adapter, M/F, Black
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

| OVERVIEW | |
|--|--|
| UPC Code | 037332238115 |
| Product Type | USB-C to VGA Adapter |
| Technology | VGA/SVGA |
| VIDEO | |
| Video Input | USB C (MALE) |
| Video Output | VGA |
| Number of Monitors Supported | 1 |
| Video Ports | VGA |
| Resolutions Supported | Supports single VGA output up to 1920 x 1080 (1080P) @ 60 Hz |
| Supported Resolutions | 1920x1200 |
| Max Supported Video Resolution | 1920 x 1200 (1080p) @ 60Hz |
| HDR Support | No |
| 3D Video Supported | No |
| AUDIO | |
| Audio Specification | Stereo |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 2.53 |
| Product Length (cm.) | 6.5 |
| POWER | |
| USB Power Delivery (PD) Charging Support | No |
| CONNECTIONS | |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | HD15 (FEMALE) |
| Contact Plating | Gold |
| PHYSICAL | |
| Color | Black |
| Material of Construction | PBT, ABS |
| Number of Displays | 1 |
| Unit Dimensions (hwd / in.) | 0.560 x 0.080 x 2.530 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|--|
| Unit Packaging Type | Polybag |
| Unit Weight (lbs.) | 0.020 |
| Unit Weight (kg) | 0.01 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| Storage Temperature Range | 5° to 122°F (-15° to 50°C) |
| Relative Humidity | 0-85% non-condensing |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.