

## USB-C to DisplayPort 1.4 Active Adapter Cable (M/M), UHD 8K, Black/Silver, 3 ft. (0.9 m)

MODEL NUMBER: U444-003-DP8SE



USB-C to DP cable connects an 8K DisplayPort monitor to your MacBook Pro or Windows laptop's USB-C or Thunderbolt 3 port.

### Features

#### USB-C to DisplayPort Adapter Cable Supports Top of the Line Video Output

This high-speed USB Type-C to DisplayPort adapter supports audio/video data transfer speeds up to 8.2 Gbps per-lane (32.4 Gbps total) bandwidth for high-end AV applications. The cable is capable of transmitting video at specifications including 7680 x 4320 (8K) @ 30 Hz and 3840 x 2160 (4K x 2K) @ 120 Hz when connected to the USB-C port of a host that supports DisplayPort Alt Mode 1.4.

#### Ideal for High-Bandwidth Audio/Video Work and Beyond

The U444-003-DP8SE is capable of supporting high bandwidth applications like editing high-resolution images or video, viewing high-definition video content or playing video games at the highest settings. While practical for future-proofing applications for 8K content, the cable is backwards compatible with DP 1.2 Alt Mode signals for existing hardware.

#### Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play USB Type-C to DisplayPort cable requires no software or external power. Just connect the USB-C plug to the USB-C or Thunderbolt 3 port on a source device that supports DisplayPort Alternate Mode, and connect the DisplayPort plug to your display.

### Highlights

- Ideal for future-proofing your current AV application in anticipation of an 8K upgrade
- Converts audio/video signals from sources supporting USB DisplayPort Alt Mode
- Supports UHD resolutions up to 8K @ 30 Hz for enhanced video without latency
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Uni-directional plug-and-play cable directs signals only from USB-C to DisplayPort

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode 1.4 for best performance
- Display device with DisplayPort input
- Both source and display devices must be compatible with 8K standards to watch 8K video

### Package Includes

U444-003-DP8SE USB-C to DisplayPort Adapter Cable, M/M, Black/Silver, 3 ft. (0.9 m)

## Specifications

OVERVIEW	
UPC Code	037332255594
Product Type	Active Cable
Technology	DisplayPort
Cable Type	Active
VIDEO	



Powering Business Worldwide

TRIPP LITE  
SERIES

Max Supported Video Resolution	7860 x 4320 (8K) @ 30Hz
Max Supported Color Depth	48-bit Deep Color
HDR Support	Yes
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>PHYSICAL</b>	
Color	Black; Gray
Material of Construction	TPE
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	4.2mm
Wire Gauge (AWG)	34/24
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	0.25 x 7.00 x 9.00
Shipping Weight (lbs.)	0.12
Unit Dimensions (hwd / in.)	0.250 x 7.000 x 9.000
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.749
Unit Weight (kg)	0.34
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Displayport Specification	1.2; 1.4
HDCP Specification	2.2
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.