




5	SHELL	1	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED 1.REMOVE ALL BURRS. 2.BREAK ALL CONNERS & EDGES CO.15 MAX. 3.CHAMFER 1ST & LAST THREADS 45°. 4.DIAMETERS ON COMMON CENTERS. TO BE CONCENTRIC WITHIN 0.1 T.I.R. 5.ALL DIMENSIONS ARE AFTER PLATING.	* MAJOR DIMENSION UNLESS OTHERWISE NOTED TOLERANCES 0.5-6=±0.2 6-30=±0.4 30-120=±0.6 120-315=±1.0 ANGLES=±1°		APPROVED		Siretta Enabling Industrial IoT TITLE QMA PLUG TO SMA JACK DRAWING NO. ADAPT-QMAM-SMAF REV A FILE NO.					
4	RETAINING RING	1	BE Cu	NICKEL				CHECKED							
3	INSULATOR	2	TEFLON	NONE				DRAWN andrew							
2	PIN	1	BE Cu	GOLD											
1	BODY	1	BRASS	NICKEL											
NO	Description	Q'ty	Material	Finish			SCALE	3/1	UNIT	MM	DRAWN DATE 02/06/24				