

QUARTZ-LITE-DUAL Series

4G Single LAN DUAL SIM Small Footprint Industrial Router



Key Features

- European 4G / LTE bands
- High speed data via LTE network
- Strong resistance to electromagnetic interference
- Built-in watch dog, multi-link detection
- LITE industrial design
- Excellent temperature endurance
- Dual SIM for network failover/backup
- 1x LAN
- 1 x RS232 and 1 x RS485
- VPN: PPTP, L2TP, GRE, IPSec
- Optional GNSS/Wi-Fi

2G GSM	3G UMTS	4G LTE	CLI Telnet	EMEA Europe	LAN Ethernet	LIVE Stats	NAT Mapping	PSU 7V to 32V	PTP Connect
SMALL Footprint	SNMP Manage	SSH Manage	Syslog Service	TEMP -30 to +75C	TRACE Route	UPNP Protocol	VPN Tunnel	RS232 Serial	RS485 Serial
WiFi 4 802.11n	WiFi 2.4G	Win Linux/Mac							

General Description


Siretta's QUARTZ-LITE-DUAL 4G/LTE router is a high speed industrial router designed for transferring large amounts of data via the cellular network. The QUARTZ-LITE-DUAL 4G/LTE's fast data transfer capability reaches up to 100Mbps download and up to 50Mbps upload speed. It also has fall-back to 3G/UMTS communication, should 4G/LTE be unavailable. It is well suited for IoT/mobile broadband applications, offering reliable, secure wireless connectivity.

The QUARTZ-LITE-DUAL 4G/LTE router is of a robust design, coming in a small sized, metal enclosure, making it ideal for deployment in industrial embedded applications. Cellular coverage is designed to match European frequencies.

The QUARTZ software means VPN security is supported, allowing the router to be used in commercial as well as industrial applications.

The QUARTZ-LITE-DUAL 4G/LTE router meets many of the needs for management of remote communication, and therefore has applications in renewable energy, security, digital signage, transport, street furniture, traffic control, parking systems, environmental monitoring, and many other IoT/mobile broadband applications.

The QUARTZ-LITE-DUAL 4G/LTE router has an array of features to empower your application. These include a dual SIM facility meaning you can configure a back-up cellular network between two different SIM cards, to ensure seamless reliable connection regardless of individual network availability. In addition, this router has dual serial ports and single Ethernet port. It has the option to come with or without Wi-Fi. It also has optional GNSS capability, which means the router is ideal for asset tracking or access management.



QUARTZ-LITE-DUAL Series

4G Single LAN DUAL SIM Small Footprint Industrial Router

Additional Features

- » Supports DHCP server
- » Supports DNS proxy and Dynamic DNS (DNSS)
- » Supports timing operation
- » Supports LED status indication
- » Supports APN and VDPN wireless private network access
- » Supports 802.11b/g/n Wi-Fi, 150Mbps data rate
- » Local and remote management
- » SNMP network management, NTP support

Cellular

- » GSM network:
B3 (1800MHz), B8 (900MHz)
- » UMTS network:
B1 (2100MHz), B8 (900MHz)
- » LTE network:
B1 (2100MHz), B3 (1800MHz), B7 (2600MHz)
B8 (900MHz), B20 (800MHz), B28A (700MHz)
B38 (2600MHz), B40 (2300MHz)
B41 (2500MHz)

Interfaces

- » 1 x 10/100Mb LAN
- » 1 x 3G/4G SMA female antenna interface
- » 2 x standard SIM/R-UIM interface
- » 1 x RS232
- » 1 x RS485

Optional Interfaces

- » 1 x GNSS OR 1 x Wi-Fi SMA female antenna interface

Environmental

- » Dimensions: 103mm x 73.5 x 25.5mm
- » Weight: 225g (without antenna)
- » Operating Temperature Range: -30 to +70 deg C
- » Storage Temperature Range: -40 to +85 deg C
- » Relative Humidity: <95% Non-condensing

Router Settings

Route Protocol

- » Static route
- » RIPv2/OSPF dynamic route

Device Management

- » Local or remote web browser (IE v8 or above)
- » CLI/Telnet command
- » M2M management platform (optional)
- » SSH management (optional)

Firewall and Filter

- » IP packet/Domain/MAC filter
- » NAT
- » DMZ

LED Instruction


- » PWR
- » LAN
- » NET

VPN

- » IPSec
- » PPTP/L2TP client
- » GRE/IPIP

Wi-Fi

- » Standard: IEEE 802.11b/g/n
- » WEP, WPA and WPA2 encryption
- » Standard 150Mbps (300Mbps optional with additional antenna)



QUARTZ-LITE-DUAL Series

4G Single LAN DUAL SIM Small Footprint Industrial Router

Power

- » Idle: 80mA @ +12VDC
- » Single module comms: 320mA : +12VDC
- » Dual module comms: 600mA @ +12VDC
- » Power supply: 7.5 - 32VDC

Approvals and Compliance

- » CE
- » RoHS
- » CCC

Models Available

4G Single LAN DUAL SIM Small Footprint Industrial Router

QUARTZ-LITE-DUAL-12-LTE (EU) - **Stock Code 62296**

QUARTZ-LITE-DUAL-12-LTE (EU) + ACCESSORIES - **Stock Code 62297**

QUARTZ-LITE-DUAL-G12-LTE (EU) - **Stock Code 62298**

QUARTZ-LITE-DUAL-G12-LTE (EU) + ACCESSORIES - **Stock Code 62299**

QUARTZ-LITE-DUAL-W12-LTE (EU) - **Stock Code 62300**

QUARTZ-LITE-DUAL-W12-LTE (EU) + ACCESSORIES - **Stock Code 62301**