



Twistable and flexible rectangular waveguide R220, with PBR/UBR 220 flanges. Length = 1.2m, core with environmental impact resistant molded rubber jacket. Hardware and gasket (for PDR/PBR flanges) included.

FEATURES / BENEFITS

Waveguide installation

- The flexible and twistable rectangular waveguide component eliminates installation difficulties
- It isolates vibration
- It provides simple aid to positioning of antennas

**Technical features****STRUCTURE**

Type of Rectangular Waveguide Component		TwistFlex
Waveguide Size IEC (EIA)		R220 (WR42)
Flange A		PBR220
Flange B		UBR220
Flange Finish		Brass un-plated
Package Quantity		1

ELECTRICAL SPECIFICATIONS

Frequency Range	GHz	18 - 26.5
Minimum Return Loss (max. VSWR)	dB (VSWR)	20.8 (1.20)
Attenuation	dB	1.5
Power rating	W	100

MECHANICAL SPECIFICATIONS

Maximum Twist	degree/m (degree/ft)	270 (82.3)
Minimum Bending Radius E-Plane	mm (in)	38 (1.5)
Minimum Bending Radius H-Plane	mm (in)	75 (3)
Length	mm (in)	1200 (47.2)

MATERIAL

Material		Core: Brass silver plated Jacket: Vulcanised Neoprene Rubber Flange: Brass
Color		Black

External Document Links

AN 030707-8 Application note for RFS Technologies Twistflex

Notes