

TP151AT/702000 S00093 - Touch panel



2401371

<https://www.phoenixcontact.com/us/products/2401371>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 38.1 cm / 15"-TFT display (analog resistive (polyester)), 1024 x 768 pixel(s) (XGA), 65536 colors, Arm9™, 200 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, CODESYS, without bus system.

Commercial data

Item number	2401371
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABZ
GTIN	4055626148915
Weight per piece (including packing)	2,300 g
Weight per piece (excluding packing)	2,300 g

TP151AT/702000 S00093 - Touch panel



2401371

<https://www.phoenixcontact.com/us/products/2401371>

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	38.1 cm / 15"-TFT
Screen resolution	1024 x 768 Pixel(s) (XGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	480 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	65536 colors
Reading angle left	80.00 °
Reading angle right	80.00 °
Reading angle top	65.00 °
Reading angle bottom	80.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	CODESYS
---------------	---------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Typical current consumption	0.9 A
-----------------------------	-------

Real-time clock

Realtime clock	Yes
----------------	-----

Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Mounting

TP151AT/702000 S00093 - Touch panel



2401371

<https://www.phoenixcontact.com/us/products/2401371>

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	400 mm / 329 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	373 mm / 302 mm / 72 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

TP151AT/702000 S00093 - Touch panel



2401371

<https://www.phoenixcontact.com/us/products/2401371>

Classifications

UNSPSC

UNSPSC 21.0	43211904
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------