







PCB Layout

N = Number of poles.
Dim.A = $N \times 7.62 + 1.0$
Dim.B = $(N-1) \times 7.62$

POLE	4x2 ~ 4x4	4x5 ~ 4x8	4x9 ~ 4x12	4x12 ~ 4x16
Dim.A	±0.15	±0.25	±0.35	±0.45
Dim.B	±0.15	±0.25	±0.30	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	09/24`11	Add is "cULus" mark	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulator(Cover): Thermoplastic (UL94V-0)
- Item ② Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ Spring clamp: Stainless steel
- Item ④ Terminal Body(contact pin): Brass, Tin plated

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Critical dimension: ▽

△ ● Safety Approval: 

HS xx 5 0 x 1 xxxx G

No. OF POLES

G: Pb<40000ppm

08: 4x2 POLES

60: 4x15 POLES

64: 4x16 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

0000: "@" Logo (Standard)


000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HS 7.62mm Series (Solder pins staggered by half the pin spacing)			
PART NO.	HSxx50x1xxxxG			DWG NO.	8HS0005
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Runner 2011.09.24	Tony 2007.12.19		UNIT: mm SCALE: NONE
				SHEET: 01/01	REV.: B2
					X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°