


Dual band whip with Shock Spring for the 150 MHz and 450 MHz bands

DESCRIPTION

- External antenna whip mounted on the ProFin mount.
- When ordering the antenna, please state the centre frequency on each band.
- Sturdy, general-purpose dual-band ¼ λ antenna in professional quality.
- Easily removable for car wash.

CONNECTION DIAGRAM



SPECIFICATIONS

Electrical	
Model	MP-G-S/150/450/FQ
Antenna Type	Dual-band ½ λ mobile antenna
Max. Input Power	25 W
Polarisation	Vertical
Impedance	50 Ω
Bandwidth	150 MHz: 8 MHz @ VSWR ≤ 2.0 450 MHz: 15 MHz @ VSWR ≤ 2.0
Gain (EIA RS-329-1)	150 MHz: Approx 0 dB 450 MHz: Approx 0 dB

Mechanical	
Materials	Whip : Polyethylene covered copper thread / glass fibre Black-chromed brass Spring : Black-chromed stainless steel
Colour	Black
Height	Approx. 350 mm / 13.78 in.
Weight	Approx. 0.05 kg / 0.11 lb.
Mounting	On the ProFin G1 mount and ProFin G2 mount

ORDERING

Model	Product No.
MP-G-S/150/450/FQ/FQ whip	132000224
Accessories	
DIPX 225/330-FME (optional) *	200000670
FME(f)-SMA(f) adaptor (optional) *	130000575

ORDERING NOTE

When ordering the antenna, please state the centre frequency on each band.
* Both to be ordered separately.

MOUNTING DETAILS

