







N = Number of poles.
Dim.A = $N \times 10.0 + 1.0$
Dim.B = $(N - 1) \times 10.0$

POLE	4×2 ~ 4×4	4×5 ~ 4×8	4×9 ~ 4×12
Dim.A	±0.25	±0.35	±0.45
Dim.B	±0.25	±0.30	±0.40

PCB Layout

SIGN	DATE	DESCRIPTION	APPROVER
△	09/24/11	Add is "cULus" mark	Runner

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Insulator(Cover): Thermoplastic (UL94V-0)
- Item 2 Insulator(housing): Thermoplastic (UL94V-0)
- Item 3 Spring clamp: Stainless steel
- Item 4 Solder Pin (The fourth layer) : Brass, Tin plated
- Item 5 Solder Pin (The third layer) : Brass, Tin plated
- Item 6 Solder Pin (The second layer) : Brass, Tin plated
- Item 7 Solder Pin (The first layer) : Brass, Tin plated
- Item 8 Insulator(pad board): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Critical dimension: ▽

△ ● Safety Approval: cULus

HS xx 2 0 x 0 xxxx G

No. OF POLES

G: Pb<40000ppm

08: 4×2 POLES

44: 4×11 POLES

48: 4×12 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request.
please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HS 10.0mm Series (Solder pins in line)							
PART NO.	HSxx20x0xxxxG			DWG NO.	8HS0301			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Runner 2011.09.24	Kind 2009.6.8				UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: B		X.XX ±0.10	
							X° ±1°	