

Model 66332APZ2

ICP® TO-8 Accelerometer

Installation and Operating Manual

For assistance with the operation of this product, contact PCB Piezotronics, Inc.

Toll-free: 800-959-4464 24-hour SensorLine: 716-684-0001

Fax: 716-684-3823 E-mail: imi@pcb.com Web: www.imi-sensors.com







Repair and Maintenance

PCB guarantees Total Customer Satisfaction through its "Lifetime Warranty Plus" on all Platinum Stock Products sold by PCB and through its limited warranties on all other PCB Stock, Standard and Special products. Due to the sophisticated nature of our sensors and associated instrumentation, field servicing and repair is not recommended and, if attempted, will void the factory warranty.

Beyond routine calibration and battery replacements where applicable, our products require no user maintenance. Clean electrical connectors, housings, and mounting surfaces with solutions and techniques that will not harm the material of construction. Observe caution when using liquids near devices that are not hermetically sealed. Such devices should only be wiped with a dampened cloth—never saturated or submerged.

In the event that equipment becomes damaged or ceases to operate, our Application Engineers are here to support your troubleshooting efforts 24 hours a day, 7 days a week. Call or email with model and serial number as well as a brief description of the problem.

Calibration

Routine calibration of sensors and associated instrumentation is necessary to maintain measurement accuracy. We recommend calibrating on an annual basis, after exposure to any extreme environmental influence, or prior to any critical test.

PCB Piezotronics is an ISO-9001 certified company whose calibration services are accredited by A2LA to ISO/IEC 17025, with full traceability to SI through N.I.S.T. In addition to our standard calibration services, we also offer specialized tests, including: sensitivity at elevated or cryogenic temperatures, phase response, extended high or low frequency response, extended range, leak testing, hydrostatic pressure testing, and others. For more information, contact your local PCB Piezotronics distributor, sales representative, or factory customer service representative.

Returning Equipment

If factory repair is required, our representatives will provide you with a Return Material Authorization (RMA) number, which we use to reference any information you have already provided and expedite the repair process. This number should be clearly marked on the outside of all returned package(s) and on any packing list(s) accompanying the shipment.

Contact Information

PCB Piezotronics, Inc. 3425 Walden Ave. Depew, NY14043 USA Toll-free: (800) 828-8840

24-hour SensorLine: (716) 684-0001 General inquiries: info@pcb.com Repair inquiries: rma@pcb.com

For a complete list of distributors, global offices and sales representatives, visit our website, www.pcb.com.

Safety Considerations

This product is intended for use by qualified personnel who recognize shock hazards and are familiar with the precautions required to avoid injury. While our equipment is designed with user safety in mind, the protection provided by the equipment may be impaired if equipment is used in a manner not specified by this manual.

Discontinue use and contact our 24-Hour Sensorline if:

- Assistance is needed to safely operate equipment
- Damage is visible or suspected
- Equipment fails or malfunctions

For complete equipment ratings, refer to the enclosed specification sheet for your product.

Definition of Terms and Symbols

The following symbols may be used in this manual:



DANGER

Indicates an immediate hazardous situation, which, if not avoided, may result in death or serious injury.



CAUTION

Refers to hazards that could damage the instrument.



NOTE

Indicates tips, recommendations and important information. The notes simplify processes and contain additional information on particular operating steps.

The following symbols may be found on the equipment described in this manual:



This symbol on the unit indicates that high voltage may be present. Use standard safety precautions to avoid personal contact with this voltage.



This symbol on the unit indicates that the user should refer to the operating instructions located in the manual.



This symbol indicates safety, earth ground.



PCB工业监视和测量设备 - 中国RoHS2公布表

PCB Industrial Monitoring and Measuring Equipment - China RoHS 2 Disclosure Table

有害物 质					
铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴 联苯 (PBB)	多溴二苯醚 (PBDE)
0	0	0	0	0	0
Х	0	0	0	0	0
0	0	0	0	0	0
Х	0	0	0	0	0
0	0	0	0	0	0
0	0	0	0	0	0
0	0	0	0	0	0
0	0	Х	0	0	0
0	0	0	0	0	0
Х	0	0	0	0	0
0	0	0	0	0	0
Х	0	0	0	0	0
Х	0	0	0	0	0
	O X O O O O X X O X X X	田 (Pb) (Hg) (Hg) (Hg) (Hg) (Hg) (Hg) (Hg) (Hg	铅 (Pb) (Hg) (Cd) (Cd) (Cd) (Hg) (Cd) (Cd) (Cd) (Cd) (Cd) (Cd) (Cd) (Cd	田(Pb) 表 (Hg) (Cd) 大价铬(Cr(VI)) の の の の の の の の の の の の の の の の の の	報(Pb) 表(Hg) (Cd) 六价铬 (Cr(VI)) 多溴联苯 (PBB) 0 0 0 0 X 0 0 0 0 0 0 0 X 0 0 0 0 X 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 X 0 0 0 0 X 0 0 0 0 X 0 0 0 0 X 0 0 0 0 X 0 0 0 0 X 0 0 0 0 X 0 0 0 0

本表格依据 SJ/T 11364 的规定编制。

O:表示该有害物质在该部件所有均质材料中的含量均在 GB/T 26572 规定的限量要求以下。

X:表示该有害物质至少在该部件的某一均质材料中的含量超出 GB/T 26572 规定的限量要求。

铅是欧洲RoHS指令2011/65/EU附件三和附件四目前由于允许的豁免。

CHINA ROHS COMPLIANCE

Component Name	Hazardous Substances					
	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Chromium VI Compounds (Cr(VI))	Polybrominated Biphenyls (PBB)	Polybrominated Diphenyl Ethers (PBDE)
Housing	0	0	0	0	0	0
PCB Board	Х	0	0	0	0	0
Electrical Connectors	0	0	0	0	0	0
Piezoelectric Crystals	Х	0	0	0	0	0
Ероху	0	0	0	0	0	0
Teflon	0	0	0	0	0	0
Electronics	0	0	0	0	0	0
Thick Film Substrate	0	0	X	0	0	0
Wires	0	0	0	0	0	0
Cables	Х	0	0	0	0	0
Plastic	0	0	0	0	0	0
Solder	Х	0	0	0	0	0
Copper Alloy/Brass	Х	0	0	0	0	0

This table is prepared in accordance with the provisions of SJ/T 11364.

Lead is present due to allowed exemption in Annex III or Annex IV of the European RoHS Directive 2011/65/EU.

O: Indicates that said hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement of GB/T 26572.

X: Indicates that said hazardous substance contained in at least one of the homogeneous materials for this part is above the limit requirement of GB/T 26572.


Model Number 66332APZ2		ICP® TO	-8 ACC	ELEROMETER
Performance	ENGLISH	SI		
Sensitivity(± 20 %)	1,000 mV/g	102 mV/(m/s²)	[1][2]	Optional versions have
Measurement Range	± 5 g	$\pm 50 \text{ m/s}^2$,
Frequency Range(± 3 dB)	0.25 to 5k Hz	0.25 to 5k Hz	[3][4]	HT - High temperatu
Resonant Frequency	> 16 kHz	> 16 kHz	[4]	temperatures
Broadband Resolution	38 µg rms	373 µm/sec ² rms	[5]	Temperature Range(Operating)
Non-Linearity	≤ 1 %	≤ 1 %	[6]	Cable Type
Transverse Sensitivity	≤ 7 %	≤ 7 %		Electrical Connections Electrical Connections
Environmental				Liectrical Confidentions
Overload Limit(Shock)	5,000 g pk	49k m/s² pk		RH - RoHS Complian
Temperature Range(Operating)	-65 to +185 °F	-54 to +85 ℃		·
Temperature Response	See Graph	See Graph	[5]	
Electrical	•	·		
Settling Time(within 1% of bias)	≤ 30 sec	≤ 30 sec		
Discharge Time Constant	≥ 0.65 sec	≥ 0.65 sec		
Excitation Voltage	18 to 28 VDC	18 to 28 VDC		
Constant Current Excitation	2 to 20 mA	2 to 20 mA		
Output Impedance	< 550 Ohm	< 550 Ohm		
Output Bias Voltage	8 to 12 VDC	8 to 12 VDC		
Spectral Noise(10 Hz)	1.9 μg/√Hz	18.6 (µm/sec ²)/√Hz	[5]	
Spectral Noise(100 Hz)	0.6 μg/√Hz	5.9 (µm/sec ²)/√Hz	[5]	
Spectral Noise(1 kHz)	0.4 μg/√Hz	3.9 (µm/sec ²)/√Hz	[5]	
Physical				
Size (Lip Diameter x Height)	0.64 in x 0.57 in	16.3 mm x 14.5 mm		
Weight	0.88 oz	25 gm		
Mounting	Adhesive	Adhesive		
Sensing Element	Ceramic	Ceramic		
Sensing Geometry	Shear	Shear		
Housing Material	Stainless Steel	Stainless Steel		
Sealing	Welded Hermetic	Welded Hermetic		
Electrical Connector	Integral Cable	Integral Cable		
Electrical Connection Position	Bottom	Bottom		
Cable Termination	Blunt cut	Blunt cut		NOTES:
Electrical Connections(Red)	Signal / Power	Signal / Power		[1]Positive output alo
Electrical Connections(Black)	Neg (-) Ground	Neg (-) Ground		[2]Conversion Factor
Calala Lamada	- 1 4	0.2		■ [∠]CONVEISION Factor

1 ft

PVC

Cable Length

Cable Type



0.3 m

PVC

All specifications are at room temperature unless otherwise specified. In the interest of constant product improvement, we reserve the right to change specifications without notice. ICP® is a registered trademark of PCB Piezotronics, Inc.

OPTIONAL VERSIONS

Revision: C

ECN #: 50920

Optional versions have identical specifications and accessories as listed for the standard model except where noted below. More than one option may be used.

HT - High temperature, extends normal operation temperatures
Temperature
Range(Operating)
Cable Type
Electrical Connections(Red)
Electrical Connections(White)
Neg (-) G -65 to 250 °F -54 to 121 °C 031 PTFE Signal / Power Neg (-) Ground 031 PTFE Signal / Power Neg (-) Ground

RH - RoHS Compliant

NOTES:

- [1] Positive output along Z-axis (in upward direction when pin mounted).
- [2]Conversion Factor $1g = 9.81 \text{ m/s}^2$.
- [3] The high frequency tolerance is accurate within $\pm 10\%$ of the specified frequency.
- [4]Performance depends on mounting
- [5]Typical.
- [6]Zero-based, least-squares, straight line method.
- [7]See PCB Declaration of Conformance PS023 or PS060 for details.

SUPPLIED ACCESSORIES:

Model ICS-2 NIST-traceable single-point amplitude response calibration at 6000 cpm (100 Hz) for each axis (1)

Entered: LK	Engineer: NJF	Sales: MC	Approved: NJF	Spec Number:
Date: 07/07/2020	Date: 07/07/2020	Date: 07/07/2020	Date: 07/07/2020	47330



Phone: 800-959-4464 Fax: 716-684-3823 E-Mail: imi@pcb.com