


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	3/DEC/2013	
A1	Added ACD P/N to the table.	24/Oct/2019	




Reverse Polarity TNC Male

Reverse Polarity TNC Female

LENGTH & P/N Table

LENGTH	CUSTOMER P/N
3FT(914±30mm)	CO-058TNCMFRP-003
6FT(1829±40mm)	CO-058TNCMFRP-006
10FT(3048±40mm)	CO-058TNCMFRP-010
15FT(4572±50mm)	CO-058TNCMFRP-015
25FT(7620±100mm)	CO-058TNCMFRP-025



SECTION A-A

NOTES:

- CABLE:[20AWG(19/0.18±0.008mm)*1C+AL/MTLAR +BRAID(16*8/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 2.95±0.10mm COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC; OD=Ø5.0±0.15mm COLOR:UL813 BLACK
 - CONNECTOR:Reverse Polarity TNC Male
 - OPEN/SHORT MISS WIRE TEST 100%
 - CONDUCTOR RESISTANCE $\leq 36.7\Omega/\text{km}$
 - INSULATION RESISTANCE $\geq 2M\Omega$ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

PIN OUT:

CENTER	CENTER
SHELL	SHELL



NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:	E&R NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760		
	APPROVALS				
	DATE				
	DRAWN				
DIMEN'S	±X	±X"	LF	3/DEC/2013	RG58C/U RP TNC M/RP TNC F
X	±XX				
XXX	±XXX		BA	3/DEC/2013	
THIRD ANGLE PROJECTION	RESP ENG				
	MFG ENG				
	SIZE		DWG. NO.		
	A		CO-058TNCMFRP-XXX		REV.
					A1
QTD FILE:	SCALE		SHEET		OF