




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		31/OCT/2011	
A1	Correction of the DWG NO.		09/Dec/2019	




BNC M


LENGTH



BNC M RA



SECTION A-A



- NOTES:
- CABLE:[26AWG(7/0.16±0.008mm)*1C +BRAID(16*4/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 1.52±0.07mm ;COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC;OD=Ø2.54±0.10mm COLOR:UL813 BLACK.
 - MARKING:RG-174/U COAXIAL CABLE RoHS
 - CONNECTOR:BNC Male NICKEL-PLATED
 - OPEN/SHORT MISS WIRE TEST 100%
 - CONDUCTOR RESISTANCE ≤150Ω/km
 - INSULATION RESISTANCE ≥2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

LENGTH & P/N Table

LENGTH	P/N
1FT(305±20mm)	CO-174BNCRBNC-001
5FT(1524±30mm)	CO-174BNCRBNC-005

PIN OUT:

CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760			
DRAWN		APPROVALS		DATE		RG174/U BNC M/BNC M RA	
		LF					
CHECKED		BA		31/OCT/2011			
RESP ENG							
MFG ENG							
THIRD ANGLE PROJECTION		SIZE		DMG. NO.		REV.	
		A		CO-174BNCRBNC-XXX		A1	
RD FILE		SCALE		SHEET		OF	

NOTES: UNLESS OTHERWISE SPECIFIED