


REVISIONS		
REV.	DESCRIPTION	DATE
A	NEW RELEASE	02/July/09



1. CABLE: [26AWG(7/0.16±0.008mm)*1C
+BRAID(16*4/0.12±0.008mm)]TINNED COPPER
INSULATION:PE OD= 1.52±0.07mm ;COLOR:TRANSPARENT
JACKET:HALF MATTE PVC LOW TOXIC;OD=Ø2.54±0.10mm
COLOR:JL813 BLACK.

LENGTH & P/N Table

- MARKING:RG-174/U COAXIAL CABLE ROHS
- 2.CONNECTOR:SMA Male GOLD-PLATING
- 3.CONNECTOR:SMA Male RA GOLD-PLATING
- 4.OPEN/SHORT MISS WIRE TEST 100%
- 5.CONDUCTOR RESISTANCE $\cong 150\Omega/\text{km}$
- 6.INSULATION RESISTANCE $\cong 2\text{M}\Omega$ DC300V 0.01Sec

ALL MATERIALS SHALL ACCORD WITH ROHS STANDARD

CENTER — CENTER



NOTES: UNLESS OTHERWISE SPECIFIED

A