


ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector

2869728
<https://www.phoenixcontact.com/us/products/2869728>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail bus connector for DIN rail mounting. Universal for TBUS housing. Gold-plated contacts, 5-pos.

Your advantages

- Space-saving installation under the housing in the DIN rail
- Contact design enables electronics modules to be easily snapped on
- Power supply and communication without additional wiring
- Parallel and serial contacts for efficient signal and data transmission
- Fast module-to-module communication without additional wiring effort

Commercial data

Item number	2869728
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHACA
GTIN	4017918983093
Weight per piece (including packing)	6.14 g
Weight per piece (excluding packing)	4.6 g
Customs tariff number	85366990
Country of origin	DE

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Technical data

Notes

Recommendation	Material of contact pads for bus connector, galvanic gold (hard gold)
----------------	---

Product properties

Product type	DIN rail bus connector
Product family	TBUS5..2-6,2..
Number of positions	5
Pitch	3.81 mm
Pin layout	Linear pinning

Electrical properties

Properties

Nominal current I_N	8 A
Nominal voltage U_N	125 V
Contact resistance	2.17 mΩ
Rated voltage (III/3)	125 V
Rated surge voltage (III/3)	2.5 kV
Rated voltage (III/2)	125 V
Rated surge voltage (III/2)	2.5 kV

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	gold-plated

Material data - housing

Color (Housing)	green (6021)
Insulating material	PBT
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

material specifications - connector

Color ()	()
-----------	-----

Dimensions

Pitch	3.81 mm
-------	---------

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Width [w]	19.25 mm
Height [h]	36.3 mm
Length [l]	17.65 mm

Mounting

Mounting type	DIN rail mounting
Pin layout	Linear pinning

Mechanical tests

Insertion and withdrawal forces

Result	Test passed
No. of cycles	25
Insertion strength per pos. approx.	2.18 N
Withdraw strength per pos. approx.	1.38 N

Polarization and coding

Specification	IEC 60512-13-5:2006-02
Result	Test passed

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
Result	Test passed

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 Hz ... 60.1 Hz)
Acceleration	5g (60.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis (pos. and neg.)

Durability test

Specification	IEC 60512-9-1:2010-03
Impulse withstand voltage at sea level	2.9 kV
Contact resistance R ₁	2.17 mΩ
Contact resistance R ₂	2.26 mΩ
Insertion/withdrawal cycles	25

Climatic test

Specification	DIN 50018:2013-05
---------------	-------------------

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Corrosive stress	0.2 dm ³ SO ₂ on 300 dm ³ /40 °C/1 cycle
Thermal stress	100 °C/168 h
Power-frequency withstand voltage	1.4 kV

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	30g
Shock duration	18 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Electrical tests

Thermal test | Test group C

Specification	IEC 60512-5-1:2002-02
Tested number of positions	5

Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Insulating material group	I
Rated insulation voltage (III/3)	125 V
Rated surge voltage (III/3)	2.5 kV
minimum clearance value - non-homogenous field (III/3)	1.5 mm
minimum creepage distance (III/3)	1.9 mm
Rated insulation voltage (III/2)	125 V
Rated surge voltage (III/2)	2.5 kV
minimum clearance value - non-homogenous field (III/2)	1.5 mm
minimum creepage distance (III/2)	1.5 mm


ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Drawings



Type: ME 6,2 TBUS-2 1,5/5-ST-3,81 ...

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2869728>

cUL Recognized Approval ID: FILE E 60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	150 V	8 A	-	-
D				
	150 V	8 A	-	-

UL Recognized Approval ID: FILE E 60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	150 V	8 A	-	-
D				
	150 V	8 A	-	-

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - DIN rail bus connector



2869728

<https://www.phoenixcontact.com/us/products/2869728>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com