


C-LC-LC-1M5OM4

1m LC to LC Aqua OM4 Duplex OFNR (Riser-Rated) Fiber Patch Cable

Features

- LC/LC Male connectors
- OM4 Rated
- 1m length
- OFNR Riser Rated
- Aqua Color Jacket
- 50/125 Patch Cable




Product Description

This is a 1m LC to LC Aqua OM4 Duplex OFNR (Riser-Rated) Fiber Patch Cable. OM4 fiber optic cable is a high-performance multimode fiber optimized for high-speed data transmission, supporting up to 100G over distances of up to 150 meters. Ideal for data centers and large-scale network infrastructures, it delivers superior bandwidth and reliability for demanding business applications. OFNR riser fiber cable jackets are designed for vertical installations in building risers, providing fire-resistant protection to ensure safe data transmission between floors. These cables meet strict safety standards, making them ideal for businesses that need reliable, in-building network infrastructure without the risk of fire spreading through conduits. The Standard Boot option provides reliable and straightforward connections for fiber cables, making it an economical choice for various networking applications. Ideal for businesses that require dependable performance without the complexity, this option ensures consistent data transmission in everyday network setups. Our cables are TIA compliant, ensuring performance for all networking needs.

Specifications

Parameter	Specifications
Environment	Indoor
Standard	OM4
Fiber Type	MMF
Connector	LC (Male) to LC (Male)
Color	Aqua
Shielded	No
Strand Count	2
Cable Mode	Duplex
Jacket Type	Riser
Termination Type	Crossover
Core/Cladding	50/125µm
Fiber Termination	UPC - Ultra Physical Contact
Polarity	Type A-B
Cable Type	OM4
Cable Length	1m
Armored	No
Bend Insensitivity	G.657.A1
Connector 1 Ferrule Polish	UPC (Ultra Physical Contact)
Connector 2 Ferrule Polish	UPC (Ultra Physical Contact)
Insertion Loss Grade	Grade C
Fire Rating	Riser (OFNR)
Jacket Material	PVC (Polyvinyl Chloride)
Outer Diameter	2.0mm
Connector 1 Boot Style	Standard Boot
Connector 2 Boot Style	Standard Boot
Connector 1 Color	Beige
Connector 2 Color	Beige
Insertion Loss	≤0.2dB
Return Loss	≥35dB
Length Tolerance	
L<1m	+50mm
1m≤L<15m	+100mm
15m≤L<30m	+150mm
L≥30m	Length*1%

Mechanical Specifications



Item	Quantity	Specifications
1	A/R	OD: 2.0mm, Multi-Mode 50/125 OM4 Duplex Fiber Optic Cable, PVC (OFNR), Color: Aqua
2	2	LC/UPC MM 2.0mm Duplex Connector, Beige Housing, 19mm Short White Boot
3	4	Cable Marker
4	2	Black Shrinkage Tube

About ProLabs

Our experience comes as standard; for over 15 years ProLabs has delivered optical connectivity solutions that give our customers freedom and choice through our ability to provide seamless interoperability. At the heart of our company is the ability to provide state-of-the-art optical transport and connectivity solutions that are compatible with over 90 optical switching and transport platforms.

Complete Portfolio of Network Solutions

ProLabs is focused on innovations in optical transport and connectivity. The combination of our knowledge of optics and networking equipment enables ProLabs to be your single source for optical transport and connectivity solutions from 100Mb to 400G while providing innovative solutions that increase network efficiency. We provide the optical connectivity expertise that is compatible with and enhances your switching and transport equipment.

Trusted Partner

Customer service is our number one value. ProLabs has invested in people, labs and manufacturing capacity to ensure that you get immediate answers to your questions and compatible product when needed. With Engineering and Manufacturing offices in the U.K. and U.S. augmented by field offices throughout the U.S., U.K. and Asia, ProLabs is able to be our customers best advocate 24 hours a day.



Contact Information

ProLabs US

Email: sales@prolabs.com

Telephone: 952-852-0252

ProLabs UK

Email: salesupport@prolabs.com

Telephone: +44 1285 719 600